

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010452

Luminaire Tested: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010452
REPORT IS A COMBINATION OF REPORTS P989221 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6405.0 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010452

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010452

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64		
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	53		
2	92	84	78	72	86	79	74	69	70	65	62	61	58	55	53	51	49	45		
3	84	74	66	60	78	70	63	57	62	56	52	54	50	47	47	44	41	38		
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	32		
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28		
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25		
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22		
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20		
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18		
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1010452

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.3
10°-20°	416.5	6.5
20°-30°	615.1	9.6
30°-40°	718.4	11.2
40°-50°	722.2	11.3
50°-60°	634.4	9.9
60°-70°	472.5	7.4
70°-80°	268.9	4.2
80°-90°	78.0	1.2
90°-100°	27.0	0.4
100°-110°	130.4	2.0
110°-120°	319.5	5.0
120°-130°	405.6	6.3
130°-140°	433.3	6.8
140°-150°	405.2	6.3
150°-160°	326.8	5.1
160°-170°	210.9	3.3
170°-180°	72.7	1.1
0°-30°	1179.1	18.4
0°-40°	1897.5	29.6
0°-60°	3254.2	50.8
0°-90°	4073.5	63.6
90°-120°	476.9	7.4
90°-150°	1721.0	26.9
90°-180°	2331.0	36.4
0°-180°	6405.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	6	14	16	17	7
95°	35	11	18	22	22	41
105°	169	176	124	24	25	180
115°	318	321	326	332	334	314
125°	448	452	454	456	457	400
135°	557	561	563	565	563	429
145°	643	647	648	649	649	403
155°	708	707	708	711	707	326
165°	747	746	745	749	746	211
175°	765	762	762	766	762	73
180°	765	765	765	765	765	

TEST NUMBER: P1010452

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.1	9.7	14.8	18.7	19.3
95°	34.7	11.4	17.6	21.6	21.6
97.5°	63.1	47.2	18.2	22.7	23.3
100°	96.0	107.4	18.7	23.3	23.9
102.5°	133.5	140.9	42.0	23.3	24.4
105°	169.3	175.6	124.4	23.9	25.0
107.5°	207.4	212.5	221.0	133.5	59.1
110°	245.5	250.0	256.2	237.5	156.2

TEST NUMBER: P1010452

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.8	285.8	292.0	297.2	296.0
115°	317.6	321.0	326.1	331.8	334.1
117.5°	352.8	356.8	359.7	364.2	364.8
120°	385.2	390.3	392.0	396.6	396.6
122.5°	418.2	422.2	424.4	427.3	427.8
125°	447.7	452.3	454.5	455.7	456.8
127.5°	477.3	481.8	484.7	486.4	485.2
130°	504.5	509.1	511.4	513.6	512.5
132.5°	530.7	535.2	536.9	539.2	537.5
135°	557.4	560.8	563.1	564.8	563.1
137.5°	580.1	584.7	585.8	588.6	587.5
140°	602.8	606.2	608.0	610.2	609.1
142.5°	623.9	627.3	629.0	630.7	629.0
145°	643.2	647.2	648.3	649.4	649.4
147.5°	661.9	664.8	665.9	667.0	664.2
150°	679.0	680.7	681.8	683.0	681.2
152.5°	694.3	694.9	695.5	697.7	694.9
155°	708.5	707.4	708.0	710.8	707.4
157.5°	719.9	719.9	719.3	722.7	718.2
160°	730.1	729.5	729.0	732.4	728.4
162.5°	739.8	738.1	737.5	741.5	738.1
165°	747.2	745.5	744.9	749.4	745.5
167.5°	753.4	751.1	751.1	755.7	751.1
170°	758.5	756.2	756.2	760.8	756.2
172.5°	761.9	759.1	759.7	764.2	759.1
175°	764.8	761.9	762.5	766.5	761.9
177.5°	765.9	763.1	763.6	768.2	762.5
180°	764.8	764.8	764.8	764.8	764.8

(END OF REPORT)