

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010453

Luminaire Tested: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010453
REPORT IS A COMBINATION OF REPORTS P989222 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6193.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010453

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010453

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64		
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	53		
2	92	84	78	72	86	79	74	69	70	65	62	61	58	55	53	51	49	45		
3	84	74	66	60	78	70	63	57	62	56	52	54	50	47	47	44	41	38		
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	32		
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28		
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25		
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22		
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20		
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18		
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1010453

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	2.3
10°-20°	402.7	6.5
20°-30°	594.7	9.6
30°-40°	694.6	11.2
40°-50°	698.3	11.3
50°-60°	613.4	9.9
60°-70°	456.8	7.4
70°-80°	260.0	4.2
80°-90°	75.4	1.2
90°-100°	26.1	0.4
100°-110°	126.1	2.0
110°-120°	309.0	5.0
120°-130°	392.2	6.3
130°-140°	419.0	6.8
140°-150°	391.8	6.3
150°-160°	316.0	5.1
160°-170°	204.0	3.3
170°-180°	70.3	1.1
0°-30°	1140.0	18.4
0°-40°	1834.6	29.6
0°-60°	3146.3	50.8
0°-90°	3938.5	63.6
90°-120°	461.1	7.4
90°-150°	1664.2	26.9
90°-180°	2255.0	36.4
0°-180°	6193.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	0	6	13	15	16	6
95°	34	11	17	21	21	40
105°	164	170	120	23	24	174
115°	307	310	315	321	323	303
125°	433	437	440	441	442	387
135°	539	542	544	546	544	415
145°	622	626	627	628	628	389
155°	685	684	685	687	684	316
165°	722	721	720	725	721	204
175°	740	737	737	741	737	70
180°	740	740	740	740	740	

TEST NUMBER: P1010453

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	0.5	6.0	13.2	15.4	16.5
92.5°	12.6	9.3	14.3	18.1	18.7
95°	33.5	11.0	17.0	20.9	20.9
97.5°	61.0	45.6	17.6	22.0	22.5
100°	92.9	103.8	18.1	22.5	23.1
102.5°	129.1	136.3	40.7	22.5	23.6
105°	163.7	169.8	120.3	23.1	24.2
107.5°	200.5	205.5	213.7	129.1	57.1
110°	237.4	241.7	247.8	229.7	151.1

TEST NUMBER: P1010453

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.5	276.4	282.4	287.4	286.3
115°	307.1	310.4	315.4	320.9	323.1
117.5°	341.2	345.0	347.8	352.2	352.7
120°	372.5	377.5	379.1	383.5	383.5
122.5°	404.4	408.2	410.4	413.2	413.7
125°	432.9	437.3	439.5	440.6	441.7
127.5°	461.5	465.9	468.7	470.3	469.2
130°	487.9	492.3	494.5	496.7	495.6
132.5°	513.2	517.6	519.2	521.4	519.8
135°	539.0	542.3	544.5	546.1	544.5
137.5°	561.0	565.4	566.5	569.2	568.1
140°	582.9	586.2	587.9	590.1	589.0
142.5°	603.3	606.6	608.2	609.9	608.2
145°	622.0	625.8	626.9	628.0	628.0
147.5°	640.1	642.8	643.9	645.0	642.3
150°	656.6	658.2	659.3	660.4	658.8
152.5°	671.4	672.0	672.5	674.7	672.0
155°	685.1	684.0	684.6	687.3	684.0
157.5°	696.1	696.1	695.6	698.9	694.5
160°	706.0	705.5	704.9	708.2	704.4
162.5°	715.4	713.7	713.2	717.0	713.7
165°	722.5	720.9	720.3	724.7	720.9
167.5°	728.5	726.3	726.3	730.7	726.3
170°	733.5	731.3	731.3	735.7	731.3
172.5°	736.8	734.0	734.6	739.0	734.0
175°	739.5	736.8	737.3	741.2	736.8
177.5°	740.6	737.9	738.4	742.8	737.3
180°	739.5	739.5	739.5	739.5	739.5

(END OF REPORT)