

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009943

Luminaire Tested: S122RDIP-B290D925UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009943
REPORT IS A COMBINATION OF REPORTS P988211 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D925UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4564.0 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009943

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009943

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	26	26	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	22	22	16
3	76	68	61	55	67	60	54	50	46	42	39	33	31	29	22	20	19	19	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17	17	17	12
5	64	53	46	40	57	47	41	36	37	32	29	27	24	22	17	16	15	15	15	11
6	59	48	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	13	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	11	11	8
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10	10	10	8
9	47	35	28	23	41	32	26	21	25	20	17	18	15	13	12	11	9	9	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7688	7688	7688
5°	7701	7315	7261
10°	7625	6937	6709
15°	7521	6492	6080
20°	7382	5987	5422
25°	7241	5467	4820
30°	7049	4961	4163
35°	6862	4450	3598
40°	6673	3950	3016
45°	6452	3432	2509
50°	6222	2934	2043
55°	5985	2435	1621
60°	5708	1947	1226
65°	5393	1485	997
70°	5006	1077	793
75°	4526	822	607
80°	3824	556	406
85°	2670	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6452 cd/sqm

TEST NUMBER: P1009943

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.0
10°-20°	125.0	2.7
20°-30°	175.5	3.8
30°-40°	191.3	4.2
40°-50°	175.8	3.9
50°-60°	138.0	3.0
60°-70°	89.9	2.0
70°-80°	46.3	1.0
80°-90°	15.1	0.3
90°-100°	207.1	4.5
100°-110°	700.1	15.3
110°-120°	735.9	16.1
120°-130°	605.2	13.3
130°-140°	486.3	10.7
140°-150°	367.4	8.0
150°-160°	258.3	5.7
160°-170°	152.1	3.3
170°-180°	49.5	1.1
0°-30°	346.0	7.6
0°-40°	537.2	11.8
0°-60°	851.1	18.6
0°-90°	1002.2	22.0
90°-120°	1643.2	36.0
90°-150°	3102.0	68.0
90°-180°	3562.0	78.0
0°-180°	4564.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	486	484	478	482	480	46
15°	462	457	442	434	430	130
25°	419	405	376	358	352	193
35°	361	339	300	272	263	226
45°	295	266	220	189	178	228
55°	225	190	143	116	108	201
65°	152	116	76	62	60	150
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	13	33	32	32	3
95°	34	84	385	145	112	36
105°	120	181	728	1301	1107	127
115°	211	267	609	1257	1457	209
125°	295	349	586	1018	1182	262
135°	346	413	579	856	980	267
145°	395	454	576	715	782	248
155°	449	485	559	632	657	207
165°	489	504	535	568	577	138
175°	510	510	515	521	520	48
180°	511	511	511	511	511	

TEST NUMBER: P1009943

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	485.7	485.7	485.7	485.7	485.7
2.5°	487.9	485.7	480.9	485.3	484.4
5°	485.7	483.5	477.8	481.8	480.5
7.5°	481.8	479.2	473.0	474.8	472.6
10°	476.5	473.4	464.6	463.3	460.7
12.5°	469.9	466.0	454.1	451.5	446.6
15°	462.0	457.2	442.2	433.9	429.5
17.5°	452.8	445.7	427.3	417.6	410.6
20°	442.2	433.4	411.5	400.5	390.8
22.5°	430.8	420.7	395.2	380.2	373.7
25°	419.4	405.3	376.3	358.3	351.7
27.5°	405.7	390.8	358.7	338.0	327.9
30°	391.2	374.5	339.4	316.9	305.1
32.5°	377.2	356.9	320.9	294.5	283.5
35°	361.3	338.9	300.2	272.5	262.9
37.5°	346.0	321.8	280.9	250.6	239.6
40°	329.7	303.3	260.7	229.5	218.0
42.5°	313.0	284.9	240.5	207.9	196.9
45°	295.4	266.0	219.8	188.6	178.0
47.5°	278.7	247.5	200.0	168.8	159.1
50°	260.2	229.0	180.7	150.3	141.1
52.5°	242.2	209.2	162.2	133.2	124.8
55°	224.6	190.3	142.9	116.5	108.1
57.5°	206.6	171.4	125.7	101.1	94.1
60°	188.1	153.0	107.7	85.3	78.2
62.5°	170.1	135.0	92.3	71.2	67.7
65°	151.7	116.1	76.5	61.5	60.2
67.5°	134.1	98.5	61.5	54.1	52.8
70°	115.6	81.3	51.0	46.6	44.8
72.5°	98.0	65.5	42.6	39.1	38.2
75°	80.9	50.1	35.2	32.1	31.7
77.5°	63.7	35.6	27.7	25.9	25.1
80°	47.9	25.5	21.1	19.3	19.3
82.5°	33.4	17.1	14.5	13.6	13.6
85°	18.9	9.7	8.4	8.4	8.4
87.5°	7.0	3.5	3.5	3.1	3.1
90°	1.0	13.2	33.4	31.9	32.4
92.5°	14.7	46.7	151.3	69.8	59.9
95°	34.4	84.5	385.1	145.4	112.0
97.5°	51.1	111.5	627.8	291.8	187.6
100°	75.6	136.6	776.1	581.2	351.7
102.5°	98.2	159.2	781.0	982.4	685.7
105°	119.9	180.8	728.0	1301.2	1107.2
107.5°	143.4	202.4	678.9	1416.6	1391.1
110°	167.0	224.4	645.5	1398.0	1507.1

TEST NUMBER: P1009943

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.6	245.6	623.9	1334.6	1505.1
115°	211.2	266.8	609.1	1257.0	1457.0
117.5°	234.8	287.8	601.3	1182.8	1384.3
120°	256.4	308.4	594.4	1116.5	1314.5
122.5°	277.0	329.6	590.4	1065.0	1241.8
125°	294.7	348.8	585.5	1018.3	1181.9
127.5°	309.5	367.0	582.6	978.5	1125.9
130°	322.2	383.2	580.6	938.2	1079.7
132.5°	334.0	398.8	579.6	896.4	1031.6
135°	345.8	412.6	578.7	855.7	979.5
137.5°	356.6	424.4	578.7	814.4	929.4
140°	369.4	435.2	577.7	778.1	877.3
142.5°	382.2	444.1	577.7	743.2	825.3
145°	394.9	453.9	575.7	714.8	782.0
147.5°	408.7	461.8	572.8	689.7	743.7
150°	422.5	469.6	569.8	668.0	710.3
152.5°	436.2	477.4	564.9	649.9	681.8
155°	449.0	484.8	559.0	632.2	657.3
157.5°	459.8	490.7	553.1	615.5	635.6
160°	470.6	496.6	547.2	598.8	615.0
162.5°	481.4	501.0	542.3	583.0	595.4
165°	489.3	504.0	535.4	567.8	576.7
167.5°	496.1	507.0	529.5	554.1	559.0
170°	503.0	508.4	524.6	541.3	543.3
172.5°	506.9	509.9	518.7	530.0	530.5
175°	509.9	510.4	514.8	521.2	519.7
177.5°	511.9	510.9	510.9	514.8	511.9
180°	510.9	510.9	510.9	510.9	510.9

(END OF REPORT)