

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010463

Luminaire Tested: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010463
REPORT IS A COMBINATION OF REPORTS P989277 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7028.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010463

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010463

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	97	92	88	84	90	85	82	78	73	70	67	61	59	57	50	48	47
2	88	80	73	68	81	74	68	63	63	59	55	53	49	47	43	41	39
3	80	70	62	56	74	65	58	52	55	50	46	46	42	39	38	35	33
4	73	62	53	47	67	57	50	44	49	43	39	41	37	33	34	30	28
5	67	55	46	40	62	51	43	38	44	38	33	37	32	28	30	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	24	21
7	57	44	36	30	52	41	34	29	35	30	25	30	25	22	25	21	19
8	53	40	32	27	49	37	30	25	32	26	22	27	23	19	23	19	17
9	49	37	29	24	45	34	27	22	30	24	20	25	21	17	21	18	15
10	46	34	26	21	42	31	25	20	27	22	18	23	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12888	12476	12466
10°	12768	12138	12046
15°	12598	11764	11599
20°	12358	11349	11120
25°	12064	10880	10624
30°	11761	10457	10127
35°	11423	10011	9720
40°	11100	9605	9292
45°	10740	9211	8939
50°	10386	8821	8555
55°	9993	8421	8203
60°	9609	8011	7840
65°	9213	7575	7418
70°	8620	7085	6983
75°	7867	6528	6532
80°	6993	5962	6019
85°	6119	5505	5650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10740 cd/sqm

TEST NUMBER: P1010463

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.3	1.6
10°-20°	322.9	4.6
20°-30°	482.9	6.9
30°-40°	576.5	8.2
40°-50°	603.2	8.6
50°-60°	566.1	8.1
60°-70°	472.8	6.7
70°-80°	338.1	4.8
80°-90°	203.1	2.9
90°-100°	161.3	2.3
100°-110°	261.4	3.7
110°-120°	475.0	6.8
120°-130°	559.6	8.0
130°-140°	575.9	8.2
140°-150°	527.0	7.5
150°-160°	422.4	6.0
160°-170°	272.6	3.9
170°-180°	93.9	1.3
0°-30°	919.1	13.1
0°-40°	1495.6	21.3
0°-60°	2664.9	37.9
0°-90°	3679.0	52.3
90°-120°	897.7	12.8
90°-150°	2560.1	36.4
90°-180°	3349.0	47.7
0°-180°	7028.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1194	1194	1194	1194	1194	
5°	1195	1193	1185	1195	1194	113
15°	1138	1142	1141	1154	1152	321
25°	1028	1041	1044	1061	1061	474
35°	884	905	922	942	947	553
45°	723	754	787	812	822	558
55°	552	594	641	676	687	494
65°	381	432	489	528	541	377
75°	207	268	333	376	392	221
85°	64	129	198	242	255	66
90°	18	89	165	212	226	15
95°	59	80	152	197	210	65
105°	229	268	258	165	178	243
115°	417	437	490	529	542	412
125°	582	588	629	658	668	521
135°	723	726	743	769	773	557
145°	832	836	838	850	855	521
155°	916	914	915	919	914	422
165°	966	963	963	968	963	273
175°	988	985	985	990	985	94
180°	988	988	988	988	988	

TEST NUMBER: P1010463

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1194.1	1194.1	1194.1	1194.1	1194.1
2.5°	1200.6	1196.7	1186.3	1196.7	1195.4
5°	1195.4	1192.8	1185.0	1195.4	1194.1
7.5°	1186.3	1186.3	1178.5	1191.5	1190.2
10°	1173.3	1175.9	1169.4	1182.4	1179.8
12.5°	1157.6	1161.5	1157.6	1169.4	1166.8
15°	1138.1	1142.0	1140.7	1153.7	1152.4
17.5°	1114.7	1122.5	1121.2	1132.9	1130.3
20°	1088.7	1096.5	1099.1	1110.8	1112.1
22.5°	1061.4	1069.2	1073.1	1088.7	1087.4
25°	1027.6	1040.6	1044.5	1061.4	1061.4
27.5°	995.1	1009.4	1017.2	1031.5	1032.8
30°	959.9	976.8	987.3	1002.9	1002.9
32.5°	920.9	940.4	954.7	971.6	975.5
35°	884.5	905.3	922.2	941.7	946.9
37.5°	845.5	868.9	888.4	910.5	914.4
40°	806.5	829.9	855.9	878.0	883.2
42.5°	763.5	793.4	820.8	845.5	853.3
45°	723.2	754.4	786.9	811.7	822.1
47.5°	680.3	715.4	751.8	779.1	786.9
50°	638.7	675.1	715.4	745.3	754.4
52.5°	594.4	633.5	679.0	710.2	721.9
55°	551.5	594.4	641.3	676.4	686.8
57.5°	509.9	554.1	604.8	640.0	651.7
60°	465.7	512.5	565.8	602.2	616.5
62.5°	424.0	472.2	529.4	565.8	578.8
65°	381.1	431.8	489.1	528.1	541.1
67.5°	338.2	391.5	448.8	491.7	502.1
70°	292.7	348.6	411.0	452.7	465.7
72.5°	251.0	307.0	372.0	414.9	427.9
75°	206.8	267.9	333.0	375.9	391.5
77.5°	169.1	230.2	295.3	340.8	352.5
80°	128.8	192.5	260.1	304.4	317.4
82.5°	93.7	158.7	227.6	271.9	284.9
85°	63.7	128.8	197.7	241.9	254.9
87.5°	39.0	104.1	170.4	214.6	227.6
90°	17.6	88.7	164.6	211.8	226.2
92.5°	32.5	84.0	155.7	203.7	216.2
95°	59.1	79.7	151.6	197.0	210.0
97.5°	94.5	120.7	144.5	189.4	203.1
100°	135.8	192.1	137.4	181.0	194.7
102.5°	183.0	228.9	159.7	171.9	186.4
105°	229.2	268.5	258.4	164.8	178.0
107.5°	277.1	311.0	375.4	297.5	213.0
110°	325.0	354.3	414.4	424.0	329.4



TEST NUMBER: P1010463

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.0	395.3	452.8	492.0	502.3
115°	417.0	437.0	490.4	529.0	542.4
117.5°	462.5	478.0	525.9	563.1	574.2
120°	503.0	516.1	561.3	597.0	606.2
122.5°	545.6	553.4	596.6	628.9	638.7
125°	582.5	588.4	629.0	657.8	668.4
127.5°	620.7	625.3	661.4	689.6	697.3
130°	655.9	660.5	689.4	717.1	723.4
132.5°	688.4	694.3	716.0	742.3	749.2
135°	722.9	726.0	743.3	768.9	773.2
137.5°	752.3	756.9	767.4	791.9	796.9
140°	780.4	784.8	790.9	813.3	818.3
142.5°	807.5	810.6	812.8	831.9	836.2
145°	832.5	836.3	837.8	849.7	854.9
147.5°	855.4	859.1	860.6	865.9	867.5
150°	877.5	879.7	881.1	882.6	883.0
152.5°	897.3	898.0	898.8	901.7	898.0
155°	915.6	914.2	914.9	918.6	914.2
157.5°	930.3	930.3	929.6	934.0	928.1
160°	943.5	942.8	942.1	946.5	941.3
162.5°	956.0	953.8	953.1	958.2	953.8
165°	965.6	963.4	962.6	968.5	963.4
167.5°	973.7	970.7	970.7	976.6	970.7
170°	980.3	977.3	977.3	983.2	977.3
172.5°	984.7	981.0	981.7	987.6	981.0
175°	988.3	984.7	985.4	990.5	984.7
177.5°	989.8	986.1	986.9	992.7	985.4
180°	988.3	988.3	988.3	988.3	988.3

(END OF REPORT)