

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009948

Luminaire Tested: S122RDIP-B290D925UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009948
REPORT IS A COMBINATION OF REPORTS P988216 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D925UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4117.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009948

CATALOG NUMBER: S122RDIP-B290D925UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009948

CATALOG NUMBER: S122RDIP-B290D925UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24		
1	92	88	84	81	82	78	75	73	60	58	57	44	42	41	28	28	27	20		
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17		
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20	15		
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	17	13		
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	18	17	15	11		
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	14	10		
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12	9		
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8		
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7		
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7435	7435	7435
5°	7447	7073	7021
10°	7374	6709	6488
15°	7272	6278	5879
20°	7138	5789	5243
25°	7001	5287	4661
30°	6816	4798	4025
35°	6636	4303	3479
40°	6452	3820	2916
45°	6238	3318	2427
50°	6017	2836	1975
55°	5788	2354	1569
60°	5520	1882	1187
65°	5212	1436	964
70°	4842	1041	768
75°	4375	794	586
80°	3696	538	393
85°	2585	247	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6238 cd/sqm

TEST NUMBER: P1009948

CATALOG NUMBER: S122RDIP-B290D925UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.1
10°-20°	120.8	2.9
20°-30°	169.7	4.1
30°-40°	184.9	4.5
40°-50°	170.0	4.1
50°-60°	133.5	3.2
60°-70°	86.9	2.1
70°-80°	44.7	1.1
80°-90°	14.6	0.4
90°-100°	69.6	1.7
100°-110°	221.4	5.4
110°-120°	378.9	9.2
120°-130°	498.3	12.1
130°-140°	559.3	13.6
140°-150°	548.5	13.3
150°-160°	460.1	11.2
160°-170°	305.1	7.4
170°-180°	106.6	2.6
0°-30°	334.5	8.1
0°-40°	519.5	12.6
0°-60°	823.0	20.0
0°-90°	969.2	23.5
90°-120°	669.9	16.3
90°-150°	2276.0	55.3
90°-180°	3148.0	76.5
0°-180°	4117.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	470	470	470	470	470	
5°	470	468	462	466	465	45
15°	447	442	428	420	415	126
25°	406	392	364	346	340	186
35°	349	328	290	264	254	219
45°	286	257	212	182	172	221
55°	217	184	138	113	105	194
65°	147	112	74	60	58	145
75°	78	48	34	31	31	83
85°	18	9	8	8	8	21
90°	1	12	33	31	32	4
95°	49	59	61	61	59	55
105°	204	207	209	211	211	216
115°	380	386	384	383	380	376
125°	553	562	559	556	555	494
135°	715	726	728	727	724	553
145°	868	875	881	882	878	543
155°	993	996	999	1003	1000	457
165°	1080	1079	1079	1086	1081	305
175°	1124	1121	1119	1126	1120	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P1009948

CATALOG NUMBER: S122RDIP-B290D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	469.7	469.7	469.7	469.7	469.7
2.5°	471.8	469.7	465.0	469.3	468.4
5°	469.7	467.6	462.0	465.9	464.6
7.5°	465.9	463.3	457.4	459.1	456.9
10°	460.8	457.8	449.3	448.0	445.5
12.5°	454.4	450.6	439.1	436.5	431.9
15°	446.7	442.1	427.6	419.5	415.3
17.5°	437.8	431.0	413.2	403.8	397.0
20°	427.6	419.1	397.9	387.2	377.9
22.5°	416.6	406.8	382.1	367.7	361.3
25°	405.5	391.9	363.9	346.4	340.1
27.5°	392.3	377.9	346.9	326.9	317.1
30°	378.3	362.2	328.2	306.5	295.0
32.5°	364.7	345.2	310.3	284.8	274.2
35°	349.4	327.7	290.3	263.5	254.2
37.5°	334.5	311.2	271.6	242.3	231.7
40°	318.8	293.3	252.1	221.9	210.8
42.5°	302.6	275.4	232.5	201.1	190.4
45°	285.6	257.2	212.5	182.4	172.2
47.5°	269.5	239.3	193.4	163.2	153.9
50°	251.6	221.5	174.7	145.4	136.4
52.5°	234.2	202.3	156.9	128.8	120.7
55°	217.2	184.1	138.1	112.6	104.6
57.5°	199.8	165.8	121.6	97.8	91.0
60°	181.9	147.9	104.1	82.5	75.7
62.5°	164.5	130.5	89.3	68.9	65.5
65°	146.6	112.2	74.0	59.5	58.2
67.5°	129.6	95.2	59.5	52.3	51.0
70°	111.8	78.6	49.3	45.1	43.4
72.5°	94.8	63.3	41.2	37.8	37.0
75°	78.2	48.5	34.0	31.0	30.6
77.5°	61.6	34.4	26.8	25.1	24.2
80°	46.3	24.7	20.4	18.7	18.7
82.5°	32.3	16.6	14.0	13.2	13.2
85°	18.3	9.4	8.1	8.1	8.1
87.5°	6.8	3.4	3.4	3.0	3.0
90°	1.0	12.4	33.3	31.4	32.3
92.5°	20.9	28.5	29.5	30.4	30.4
95°	49.4	58.9	60.8	60.8	58.9
97.5°	82.7	91.2	95.0	95.0	95.0
100°	120.7	128.3	131.1	131.1	130.2
102.5°	160.6	166.3	170.1	171.0	170.1
105°	204.3	207.1	209.0	210.9	210.9
107.5°	248.0	251.8	251.8	252.7	248.0
110°	289.8	295.5	295.5	295.5	292.6

TEST NUMBER: P1009948

CATALOG NUMBER: S122RDIP-B290D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.4	341.1	340.1	337.3	335.4
115°	380.0	385.8	383.9	382.9	380.0
117.5°	424.7	432.3	427.6	424.7	421.9
120°	469.4	477.0	469.4	469.4	466.5
122.5°	510.2	519.7	515.0	512.1	510.2
125°	553.0	561.5	558.7	555.8	554.9
127.5°	594.8	605.2	601.4	597.6	594.8
130°	633.7	646.1	644.2	642.3	638.5
132.5°	677.4	686.9	687.9	683.1	680.3
135°	715.4	725.9	727.8	726.8	724.0
137.5°	757.2	765.8	767.7	766.8	762.9
140°	794.3	802.9	807.6	807.6	803.8
142.5°	832.3	840.9	843.7	844.7	840.9
145°	868.4	875.1	880.8	881.7	877.9
147.5°	900.7	909.3	913.1	915.0	911.2
150°	934.0	939.7	943.5	946.3	943.5
152.5°	963.4	969.1	973.9	977.7	973.9
155°	992.9	995.7	998.6	1003.3	1000.5
157.5°	1018.5	1020.4	1022.3	1029.0	1024.2
160°	1041.3	1043.2	1044.2	1049.9	1046.1
162.5°	1062.2	1062.2	1063.2	1069.8	1065.1
165°	1080.3	1079.3	1079.3	1086.0	1081.2
167.5°	1096.4	1093.6	1093.6	1100.2	1095.5
170°	1108.8	1105.9	1105.0	1111.6	1105.9
172.5°	1117.3	1114.5	1113.5	1120.2	1114.5
175°	1124.0	1121.1	1119.2	1125.9	1120.2
177.5°	1127.8	1124.9	1123.0	1128.7	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9

(END OF REPORT)