

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010466

Luminaire Tested: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010466
REPORT IS A COMBINATION OF REPORTS P989280 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7262.0 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010466

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010466

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	62	55	54	52
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	43	43	40	38
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	38	33	55	44	36	31	38	32	28	33	29	25	29	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	23	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	21	18
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1010466

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.1
10°-20°	420.7	5.8
20°-30°	621.3	8.6
30°-40°	725.6	10.0
40°-50°	729.5	10.0
50°-60°	640.8	8.8
60°-70°	477.3	6.6
70°-80°	271.6	3.7
80°-90°	79.3	1.1
90°-100°	36.4	0.5
100°-110°	176.0	2.4
110°-120°	431.3	5.9
120°-130°	547.5	7.5
130°-140°	584.9	8.1
140°-150°	546.9	7.5
150°-160°	441.1	6.1
160°-170°	284.7	3.9
170°-180°	98.1	1.4
0°-30°	1191.0	16.4
0°-40°	1916.6	26.4
0°-60°	3286.9	45.3
0°-90°	4115.1	56.7
90°-120°	643.7	8.9
90°-150°	2323.0	32.0
90°-180°	3147.0	43.3
0°-180°	7262.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	1	8	18	22	23	7
95°	47	15	24	29	29	56
105°	228	237	168	32	34	242
115°	429	433	440	448	451	423
125°	604	610	614	615	617	540
135°	752	757	760	762	760	579
145°	868	874	875	877	877	544
155°	956	955	956	959	955	441
165°	1008	1006	1005	1012	1006	285
175°	1032	1028	1029	1035	1028	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1010466

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	0.8	8.4	18.4	21.5	23.0
92.5°	17.6	13.0	19.9	25.3	26.1
95°	46.8	15.3	23.8	29.1	29.1
97.5°	85.1	63.7	24.5	30.7	31.4
100°	129.6	144.9	25.3	31.4	32.2
102.5°	180.2	190.2	56.8	31.4	33.0
105°	228.5	237.0	168.0	32.2	33.7
107.5°	279.9	286.8	298.3	180.2	79.8
110°	331.3	337.4	345.9	320.6	210.9



TEST NUMBER: P1010466

CATALOG NUMBER: S123DIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.8	394.2	401.1	399.6
115°	428.7	433.3	440.2	447.9	450.9
117.5°	476.3	481.6	485.5	491.6	492.4
120°	520.0	526.9	529.2	535.3	535.3
122.5°	564.4	569.8	572.9	576.7	577.5
125°	604.3	610.5	613.5	615.1	616.6
127.5°	644.2	650.3	654.2	656.5	654.9
130°	681.0	687.2	690.2	693.3	691.8
132.5°	716.3	722.4	724.7	727.8	725.5
135°	752.3	756.9	760.0	762.3	760.0
137.5°	783.0	789.2	790.7	794.5	793.0
140°	813.7	818.3	820.6	823.7	822.1
142.5°	842.1	846.7	849.0	851.3	849.0
145°	868.1	873.5	875.0	876.6	876.6
147.5°	893.5	897.3	898.8	900.4	896.5
150°	916.5	918.8	920.3	921.8	919.5
152.5°	937.2	937.9	938.7	941.8	937.9
155°	956.3	954.8	955.6	959.4	954.8
157.5°	971.7	971.7	970.9	975.5	969.4
160°	985.5	984.7	983.9	988.5	983.2
162.5°	998.5	996.2	995.5	1000.8	996.2
165°	1008.5	1006.2	1005.4	1011.6	1006.2
167.5°	1016.9	1013.9	1013.9	1020.0	1013.9
170°	1023.8	1020.8	1020.8	1026.9	1020.8
172.5°	1028.4	1024.6	1025.4	1031.5	1024.6
175°	1032.3	1028.4	1029.2	1034.6	1028.4
177.5°	1033.8	1030.0	1030.7	1036.9	1029.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)