

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009950

Luminaire Tested: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009950
REPORT IS A COMBINATION OF REPORTS P988218 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D1080UB27-4F0-XX-W2A-A
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6104.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17
7	57	45	38	32	51	41	34	30	33	28	25	26	23	20	19	17	16
8	52	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	16	14	13
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16800	16800	16800	16800
5°	16838	17843	16897	14255
10°	16653	18861	16771	11771
15°	16292	18866	16568	8843
20°	15857	15595	16202	7295
25°	15331	9745	15661	6206
30°	14658	6240	15056	5343
35°	13839	4794	14287	4573
40°	12927	4030	13479	4000
45°	11951	3431	12451	3357
50°	10952	2914	11464	2904
55°	9846	2533	10376	2500
60°	8864	1932	9331	1908
65°	7945	1454	8415	1650
70°	6929	1161	7475	1344
75°	5857	890	6394	1016
80°	4655	605	5006	666
85°	3235	313	3546	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15368 cd/sqm

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	1.6
10°-20°	281.0	4.6
20°-30°	361.6	5.9
30°-40°	343.1	5.6
40°-50°	294.0	4.8
50°-60°	223.9	3.7
60°-70°	141.2	2.3
70°-80°	70.5	1.2
80°-90°	20.7	0.3
90°-100°	48.0	0.8
100°-110°	178.9	2.9
110°-120°	474.6	7.8
120°-130°	787.1	12.9
130°-140°	836.1	13.7
140°-150°	777.0	12.7
150°-160°	624.7	10.2
160°-170°	402.5	6.6
170°-180°	138.5	2.3
0°-30°	743.3	12.2
0°-40°	1086.3	17.8
0°-60°	1604.3	26.3
0°-90°	1836.6	30.1
90°-120°	701.5	11.5
90°-150°	3101.6	50.8
90°-180°	4267.0	69.9
0°-180°	6104.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1061	1061	1061	1061	1061	
5°	1062	1181	1066	943	1062	101
15°	1001	1333	1018	625	1001	282
25°	888	711	907	453	888	408
35°	729	350	752	334	729	456
45°	547	243	570	238	547	422
55°	370	169	389	167	370	333
65°	224	88	237	100	224	222
75°	105	46	114	53	105	113
85°	23	13	25	14	23	26
90°	1	28	1	28	1	5
95°	68	45	68	45	68	81
105°	320	80	320	80	320	342
115°	606	86	606	86	606	596
125°	856	901	856	901	856	764
135°	1060	1094	1060	1094	1060	819
145°	1229	1248	1229	1248	1229	769
155°	1354	1354	1354	1354	1354	624
165°	1426	1423	1426	1423	1426	403
175°	1459	1450	1459	1450	1459	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.9	1072.3	1074.5	1077.5	1084.1	1088.6	1095.2	1096.7	1095.9	1098.9	1090.8
5°	1062.0	1071.6	1080.4	1087.8	1099.6	1107.0	1115.1	1124.7	1126.9	1138.0	1131.3
7.5°	1053.9	1067.9	1080.4	1095.2	1112.9	1122.5	1135.0	1149.8	1156.4	1169.7	1173.4
10°	1040.6	1060.5	1081.9	1097.4	1121.7	1138.7	1150.5	1174.1	1189.6	1209.5	1206.6
12.5°	1019.2	1045.0	1073.8	1099.6	1131.3	1142.4	1164.5	1188.9	1208.8	1227.2	1243.4
15°	1000.8	1030.3	1062.0	1093.7	1129.9	1150.5	1172.6	1204.3	1225.7	1258.2	1272.2
17.5°	975.7	1013.3	1050.9	1086.3	1129.1	1152.7	1180.0	1211.0	1242.7	1273.7	1284.7
20°	949.9	990.5	1031.0	1079.0	1127.6	1150.5	1178.5	1216.9	1247.9	1272.2	1272.2
22.5°	918.9	968.3	1014.8	1060.5	1113.6	1146.8	1175.6	1220.6	1242.7	1247.9	1227.9
25°	888.0	937.4	988.3	1045.0	1105.5	1135.0	1167.5	1209.5	1216.9	1196.2	1144.6
27.5°	851.1	906.4	963.9	1025.1	1088.6	1125.4	1154.9	1183.0	1168.9	1113.6	1033.2
30°	813.5	873.2	938.1	996.4	1073.1	1107.0	1132.1	1140.2	1095.9	1006.0	902.0
32.5°	774.4	832.6	901.2	971.3	1048.7	1081.2	1097.4	1076.0	994.9	881.3	754.5
35°	728.7	794.3	865.8	938.8	1015.5	1039.9	1049.5	997.1	893.1	746.4	620.2
37.5°	687.4	753.0	829.7	904.2	978.7	991.9	982.4	900.5	768.5	623.2	500.0
40°	638.7	708.7	784.0	867.3	928.5	932.2	908.6	802.4	638.7	502.2	426.3
42.5°	593.7	664.5	739.7	824.5	871.0	858.5	826.7	687.4	533.2	432.9	371.7
45°	547.2	614.3	695.5	770.7	803.9	774.4	726.4	578.2	447.7	372.4	325.2
47.5°	502.2	564.9	645.3	717.6	723.5	690.3	633.5	484.5	387.9	327.5	289.1
50°	458.0	520.7	595.9	655.6	649.7	604.0	539.9	421.1	337.0	289.1	257.4
52.5°	413.7	470.5	543.5	590.7	565.7	521.4	458.0	357.0	294.3	252.2	227.9
55°	369.5	422.6	485.3	524.4	484.5	433.7	388.7	306.1	255.2	221.3	202.8
57.5°	332.6	374.7	432.2	455.8	407.8	368.0	328.9	263.3	221.3	196.9	175.5
60°	292.1	330.4	377.6	391.6	342.2	309.8	276.6	222.7	189.5	168.2	154.1
62.5°	257.4	289.1	325.2	325.2	281.7	257.4	232.3	186.6	159.3	142.3	135.7
65°	223.5	246.3	272.1	269.2	232.3	210.9	191.0	154.1	133.5	121.7	115.1
67.5°	190.3	208.0	224.9	214.6	188.1	169.6	151.2	124.6	110.6	102.5	93.7
70°	160.0	174.1	182.9	173.3	146.8	131.3	118.0	100.3	89.2	78.9	73.8
72.5°	134.2	140.1	143.1	131.3	109.2	100.3	90.7	78.2	68.6	63.4	62.0
75°	104.7	109.9	107.7	98.8	80.4	73.8	66.4	57.5	55.3	52.4	50.9
77.5°	81.9	81.9	78.2	70.1	57.5	52.4	49.4	45.0	42.8	42.0	40.6
80°	58.3	57.5	55.3	46.5	39.1	36.1	36.1	33.2	32.5	31.0	31.0
82.5°	38.4	38.4	35.4	28.0	25.8	25.1	24.3	22.9	22.9	22.1	22.1
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.0	13.3	14.0	13.3	13.3
87.5°	10.3	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	1.1	3.7	6.2	8.8	11.3	12.6	13.5	15.4	17.3	19.2	21.1
92.5°	26.3	25.4	24.4	23.5	22.6	22.1	22.5	23.2	23.9	24.6	25.3
95°	68.5	60.8	53.0	45.3	37.6	33.7	34.5	36.2	37.8	39.5	41.1
97.5°	123.2	104.0	84.8	65.7	46.5	36.9	38.8	42.5	46.2	50.0	53.7
100°	186.4	154.3	122.3	90.2	58.1	42.1	44.1	48.1	52.0	56.0	60.0
102.5°	255.9	255.4	255.0	254.5	254.0	253.8	232.5	189.9	147.3	104.7	62.1
105°	320.2	327.2	334.2	341.3	348.3	351.8	319.9	256.0	192.1	128.2	64.3
107.5°	395.0	400.8	406.7	412.5	418.4	421.3	381.9	303.0	224.1	145.3	66.4
110°	466.6	471.5	476.4	481.3	486.2	488.7	454.9	387.2	319.6	251.9	184.3

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	534.0	538.2	542.4	546.7	550.9	553.0	551.0	547.0	543.1	539.1	535.1
115°	605.6	609.6	613.6	617.5	621.5	623.5	626.4	632.3	638.2	644.0	649.9
117.5°	667.8	672.5	677.2	681.9	686.6	688.9	690.9	694.9	698.8	702.8	706.8
120°	737.3	740.8	744.3	747.8	751.3	753.1	755.2	759.4	763.7	767.9	772.1
122.5°	796.3	800.0	803.8	807.5	811.2	813.1	815.4	820.1	824.8	829.5	834.2
125°	856.3	859.3	862.4	865.4	868.5	870.0	872.2	876.7	881.1	885.6	890.0
127.5°	911.1	914.4	917.6	920.9	924.2	925.8	927.6	931.1	934.6	938.1	941.6
130°	962.7	966.5	970.2	974.0	977.7	979.6	980.9	983.4	986.0	988.5	991.1
132.5°	1015.4	1018.4	1021.5	1024.5	1027.6	1029.1	1030.4	1032.9	1035.5	1038.0	1040.6
135°	1059.6	1063.4	1067.1	1070.9	1074.6	1076.5	1077.5	1079.6	1081.7	1083.8	1085.9
137.5°	1106.0	1108.8	1111.6	1114.4	1117.2	1118.6	1119.8	1122.1	1124.4	1126.8	1129.1
140°	1151.2	1153.1	1155.0	1156.9	1158.8	1159.7	1161.0	1163.6	1166.1	1168.7	1171.3
142.5°	1189.2	1190.8	1192.4	1194.1	1195.7	1196.5	1198.0	1201.1	1204.1	1207.2	1210.2
145°	1229.2	1229.0	1228.7	1228.5	1228.2	1228.1	1230.1	1234.1	1238.0	1242.0	1246.0
147.5°	1263.9	1263.2	1262.5	1261.8	1261.1	1260.8	1262.8	1266.8	1270.7	1274.7	1278.7
150°	1297.7	1296.1	1294.4	1292.8	1291.1	1290.3	1292.2	1295.9	1299.6	1303.4	1307.1
152.5°	1326.1	1324.2	1322.4	1320.5	1318.6	1317.7	1319.5	1323.0	1326.5	1330.0	1333.5
155°	1353.5	1351.4	1349.3	1347.2	1345.1	1344.0	1345.4	1348.2	1351.0	1353.8	1356.6
157.5°	1375.6	1373.7	1371.9	1370.0	1368.1	1367.2	1368.2	1370.3	1372.4	1374.5	1376.6
160°	1394.6	1393.2	1391.8	1390.3	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6
162.5°	1411.4	1410.0	1408.6	1407.2	1405.8	1405.1	1405.7	1406.9	1408.0	1409.2	1410.4
165°	1426.2	1424.8	1423.4	1421.9	1420.5	1419.8	1420.2	1420.9	1421.6	1422.3	1423.0
167.5°	1437.7	1436.3	1434.9	1433.5	1432.1	1431.4	1431.8	1432.5	1433.2	1433.9	1434.6
170°	1447.2	1445.8	1444.4	1443.0	1441.6	1440.9	1441.1	1441.6	1442.1	1442.5	1443.0
172.5°	1453.5	1452.1	1450.7	1449.3	1447.9	1447.2	1447.4	1447.9	1448.4	1448.8	1449.3
175°	1458.8	1457.2	1455.5	1453.9	1452.2	1451.4	1451.6	1452.1	1452.6	1453.0	1453.5
177.5°	1460.9	1459.3	1457.6	1456.0	1454.3	1453.5	1453.6	1453.9	1454.1	1454.4	1454.6
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1098.9	1100.4	1102.6	1112.9	1114.4	1117.3	1115.8	1115.8	1116.6	1115.1	1115.8
5°	1146.1	1148.3	1159.4	1171.9	1174.8	1171.9	1175.6	1180.7	1180.7	1180.7	1179.3
7.5°	1190.3	1198.4	1211.0	1229.4	1233.1	1236.8	1243.4	1239.0	1240.5	1247.1	1244.9
10°	1233.1	1244.9	1258.9	1274.4	1282.5	1287.7	1290.6	1297.3	1312.8	1295.1	1301.7
12.5°	1273.7	1290.6	1305.4	1322.3	1328.2	1334.9	1337.1	1343.0	1343.0	1342.3	1347.4
15°	1300.2	1315.7	1329.0	1340.0	1341.5	1340.0	1338.6	1339.3	1341.5	1332.7	1337.8
17.5°	1306.1	1307.6	1312.0	1307.6	1308.3	1292.8	1284.0	1281.8	1261.1	1261.9	1278.8
20°	1277.4	1252.3	1245.6	1221.3	1206.6	1166.7	1165.3	1154.2	1110.7	1124.0	1121.0
22.5°	1198.4	1155.7	1098.9	1070.9	1056.8	1014.8	982.4	959.5	944.0	928.5	921.9
25°	1094.5	1025.1	944.7	889.4	881.3	842.2	782.5	754.5	721.3	711.0	728.7
27.5°	960.2	870.3	779.5	694.7	679.2	643.8	613.6	593.7	555.3	553.1	554.6
30°	778.1	687.4	611.4	556.1	517.7	501.5	481.6	466.8	451.4	457.3	458.7
32.5°	639.4	553.1	482.3	452.8	435.1	424.8	407.8	398.3	391.6	389.4	388.7
35°	508.1	450.6	418.9	390.1	379.8	372.4	359.9	355.5	349.6	350.3	350.3
37.5°	435.1	387.2	363.6	348.8	339.3	335.6	327.5	323.0	319.3	317.9	320.1
40°	375.4	342.2	327.5	314.2	306.1	304.6	300.2	295.0	290.6	291.3	293.5
42.5°	331.9	312.7	295.0	284.7	278.8	276.6	272.9	269.2	269.2	267.0	266.2
45°	297.2	281.7	267.0	257.4	253.7	250.8	246.3	245.6	242.6	243.4	244.1
47.5°	266.2	253.7	242.6	233.1	229.4	228.6	224.2	221.3	221.3	220.5	219.8
50°	238.2	225.7	216.1	210.9	205.8	204.3	203.6	202.8	201.3	201.3	202.1
52.5°	215.4	202.8	195.4	191.0	188.1	186.6	186.6	185.9	185.9	185.9	185.1
55°	190.3	180.0	174.1	172.6	171.1	170.4	169.6	168.2	167.4	168.9	167.4
57.5°	166.7	163.0	157.8	156.4	152.7	152.7	150.5	149.0	147.5	149.0	149.0
60°	148.2	143.1	140.1	135.7	132.8	129.8	126.1	125.4	123.9	123.2	122.4
62.5°	129.1	124.6	117.3	110.6	106.2	103.3	101.8	101.0	101.0	100.3	100.3
65°	107.7	97.4	93.7	91.5	90.7	90.0	88.5	87.8	88.5	87.8	88.5
67.5°	84.1	82.6	80.4	78.9	78.2	77.4	77.4	76.7	76.7	76.7	76.7
70°	73.0	69.3	68.6	67.1	67.1	66.4	66.4	66.4	66.4	65.6	67.1
72.5°	60.5	58.3	57.5	56.8	56.8	56.8	56.1	56.1	56.1	55.3	56.1
75°	49.4	48.7	47.2	47.2	46.5	47.2	46.5	46.5	45.7	46.5	46.5
77.5°	39.8	39.1	38.4	38.4	37.6	37.6	37.6	37.6	37.6	37.6	38.4
80°	30.2	29.5	28.8	29.5	28.8	29.5	28.8	28.8	29.5	28.8	28.8
82.5°	22.1	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.5	12.5	13.3	12.5	13.3	12.5	12.5	12.5	13.3	13.3
87.5°	5.9	6.6	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.6
90°	22.3	23.4	24.6	25.7	26.3	26.5	27.0	27.5	27.9	28.4	27.9
92.5°	25.8	26.2	26.7	27.2	27.4	27.5	27.7	28.0	28.2	28.4	28.2
95°	42.3	43.4	44.6	45.7	46.3	46.2	46.0	45.7	45.5	45.3	45.5
97.5°	54.4	55.1	55.8	56.5	56.9	57.0	57.2	57.5	57.7	57.9	57.7
100°	61.9	63.8	65.7	67.6	68.5	68.7	69.2	69.7	70.1	70.6	70.1
102.5°	64.7	67.3	69.8	72.4	73.7	74.1	74.8	75.5	76.2	76.9	76.2
105°	66.9	69.4	72.0	74.5	75.8	76.3	77.2	78.1	79.1	80.0	79.1
107.5°	69.0	71.5	74.1	76.6	77.9	78.4	79.3	80.3	81.2	82.2	81.2
110°	160.9	137.5	114.1	90.7	79.0	79.5	80.4	81.3	82.3	83.2	82.3

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	434.2	333.3	232.4	131.5	81.1	81.5	82.2	82.9	83.6	84.3	83.6
115°	541.5	433.1	324.8	216.4	162.2	153.8	136.9	120.1	103.2	86.4	103.2
117.5°	673.3	639.8	606.3	572.8	556.1	525.4	464.1	402.8	341.5	280.2	341.5
120°	774.9	777.7	780.5	783.3	784.7	768.9	737.3	705.7	674.1	642.5	674.1
122.5°	835.6	837.0	838.4	839.8	840.5	840.6	840.9	841.1	841.4	841.6	841.4
125°	891.6	893.3	894.9	896.6	897.4	897.8	898.5	899.2	899.9	900.6	899.9
127.5°	944.0	946.3	948.7	951.0	952.2	952.3	952.5	952.8	953.0	953.2	953.0
130°	993.7	996.3	998.8	1001.4	1002.7	1002.6	1002.4	1002.1	1001.9	1001.7	1001.9
132.5°	1042.7	1044.8	1046.9	1049.0	1050.1	1050.0	1049.8	1049.5	1049.3	1049.1	1049.3
135°	1088.3	1090.6	1093.0	1095.3	1096.5	1096.3	1095.8	1095.3	1094.9	1094.4	1094.9
137.5°	1131.5	1133.8	1136.2	1138.5	1139.7	1139.3	1138.6	1137.9	1137.2	1136.5	1137.2
140°	1173.4	1175.5	1177.6	1179.7	1180.7	1180.1	1179.0	1177.8	1176.7	1175.5	1176.7
142.5°	1212.1	1214.0	1215.9	1217.8	1218.7	1218.1	1216.9	1215.8	1214.6	1213.4	1214.6
145°	1247.6	1249.3	1250.9	1252.6	1253.4	1252.8	1251.6	1250.5	1249.3	1248.1	1249.3
147.5°	1279.9	1281.1	1282.2	1283.4	1284.0	1283.5	1282.6	1281.6	1280.7	1279.7	1280.7
150°	1308.5	1309.9	1311.4	1312.8	1313.5	1312.9	1311.7	1310.6	1309.4	1308.2	1309.4
152.5°	1334.9	1336.3	1337.7	1339.1	1339.8	1339.0	1337.3	1335.7	1334.0	1332.4	1334.0
155°	1358.0	1359.4	1360.9	1362.3	1363.0	1362.1	1360.2	1358.3	1356.4	1354.5	1356.4
157.5°	1378.2	1379.9	1381.5	1383.2	1384.0	1383.1	1381.2	1379.3	1377.5	1375.6	1377.5
160°	1396.0	1397.4	1398.8	1400.2	1400.9	1400.1	1398.4	1396.8	1395.1	1393.5	1395.1
162.5°	1412.0	1413.6	1415.3	1416.9	1417.7	1416.6	1414.5	1412.4	1410.3	1408.2	1410.3
165°	1424.6	1426.3	1427.9	1429.6	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1424.6
167.5°	1436.2	1437.9	1439.5	1441.2	1442.0	1440.9	1438.8	1436.7	1434.6	1432.5	1434.6
170°	1444.6	1446.3	1447.9	1449.6	1450.4	1449.3	1447.2	1445.1	1443.0	1440.9	1443.0
172.5°	1450.9	1452.6	1454.2	1455.9	1456.7	1455.6	1453.5	1451.4	1449.3	1447.2	1449.3
175°	1455.1	1456.8	1458.4	1460.1	1460.9	1459.7	1457.4	1455.1	1452.7	1450.4	1452.7
177.5°	1456.2	1457.9	1459.5	1461.2	1462.0	1460.9	1458.8	1456.7	1454.6	1452.5	1454.6
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1118.8	1113.6	1112.2	1113.6	1112.2	1112.9	1107.7	1088.6	1093.7	1085.6	1090.0
5°	1182.2	1177.8	1168.2	1166.7	1165.3	1163.8	1156.4	1139.4	1132.8	1121.7	1121.0
7.5°	1242.7	1242.7	1235.3	1230.2	1223.5	1218.4	1208.8	1183.7	1173.4	1160.1	1152.7
10°	1302.4	1283.3	1291.4	1286.2	1270.0	1267.0	1249.3	1234.6	1214.7	1201.4	1189.6
12.5°	1345.2	1339.3	1331.9	1327.5	1323.1	1313.5	1301.7	1264.1	1253.8	1227.2	1213.9
15°	1343.7	1340.0	1342.3	1342.3	1340.8	1338.6	1329.0	1301.7	1284.0	1258.2	1235.3
17.5°	1271.5	1281.0	1290.6	1297.3	1312.0	1318.7	1327.5	1311.3	1300.2	1278.1	1253.8
20°	1145.3	1168.9	1197.0	1202.9	1216.1	1255.2	1272.9	1286.9	1291.4	1284.0	1264.1
22.5°	969.8	989.7	1057.6	1056.1	1075.3	1121.7	1173.4	1215.4	1248.6	1267.0	1259.7
25°	759.6	787.7	823.8	851.1	913.8	983.1	1047.3	1114.4	1171.9	1222.8	1235.3
27.5°	574.5	611.4	640.2	676.3	708.0	789.9	872.5	977.2	1044.3	1140.9	1191.1
30°	464.6	481.6	510.4	527.3	542.8	605.5	699.2	802.4	920.4	1031.8	1118.1
32.5°	396.8	408.6	430.0	437.3	453.6	495.6	554.6	649.0	770.7	905.7	1019.2
35°	356.2	368.8	373.2	379.8	393.1	419.6	460.2	528.8	638.7	770.7	906.4
37.5°	321.6	328.2	340.7	345.2	349.6	369.5	396.8	444.7	517.7	626.1	776.6
40°	297.2	300.9	307.5	311.2	314.2	328.2	352.5	385.0	438.8	521.4	660.1
42.5°	271.4	275.8	280.3	284.7	288.4	299.4	314.2	345.2	381.3	444.0	544.3
45°	246.3	249.3	254.4	257.4	262.6	271.4	284.7	306.1	338.5	378.3	459.5
47.5°	223.5	227.2	229.4	233.1	236.7	246.3	258.9	272.9	299.4	338.5	397.5
50°	202.8	207.2	210.2	210.9	213.9	222.7	233.1	248.5	265.5	295.7	347.4
52.5°	188.1	188.8	191.0	194.0	193.2	198.4	208.0	219.8	237.5	261.8	299.4
55°	171.1	173.3	174.8	175.5	175.5	180.0	185.1	196.2	210.2	230.1	261.8
57.5°	149.7	151.9	156.4	157.8	160.0	162.3	164.5	171.8	183.6	202.8	228.6
60°	127.6	129.1	133.5	136.4	137.9	143.8	146.8	152.7	159.3	173.3	197.7
62.5°	102.5	104.0	106.2	109.2	112.1	121.0	128.3	134.2	139.4	149.0	168.9
65°	89.2	90.0	91.5	92.2	92.9	96.6	103.3	111.4	121.0	128.3	140.1
67.5°	77.4	78.2	78.9	80.4	81.1	81.9	84.8	87.0	96.6	106.9	115.8
70°	66.4	67.9	68.6	68.6	69.3	70.8	72.3	75.2	78.2	83.3	94.4
72.5°	56.1	56.8	58.3	58.3	58.3	59.7	61.2	62.7	64.2	67.1	71.5
75°	46.5	47.9	47.9	47.9	48.7	48.7	50.2	51.6	53.1	55.3	56.8
77.5°	38.4	38.4	38.4	38.4	39.1	39.1	39.8	41.3	42.0	42.8	44.3
80°	28.8	29.5	29.5	29.5	30.2	30.2	30.2	31.7	32.5	32.5	33.9
82.5°	21.4	21.4	21.4	22.1	21.4	22.1	22.1	22.9	22.1	22.9	23.6
85°	13.3	13.3	13.3	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.8
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.4	6.6	6.6
90°	27.5	27.0	26.5	26.3	25.7	24.6	23.4	22.3	21.1	19.2	17.3
92.5°	28.0	27.7	27.5	27.4	27.2	26.7	26.2	25.8	25.3	24.6	23.9
95°	45.7	46.0	46.2	46.3	45.7	44.6	43.4	42.3	41.1	39.5	37.8
97.5°	57.5	57.2	57.0	56.9	56.5	55.8	55.1	54.4	53.7	50.0	46.2
100°	69.7	69.2	68.7	68.5	67.6	65.7	63.8	61.9	60.0	56.0	52.0
102.5°	75.5	74.8	74.1	73.7	72.4	69.8	67.3	64.7	62.1	104.7	147.3
105°	78.1	77.2	76.3	75.8	74.5	72.0	69.4	66.9	64.3	128.2	192.1
107.5°	80.3	79.3	78.4	77.9	76.6	74.1	71.5	69.0	66.4	145.3	224.1
110°	81.3	80.4	79.5	79.0	90.7	114.1	137.5	160.9	184.3	251.9	319.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	82.9	82.2	81.5	81.1	131.5	232.4	333.3	434.2	535.1	539.1	543.1
115°	120.1	136.9	153.8	162.2	216.4	324.8	433.1	541.5	649.9	644.0	638.2
117.5°	402.8	464.1	525.4	556.1	572.8	606.3	639.8	673.3	706.8	702.8	698.8
120°	705.7	737.3	768.9	784.7	783.3	780.5	777.7	774.9	772.1	767.9	763.7
122.5°	841.1	840.9	840.6	840.5	839.8	838.4	837.0	835.6	834.2	829.5	824.8
125°	899.2	898.5	897.8	897.4	896.6	894.9	893.3	891.6	890.0	885.6	881.1
127.5°	952.8	952.5	952.3	952.2	951.0	948.7	946.3	944.0	941.6	938.1	934.6
130°	1002.1	1002.4	1002.6	1002.7	1001.4	998.8	996.3	993.7	991.1	988.5	986.0
132.5°	1049.5	1049.8	1050.0	1050.1	1049.0	1046.9	1044.8	1042.7	1040.6	1038.0	1035.5
135°	1095.3	1095.8	1096.3	1096.5	1095.3	1093.0	1090.6	1088.3	1085.9	1083.8	1081.7
137.5°	1137.9	1138.6	1139.3	1139.7	1138.5	1136.2	1133.8	1131.5	1129.1	1126.8	1124.4
140°	1177.8	1179.0	1180.1	1180.7	1179.7	1177.6	1175.5	1173.4	1171.3	1168.7	1166.1
142.5°	1215.8	1216.9	1218.1	1218.7	1217.8	1215.9	1214.0	1212.1	1210.2	1207.2	1204.1
145°	1250.5	1251.6	1252.8	1253.4	1252.6	1250.9	1249.3	1247.6	1246.0	1242.0	1238.0
147.5°	1281.6	1282.6	1283.5	1284.0	1283.4	1282.2	1281.1	1279.9	1278.7	1274.7	1270.7
150°	1310.6	1311.7	1312.9	1313.5	1312.8	1311.4	1309.9	1308.5	1307.1	1303.4	1299.6
152.5°	1335.7	1337.3	1339.0	1339.8	1339.1	1337.7	1336.3	1334.9	1333.5	1330.0	1326.5
155°	1358.3	1360.2	1362.1	1363.0	1362.3	1360.9	1359.4	1358.0	1356.6	1353.8	1351.0
157.5°	1379.3	1381.2	1383.1	1384.0	1383.2	1381.5	1379.9	1378.2	1376.6	1374.5	1372.4
160°	1396.8	1398.4	1400.1	1400.9	1400.2	1398.8	1397.4	1396.0	1394.6	1393.2	1391.8
162.5°	1412.4	1414.5	1416.6	1417.7	1416.9	1415.3	1413.6	1412.0	1410.4	1409.2	1408.0
165°	1426.3	1427.9	1429.6	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1422.3	1421.6
167.5°	1436.7	1438.8	1440.9	1442.0	1441.2	1439.5	1437.9	1436.2	1434.6	1433.9	1433.2
170°	1445.1	1447.2	1449.3	1450.4	1449.6	1447.9	1446.3	1444.6	1443.0	1442.5	1442.1
172.5°	1451.4	1453.5	1455.6	1456.7	1455.9	1454.2	1452.6	1450.9	1449.3	1448.8	1448.4
175°	1455.1	1457.4	1459.7	1460.9	1460.1	1458.4	1456.8	1455.1	1453.5	1453.0	1452.6
177.5°	1456.7	1458.8	1460.9	1462.0	1461.2	1459.5	1457.9	1456.2	1454.6	1454.4	1454.1
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1083.4	1079.7	1079.7	1077.5	1077.5	1065.7	1065.7	1069.4	1065.0	1059.8	1052.4
5°	1111.4	1103.3	1101.1	1098.1	1088.6	1073.8	1067.9	1065.7	1056.8	1045.8	1033.2
7.5°	1138.0	1124.7	1118.1	1111.4	1098.9	1078.2	1066.4	1058.3	1045.0	1028.1	1011.9
10°	1163.8	1146.8	1129.9	1121.7	1104.0	1078.2	1061.3	1048.0	1028.8	1006.0	983.1
12.5°	1187.4	1152.0	1149.0	1132.8	1107.0	1077.5	1051.7	1032.5	1008.2	981.6	955.1
15°	1208.0	1171.9	1154.2	1139.4	1105.5	1068.6	1041.4	1017.8	985.3	955.1	922.6
17.5°	1218.4	1179.3	1167.5	1143.1	1108.5	1060.5	1023.7	994.9	959.5	923.4	886.5
20°	1228.7	1183.0	1163.8	1146.8	1099.6	1045.0	1003.7	970.6	931.5	888.7	848.1
22.5°	1233.8	1183.0	1160.1	1136.5	1090.8	1028.1	979.4	940.3	894.6	851.1	802.4
25°	1225.0	1178.5	1151.2	1126.9	1075.3	1007.4	951.4	907.1	858.5	809.0	759.6
27.5°	1202.9	1168.2	1136.5	1111.4	1053.9	980.9	921.9	871.7	821.6	766.3	716.1
30°	1161.6	1146.1	1121.0	1093.0	1030.3	957.3	887.2	835.6	780.3	725.0	672.6
32.5°	1097.4	1110.7	1094.5	1070.1	1002.3	924.8	850.3	798.0	737.5	677.8	629.8
35°	1019.2	1066.4	1057.6	1040.6	972.8	890.2	815.7	752.3	691.8	631.3	583.4
37.5°	933.7	1005.2	1012.6	1002.3	938.8	854.8	772.9	711.0	649.0	587.8	539.1
40°	816.4	926.3	949.9	954.3	903.4	812.0	726.4	666.0	604.8	545.0	486.0
42.5°	708.7	847.4	876.9	895.3	858.5	770.0	683.7	616.6	556.1	502.2	443.2
45°	607.7	752.3	800.2	823.8	807.6	722.0	632.8	570.1	514.8	465.4	408.6
47.5°	503.7	649.0	716.1	753.7	753.7	673.3	584.1	522.2	469.1	427.0	376.9
50°	434.4	555.3	624.7	674.1	687.4	623.9	539.9	479.4	429.2	383.5	345.2
52.5°	370.2	478.6	536.2	587.8	626.1	570.8	490.4	435.9	386.5	343.7	313.4
55°	320.1	401.2	453.6	510.4	553.1	517.0	442.5	389.4	346.6	311.2	285.4
57.5°	272.1	342.9	385.7	435.9	481.6	454.3	394.6	348.8	311.2	280.3	257.4
60°	231.6	289.1	322.3	361.4	418.2	399.0	349.6	307.5	277.3	249.3	230.1
62.5°	196.9	242.6	270.7	298.7	350.3	341.5	303.1	270.7	244.9	221.3	205.0
65°	161.5	199.1	221.3	245.6	286.9	290.6	259.6	236.7	213.1	192.5	177.7
67.5°	130.5	160.0	180.0	200.6	233.8	244.1	222.7	203.6	183.6	166.7	153.4
70°	105.5	126.1	140.9	157.1	184.4	196.9	185.9	172.6	156.4	142.3	130.5
72.5°	83.3	96.6	105.5	118.0	140.1	152.7	151.9	140.1	128.3	118.7	109.2
75°	61.2	71.5	78.9	87.0	104.7	116.5	119.5	114.3	102.5	95.1	87.8
77.5°	46.5	52.4	56.1	62.0	74.5	84.8	89.2	87.8	79.7	73.8	68.6
80°	35.4	36.9	38.4	40.6	50.9	60.5	63.4	62.7	58.3	56.1	50.2
82.5°	25.1	25.8	26.6	27.3	31.0	39.1	42.0	43.5	39.8	37.6	32.5
85°	14.8	15.5	15.5	17.0	17.7	19.9	25.1	25.1	24.3	21.4	20.7
87.5°	7.4	7.4	6.6	6.6	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	15.4	13.5	12.6	11.3	8.8	6.2	3.7	1.1	3.7	6.2	8.8
92.5°	23.2	22.5	22.1	22.6	23.5	24.4	25.4	26.3	25.4	24.4	23.5
95°	36.2	34.5	33.7	37.6	45.3	53.0	60.8	68.5	60.8	53.0	45.3
97.5°	42.5	38.8	36.9	46.5	65.7	84.8	104.0	123.2	104.0	84.8	65.7
100°	48.1	44.1	42.1	58.1	90.2	122.3	154.3	186.4	154.3	122.3	90.2
102.5°	189.9	232.5	253.8	254.0	254.5	255.0	255.4	255.9	255.4	255.0	254.5
105°	256.0	319.9	351.8	348.3	341.3	334.2	327.2	320.2	327.2	334.2	341.3
107.5°	303.0	381.9	421.3	418.4	412.5	406.7	400.8	395.0	400.8	406.7	412.5
110°	387.2	454.9	488.7	486.2	481.3	476.4	471.5	466.6	471.5	476.4	481.3

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4FO-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	547.0	551.0	553.0	550.9	546.7	542.4	538.2	534.0	538.2	542.4	546.7
115°	632.3	626.4	623.5	621.5	617.5	613.6	609.6	605.6	609.6	613.6	617.5
117.5°	694.9	690.9	688.9	686.6	681.9	677.2	672.5	667.8	672.5	677.2	681.9
120°	759.4	755.2	753.1	751.3	747.8	744.3	740.8	737.3	740.8	744.3	747.8
122.5°	820.1	815.4	813.1	811.2	807.5	803.8	800.0	796.3	800.0	803.8	807.5
125°	876.7	872.2	870.0	868.5	865.4	862.4	859.3	856.3	859.3	862.4	865.4
127.5°	931.1	927.6	925.8	924.2	920.9	917.6	914.4	911.1	914.4	917.6	920.9
130°	983.4	980.9	979.6	977.7	974.0	970.2	966.5	962.7	966.5	970.2	974.0
132.5°	1032.9	1030.4	1029.1	1027.6	1024.5	1021.5	1018.4	1015.4	1018.4	1021.5	1024.5
135°	1079.6	1077.5	1076.5	1074.6	1070.9	1067.1	1063.4	1059.6	1063.4	1067.1	1070.9
137.5°	1122.1	1119.8	1118.6	1117.2	1114.4	1111.6	1108.8	1106.0	1108.8	1111.6	1114.4
140°	1163.6	1161.0	1159.7	1158.8	1156.9	1155.0	1153.1	1151.2	1153.1	1155.0	1156.9
142.5°	1201.1	1198.0	1196.5	1195.7	1194.1	1192.4	1190.8	1189.2	1190.8	1192.4	1194.1
145°	1234.1	1230.1	1228.1	1228.2	1228.5	1228.7	1229.0	1229.2	1229.0	1228.7	1228.5
147.5°	1266.8	1262.8	1260.8	1261.1	1261.8	1262.5	1263.2	1263.9	1263.2	1262.5	1261.8
150°	1295.9	1292.2	1290.3	1291.1	1292.8	1294.4	1296.1	1297.7	1296.1	1294.4	1292.8
152.5°	1323.0	1319.5	1317.7	1318.6	1320.5	1322.4	1324.2	1326.1	1324.2	1322.4	1320.5
155°	1348.2	1345.4	1344.0	1345.1	1347.2	1349.3	1351.4	1353.5	1351.4	1349.3	1347.2
157.5°	1370.3	1368.2	1367.2	1368.1	1370.0	1371.9	1373.7	1375.6	1373.7	1371.9	1370.0
160°	1390.3	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6	1393.2	1391.8	1390.3
162.5°	1406.9	1405.7	1405.1	1405.8	1407.2	1408.6	1410.0	1411.4	1410.0	1408.6	1407.2
165°	1420.9	1420.2	1419.8	1420.5	1421.9	1423.4	1424.8	1426.2	1424.8	1423.4	1421.9
167.5°	1432.5	1431.8	1431.4	1432.1	1433.5	1434.9	1436.3	1437.7	1436.3	1434.9	1433.5
170°	1441.6	1441.1	1440.9	1441.6	1443.0	1444.4	1445.8	1447.2	1445.8	1444.4	1443.0
172.5°	1447.9	1447.4	1447.2	1447.9	1449.3	1450.7	1452.1	1453.5	1452.1	1450.7	1449.3
175°	1452.1	1451.6	1451.4	1452.2	1453.9	1455.5	1457.2	1458.8	1457.2	1455.5	1453.9
177.5°	1453.9	1453.6	1453.5	1454.3	1456.0	1457.6	1459.3	1460.9	1459.3	1457.6	1456.0
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1049.5	1050.2	1052.4	1045.8	1035.5	1031.0	1017.8	1015.5	1013.3	1013.3	1015.5
5°	1025.9	1022.9	1023.7	1011.1	996.4	987.5	969.1	972.0	962.4	956.5	958.0
7.5°	1000.1	991.9	991.2	975.0	956.5	940.3	921.1	916.7	907.9	897.5	893.1
10°	967.6	961.7	950.6	932.2	908.6	895.3	869.5	854.0	851.8	836.3	830.4
12.5°	934.4	924.1	913.0	887.2	860.7	839.3	820.1	803.1	791.3	778.1	769.2
15°	896.1	883.5	871.0	843.7	812.7	791.3	762.6	737.5	702.8	675.6	660.1
17.5°	854.0	840.0	823.1	792.8	762.6	733.1	680.0	650.5	626.1	609.9	600.3
20°	810.5	795.0	778.1	747.8	695.5	643.8	614.3	591.5	576.7	560.5	548.7
22.5°	764.8	748.6	730.1	682.9	627.6	591.5	568.6	547.2	525.8	517.0	511.1
25°	722.0	707.3	683.7	619.5	576.0	542.8	517.0	503.0	491.9	480.1	469.1
27.5°	677.8	650.5	617.3	563.5	536.2	502.2	483.8	473.5	454.3	446.2	441.0
30°	624.7	594.4	562.7	524.4	492.7	469.1	452.1	435.1	424.1	416.0	407.1
32.5°	570.8	542.1	522.2	482.3	458.7	434.4	418.2	407.8	391.6	386.5	382.8
35°	524.4	500.0	482.3	449.9	427.8	405.6	393.8	378.3	368.0	358.4	352.5
37.5°	478.6	465.4	446.9	419.6	396.0	378.3	362.1	357.0	342.9	337.8	331.9
40°	446.9	427.0	411.5	387.9	368.0	348.8	338.5	326.7	317.1	309.0	306.8
42.5°	408.6	393.8	385.0	359.2	338.5	327.5	314.9	301.6	294.3	287.6	279.5
45°	379.8	366.5	354.0	333.4	314.9	300.9	289.8	281.0	268.5	265.5	253.0
47.5°	349.6	336.3	326.7	306.1	289.1	275.8	267.7	255.9	245.6	239.0	233.1
50°	319.3	308.3	299.4	281.7	267.0	253.0	241.9	230.1	225.7	214.6	210.9
52.5°	290.6	283.2	273.6	256.7	241.9	230.1	218.3	208.7	202.1	196.2	191.8
55°	266.2	254.4	250.0	231.6	219.0	206.5	196.2	190.3	182.2	178.5	174.8
57.5°	239.0	232.3	224.9	210.9	196.9	185.1	177.7	168.9	164.5	160.0	157.1
60°	215.4	205.8	199.9	188.1	175.5	164.5	157.8	151.2	145.3	141.6	135.7
62.5°	188.1	180.7	177.0	164.5	154.1	143.8	137.9	131.3	126.9	120.2	112.8
65°	164.5	158.6	154.1	143.8	134.2	124.6	118.7	110.6	104.7	101.0	100.3
67.5°	143.8	139.4	132.8	123.2	113.6	106.2	99.6	92.9	92.2	90.7	90.7
70°	121.0	116.5	112.8	102.5	94.4	86.3	84.8	82.6	80.4	79.7	78.2
72.5°	101.0	97.4	92.9	84.1	76.0	73.8	72.3	70.8	68.6	67.9	67.1
75°	81.9	76.7	73.8	65.6	63.4	62.0	60.5	58.3	56.8	56.1	54.6
77.5°	62.7	57.5	57.5	53.1	51.6	49.4	47.9	46.5	45.7	44.3	44.3
80°	44.3	44.3	42.8	40.6	38.4	37.6	35.4	34.7	33.9	34.7	33.2
82.5°	32.5	29.5	29.5	28.0	26.6	25.8	24.3	24.3	23.6	23.6	23.6
85°	18.4	18.4	17.7	16.2	15.5	15.5	14.8	14.8	14.0	14.0	13.3
87.5°	7.4	6.6	7.4	6.6	6.6	5.9	5.9	5.9	5.2	5.9	5.2
90°	11.3	12.6	13.5	15.4	17.3	19.2	21.1	22.3	23.4	24.6	25.7
92.5°	22.6	22.1	22.5	23.2	23.9	24.6	25.3	25.8	26.2	26.7	27.2
95°	37.6	33.7	34.5	36.2	37.8	39.5	41.1	42.3	43.4	44.6	45.7
97.5°	46.5	36.9	38.8	42.5	46.2	50.0	53.7	54.4	55.1	55.8	56.5
100°	58.1	42.1	44.1	48.1	52.0	56.0	60.0	61.9	63.8	65.7	67.6
102.5°	254.0	253.8	232.5	189.9	147.3	104.7	62.1	64.7	67.3	69.8	72.4
105°	348.3	351.8	319.9	256.0	192.1	128.2	64.3	66.9	69.4	72.0	74.5
107.5°	418.4	421.3	381.9	303.0	224.1	145.3	66.4	69.0	71.5	74.1	76.6
110°	486.2	488.7	454.9	387.2	319.6	251.9	184.3	160.9	137.5	114.1	90.7

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	550.9	553.0	551.0	547.0	543.1	539.1	535.1	434.2	333.3	232.4	131.5
115°	621.5	623.5	626.4	632.3	638.2	644.0	649.9	541.5	433.1	324.8	216.4
117.5°	686.6	688.9	690.9	694.9	698.8	702.8	706.8	673.3	639.8	606.3	572.8
120°	751.3	753.1	755.2	759.4	763.7	767.9	772.1	774.9	777.7	780.5	783.3
122.5°	811.2	813.1	815.4	820.1	824.8	829.5	834.2	835.6	837.0	838.4	839.8
125°	868.5	870.0	872.2	876.7	881.1	885.6	890.0	891.6	893.3	894.9	896.6
127.5°	924.2	925.8	927.6	931.1	934.6	938.1	941.6	944.0	946.3	948.7	951.0
130°	977.7	979.6	980.9	983.4	986.0	988.5	991.1	993.7	996.3	998.8	1001.4
132.5°	1027.6	1029.1	1030.4	1032.9	1035.5	1038.0	1040.6	1042.7	1044.8	1046.9	1049.0
135°	1074.6	1076.5	1077.5	1079.6	1081.7	1083.8	1085.9	1088.3	1090.6	1093.0	1095.3
137.5°	1117.2	1118.6	1119.8	1122.1	1124.4	1126.8	1129.1	1131.5	1133.8	1136.2	1138.5
140°	1158.8	1159.7	1161.0	1163.6	1166.1	1168.7	1171.3	1173.4	1175.5	1177.6	1179.7
142.5°	1195.7	1196.5	1198.0	1201.1	1204.1	1207.2	1210.2	1212.1	1214.0	1215.9	1217.8
145°	1228.2	1228.1	1230.1	1234.1	1238.0	1242.0	1246.0	1247.6	1249.3	1250.9	1252.6
147.5°	1261.1	1260.8	1262.8	1266.8	1270.7	1274.7	1278.7	1279.9	1281.1	1282.2	1283.4
150°	1291.1	1290.3	1292.2	1295.9	1299.6	1303.4	1307.1	1308.5	1309.9	1311.4	1312.8
152.5°	1318.6	1317.7	1319.5	1323.0	1326.5	1330.0	1333.5	1334.9	1336.3	1337.7	1339.1
155°	1345.1	1344.0	1345.4	1348.2	1351.0	1353.8	1356.6	1358.0	1359.4	1360.9	1362.3
157.5°	1368.1	1367.2	1368.2	1370.3	1372.4	1374.5	1376.6	1378.2	1379.9	1381.5	1383.2
160°	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6	1396.0	1397.4	1398.8	1400.2
162.5°	1405.8	1405.1	1405.7	1406.9	1408.0	1409.2	1410.4	1412.0	1413.6	1415.3	1416.9
165°	1420.5	1419.8	1420.2	1420.9	1421.6	1422.3	1423.0	1424.6	1426.3	1427.9	1429.6
167.5°	1432.1	1431.4	1431.8	1432.5	1433.2	1433.9	1434.6	1436.2	1437.9	1439.5	1441.2
170°	1441.6	1440.9	1441.1	1441.6	1442.1	1442.5	1443.0	1444.6	1446.3	1447.9	1449.6
172.5°	1447.9	1447.2	1447.4	1447.9	1448.4	1448.8	1449.3	1450.9	1452.6	1454.2	1455.9
175°	1452.2	1451.4	1451.6	1452.1	1452.6	1453.0	1453.5	1455.1	1456.8	1458.4	1460.1
177.5°	1454.3	1453.5	1453.6	1453.9	1454.1	1454.4	1454.6	1456.2	1457.9	1459.5	1461.2
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1015.5	1014.1	1009.6	1011.1	1008.9	1008.9	1007.4	1007.4	1007.4	1011.1	1008.9
5°	960.2	955.1	949.9	947.7	945.5	943.3	943.3	942.5	949.2	947.7	953.6
7.5°	891.6	890.2	879.8	879.8	876.2	874.7	878.4	879.1	879.8	881.3	885.0
10°	830.4	826.7	812.0	813.5	811.3	808.3	810.5	809.0	814.2	815.7	814.2
12.5°	758.2	751.5	735.3	727.2	718.3	711.7	719.8	713.9	734.6	740.5	756.7
15°	662.3	649.7	638.7	638.7	630.6	624.7	628.4	635.0	639.4	646.1	649.0
17.5°	598.1	593.0	584.1	578.9	576.7	574.5	574.5	577.5	587.1	586.3	592.2
20°	543.5	540.6	536.2	529.5	527.3	525.8	525.8	525.8	532.5	538.4	542.1
22.5°	505.9	503.7	500.8	491.9	487.5	486.0	489.7	491.9	497.1	501.5	505.2
25°	468.3	463.2	458.0	455.0	452.8	452.8	454.3	455.0	457.3	459.5	463.9
27.5°	437.3	433.7	426.3	418.2	418.2	416.0	417.4	418.9	424.1	431.4	435.1
30°	402.7	401.9	399.0	396.0	393.1	391.6	394.6	396.8	397.5	401.2	401.2
32.5°	377.6	372.4	367.3	364.3	362.9	362.1	362.9	365.8	365.8	370.2	375.4
35°	352.5	349.6	344.4	339.3	337.8	334.1	337.0	340.0	345.2	347.4	349.6
37.5°	325.2	321.6	319.3	317.9	314.9	315.7	313.4	317.9	322.3	321.6	323.0
40°	304.6	298.0	291.3	290.6	289.8	289.1	289.1	289.8	292.8	295.7	300.2
42.5°	278.0	275.8	269.9	264.0	262.6	261.1	259.6	262.6	268.5	273.6	275.8
45°	250.8	247.8	246.3	241.9	239.0	238.2	236.7	240.4	245.6	247.8	249.3
47.5°	225.7	224.9	220.5	221.3	219.0	219.8	219.0	221.3	221.3	223.5	224.9
50°	208.7	206.5	204.3	202.8	200.6	200.6	199.9	200.6	203.6	206.5	205.8
52.5°	191.8	188.1	187.3	186.6	185.1	186.6	184.4	185.1	188.1	189.5	188.8
55°	171.8	171.1	169.6	168.2	167.4	166.7	166.7	166.7	169.6	171.8	172.6
57.5°	156.4	152.7	149.7	149.7	146.8	146.0	147.5	148.2	150.5	151.9	153.4
60°	135.0	133.5	129.1	126.9	122.4	121.7	121.7	124.6	128.3	133.5	135.0
62.5°	112.1	109.9	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.9	109.9
65°	99.6	100.3	99.6	98.8	99.6	99.6	98.8	98.8	98.8	99.6	100.3
67.5°	89.2	88.5	89.2	88.5	87.8	87.8	87.0	87.8	88.5	89.2	89.2
70°	77.4	77.4	76.7	77.4	76.7	76.0	75.2	75.2	76.7	77.4	77.4
72.5°	66.4	66.4	65.6	65.6	64.2	64.2	64.9	64.2	64.2	66.4	66.4
75°	55.3	54.6	53.8	53.8	53.1	53.1	53.1	52.4	53.8	53.8	54.6
77.5°	43.5	43.5	43.5	42.8	42.8	42.0	42.0	42.8	42.8	42.8	43.5
80°	33.2	33.2	33.2	32.5	31.7	31.7	31.7	31.7	31.7	32.5	31.7
82.5°	22.9	22.9	22.9	22.9	22.9	22.1	22.1	22.1	22.9	22.9	22.1
85°	14.0	13.3	14.0	14.0	13.3	14.0	13.3	13.3	12.5	12.5	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	26.3	26.5	27.0	27.5	27.9	28.4	27.9	27.5	27.0	26.5	26.3
92.5°	27.4	27.5	27.7	28.0	28.2	28.4	28.2	28.0	27.7	27.5	27.4
95°	46.3	46.2	46.0	45.7	45.5	45.3	45.5	45.7	46.0	46.2	46.3
97.5°	56.9	57.0	57.2	57.5	57.7	57.9	57.7	57.5	57.2	57.0	56.9
100°	68.5	68.7	69.2	69.7	70.1	70.6	70.1	69.7	69.2	68.7	68.5
102.5°	73.7	74.1	74.8	75.5	76.2	76.9	76.2	75.5	74.8	74.1	73.7
105°	75.8	76.3	77.2	78.1	79.1	80.0	79.1	78.1	77.2	76.3	75.8
107.5°	77.9	78.4	79.3	80.3	81.2	82.2	81.2	80.3	79.3	78.4	77.9
110°	79.0	79.5	80.4	81.3	82.3	83.2	82.3	81.3	80.4	79.5	79.0

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.1	81.5	82.2	82.9	83.6	84.3	83.6	82.9	82.2	81.5	81.1
115°	162.2	153.8	136.9	120.1	103.2	86.4	103.2	120.1	136.9	153.8	162.2
117.5°	556.1	525.4	464.1	402.8	341.5	280.2	341.5	402.8	464.1	525.4	556.1
120°	784.7	768.9	737.3	705.7	674.1	642.5	674.1	705.7	737.3	768.9	784.7
122.5°	840.5	840.6	840.9	841.1	841.4	841.6	841.4	841.1	840.9	840.6	840.5
125°	897.4	897.8	898.5	899.2	899.9	900.6	899.9	899.2	898.5	897.8	897.4
127.5°	952.2	952.3	952.5	952.8	953.0	953.2	953.0	952.8	952.5	952.3	952.2
130°	1002.7	1002.6	1002.4	1002.1	1001.9	1001.7	1001.9	1002.1	1002.4	1002.6	1002.7
132.5°	1050.1	1050.0	1049.8	1049.5	1049.3	1049.1	1049.3	1049.5	1049.8	1050.0	1050.1
135°	1096.5	1096.3	1095.8	1095.3	1094.9	1094.4	1094.9	1095.3	1095.8	1096.3	1096.5
137.5°	1139.7	1139.3	1138.6	1137.9	1137.2	1136.5	1137.2	1137.9	1138.6	1139.3	1139.7
140°	1180.7	1180.1	1179.0	1177.8	1176.7	1175.5	1176.7	1177.8	1179.0	1180.1	1180.7
142.5°	1218.7	1218.1	1216.9	1215.8	1214.6	1213.4	1214.6	1215.8	1216.9	1218.1	1218.7
145°	1253.4	1252.8	1251.6	1250.5	1249.3	1248.1	1249.3	1250.5	1251.6	1252.8	1253.4
147.5°	1284.0	1283.5	1282.6	1281.6	1280.7	1279.7	1280.7	1281.6	1282.6	1283.5	1284.0
150°	1313.5	1312.9	1311.7	1310.6	1309.4	1308.2	1309.4	1310.6	1311.7	1312.9	1313.5
152.5°	1339.8	1339.0	1337.3	1335.7	1334.0	1332.4	1334.0	1335.7	1337.3	1339.0	1339.8
155°	1363.0	1362.1	1360.2	1358.3	1356.4	1354.5	1356.4	1358.3	1360.2	1362.1	1363.0
157.5°	1384.0	1383.1	1381.2	1379.3	1377.5	1375.6	1377.5	1379.3	1381.2	1383.1	1384.0
160°	1400.9	1400.1	1398.4	1396.8	1395.1	1393.5	1395.1	1396.8	1398.4	1400.1	1400.9
162.5°	1417.7	1416.6	1414.5	1412.4	1410.3	1408.2	1410.3	1412.4	1414.5	1416.6	1417.7
165°	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1424.6	1426.3	1427.9	1429.6	1430.4
167.5°	1442.0	1440.9	1438.8	1436.7	1434.6	1432.5	1434.6	1436.7	1438.8	1440.9	1442.0
170°	1450.4	1449.3	1447.2	1445.1	1443.0	1440.9	1443.0	1445.1	1447.2	1449.3	1450.4
172.5°	1456.7	1455.6	1453.5	1451.4	1449.3	1447.2	1449.3	1451.4	1453.5	1455.6	1456.7
175°	1460.9	1459.7	1457.4	1455.1	1452.7	1450.4	1452.7	1455.1	1457.4	1459.7	1460.9
177.5°	1462.0	1460.9	1458.8	1456.7	1454.6	1452.5	1454.6	1456.7	1458.8	1460.9	1462.0
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1011.1	1014.8	1013.3	1005.2	1013.3	1015.5	1020.0	1024.4	1027.3	1031.8	1035.5
5°	947.7	955.1	959.5	955.1	969.8	972.0	982.4	988.3	997.1	1004.5	1010.4
7.5°	888.0	893.9	902.7	904.2	913.0	923.4	938.1	952.9	966.9	974.2	980.9
10°	823.8	834.1	847.4	844.4	857.7	873.9	889.4	913.0	924.8	938.1	949.9
12.5°	759.6	766.3	784.0	789.9	809.0	821.6	843.0	857.7	887.2	902.7	913.0
15°	647.5	674.8	696.9	723.5	748.6	772.2	791.3	817.9	843.7	855.5	872.5
17.5°	596.6	609.2	622.5	635.7	668.2	710.2	744.1	772.9	795.0	810.5	830.4
20°	543.5	556.1	570.8	583.4	603.3	633.5	675.6	725.0	751.5	767.7	786.9
22.5°	505.9	517.7	527.3	538.4	553.9	576.0	607.7	668.9	704.3	724.2	741.2
25°	465.4	480.1	490.4	498.6	511.1	535.4	561.2	595.9	659.3	674.8	698.4
27.5°	437.3	441.8	453.6	466.1	478.6	491.9	518.5	548.0	590.7	624.7	653.4
30°	404.2	415.2	426.3	431.4	442.5	461.7	477.9	509.6	542.8	569.4	604.0
32.5°	379.1	385.7	393.1	405.6	416.0	429.2	445.5	472.0	500.0	517.0	543.5
35°	351.1	355.5	371.0	376.1	386.5	399.7	416.0	436.6	466.8	480.1	499.3
37.5°	324.5	334.8	339.3	351.1	360.6	373.9	385.7	409.3	429.2	444.7	462.4
40°	303.9	308.3	316.4	326.7	334.8	345.2	359.9	376.9	398.3	410.8	426.3
42.5°	278.8	282.5	292.8	298.7	312.0	321.6	330.4	351.1	370.2	379.8	395.3
45°	251.5	260.3	267.0	278.8	286.2	298.0	309.0	323.8	341.5	352.5	361.4
47.5°	227.9	236.7	243.4	254.4	266.2	271.4	283.2	298.7	314.9	323.8	336.3
50°	208.7	211.7	224.2	229.4	241.9	252.2	260.3	273.6	291.3	296.5	306.8
52.5°	190.3	192.5	200.6	207.2	218.3	227.2	237.5	250.0	264.8	272.9	281.0
55°	174.1	175.5	179.2	186.6	194.0	205.0	214.6	226.4	239.0	247.8	255.2
57.5°	155.6	158.6	161.5	165.9	173.3	183.6	194.0	205.0	215.4	221.3	230.8
60°	134.2	138.7	143.8	149.0	154.1	161.5	173.3	183.6	193.2	198.4	205.8
62.5°	111.4	120.2	124.6	130.5	135.0	141.6	150.5	162.3	168.9	175.5	181.4
65°	100.3	101.0	101.8	107.7	115.8	122.4	130.5	139.4	149.7	154.1	158.6
67.5°	89.2	90.0	91.5	92.2	95.1	102.5	111.4	121.0	129.1	132.0	136.4
70°	78.2	78.2	81.1	81.9	82.6	83.3	90.7	100.3	107.7	111.4	116.5
72.5°	66.4	67.1	68.6	69.3	70.8	72.3	74.5	79.7	88.5	92.2	98.1
75°	54.6	55.3	56.1	56.8	59.0	59.7	62.0	64.9	68.6	73.0	76.7
77.5°	43.5	43.5	44.3	45.7	47.2	47.9	50.2	51.6	53.1	55.3	58.3
80°	32.5	33.2	33.2	34.7	34.7	35.4	36.1	38.4	39.8	41.3	42.8
82.5°	22.1	23.6	23.6	23.6	24.3	25.1	25.8	25.8	27.3	28.0	30.2
85°	13.3	14.0	14.0	14.0	13.3	14.8	14.8	15.5	15.5	15.5	16.2
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.6	6.6
90°	25.7	24.6	23.4	22.3	21.1	19.2	17.3	15.4	13.5	12.6	11.3
92.5°	27.2	26.7	26.2	25.8	25.3	24.6	23.9	23.2	22.5	22.1	22.6
95°	45.7	44.6	43.4	42.3	41.1	39.5	37.8	36.2	34.5	33.7	37.6
97.5°	56.5	55.8	55.1	54.4	53.7	50.0	46.2	42.5	38.8	36.9	46.5
100°	67.6	65.7	63.8	61.9	60.0	56.0	52.0	48.1	44.1	42.1	58.1
102.5°	72.4	69.8	67.3	64.7	62.1	104.7	147.3	189.9	232.5	253.8	254.0
105°	74.5	72.0	69.4	66.9	64.3	128.2	192.1	256.0	319.9	351.8	348.3
107.5°	76.6	74.1	71.5	69.0	66.4	145.3	224.1	303.0	381.9	421.3	418.4
110°	90.7	114.1	137.5	160.9	184.3	251.9	319.6	387.2	454.9	488.7	486.2

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	131.5	232.4	333.3	434.2	535.1	539.1	543.1	547.0	551.0	553.0	550.9
115°	216.4	324.8	433.1	541.5	649.9	644.0	638.2	632.3	626.4	623.5	621.5
117.5°	572.8	606.3	639.8	673.3	706.8	702.8	698.8	694.9	690.9	688.9	686.6
120°	783.3	780.5	777.7	774.9	772.1	767.9	763.7	759.4	755.2	753.1	751.3
122.5°	839.8	838.4	837.0	835.6	834.2	829.5	824.8	820.1	815.4	813.1	811.2
125°	896.6	894.9	893.3	891.6	890.0	885.6	881.1	876.7	872.2	870.0	868.5
127.5°	951.0	948.7	946.3	944.0	941.6	938.1	934.6	931.1	927.6	925.8	924.2
130°	1001.4	998.8	996.3	993.7	991.1	988.5	986.0	983.4	980.9	979.6	977.7
132.5°	1049.0	1046.9	1044.8	1042.7	1040.6	1038.0	1035.5	1032.9	1030.4	1029.1	1027.6
135°	1095.3	1093.0	1090.6	1088.3	1085.9	1083.8	1081.7	1079.6	1077.5	1076.5	1074.6
137.5°	1138.5	1136.2	1133.8	1131.5	1129.1	1126.8	1124.4	1122.1	1119.8	1118.6	1117.2
140°	1179.7	1177.6	1175.5	1173.4	1171.3	1168.7	1166.1	1163.6	1161.0	1159.7	1158.8
142.5°	1217.8	1215.9	1214.0	1212.1	1210.2	1207.2	1204.1	1201.1	1198.0	1196.5	1195.7
145°	1252.6	1250.9	1249.3	1247.6	1246.0	1242.0	1238.0	1234.1	1230.1	1228.1	1228.2
147.5°	1283.4	1282.2	1281.1	1279.9	1278.7	1274.7	1270.7	1266.8	1262.8	1260.8	1261.1
150°	1312.8	1311.4	1309.9	1308.5	1307.1	1303.4	1299.6	1295.9	1292.2	1290.3	1291.1
152.5°	1339.1	1337.7	1336.3	1334.9	1333.5	1330.0	1326.5	1323.0	1319.5	1317.7	1318.6
155°	1362.3	1360.9	1359.4	1358.0	1356.6	1353.8	1351.0	1348.2	1345.4	1344.0	1345.1
157.5°	1383.2	1381.5	1379.9	1378.2	1376.6	1374.5	1372.4	1370.3	1368.2	1367.2	1368.1
160°	1400.2	1398.8	1397.4	1396.0	1394.6	1393.2	1391.8	1390.3	1388.9	1388.2	1388.9
162.5°	1416.9	1415.3	1413.6	1412.0	1410.4	1409.2	1408.0	1406.9	1405.7	1405.1	1405.8
165°	1429.6	1427.9	1426.3	1424.6	1423.0	1422.3	1421.6	1420.9	1420.2	1419.8	1420.5
167.5°	1441.2	1439.5	1437.9	1436.2	1434.6	1433.9	1433.2	1432.5	1431.8	1431.4	1432.1
170°	1449.6	1447.9	1446.3	1444.6	1443.0	1442.5	1442.1	1441.6	1441.1	1440.9	1441.6
172.5°	1455.9	1454.2	1452.6	1450.9	1449.3	1448.8	1448.4	1447.9	1447.4	1447.2	1447.9
175°	1460.1	1458.4	1456.8	1455.1	1453.5	1453.0	1452.6	1452.1	1451.6	1451.4	1452.2
177.5°	1461.2	1459.5	1457.9	1456.2	1454.6	1454.4	1454.1	1453.9	1453.6	1453.5	1454.3
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1061.3	1061.3	1061.3	1061.3
2.5°	1042.1	1039.9	1053.2	1067.9
5°	1020.7	1024.4	1041.4	1062.0
7.5°	998.6	1006.7	1026.6	1053.9
10°	967.6	982.4	1012.6	1040.6
12.5°	937.4	957.3	986.0	1019.2
15°	903.4	925.6	961.0	1000.8
17.5°	865.8	890.9	932.2	975.7
20°	826.0	859.2	902.7	949.9
22.5°	781.8	821.6	866.6	918.9
25°	739.0	782.5	827.5	888.0
27.5°	696.9	739.7	789.9	851.1
30°	654.9	694.0	747.8	813.5
32.5°	609.9	650.5	707.3	774.4
35°	568.6	609.2	662.3	728.7
37.5°	524.4	567.9	618.8	687.4
40°	472.7	523.6	573.0	638.7
42.5°	430.0	483.8	531.7	593.7
45°	396.0	446.9	486.8	547.2
47.5°	364.3	405.6	446.2	502.2
50°	334.1	365.8	407.8	458.0
52.5°	303.1	330.4	366.5	413.7
55°	275.1	300.9	333.4	369.5
57.5°	249.3	267.7	300.2	332.6
60°	220.5	239.7	264.8	292.1
62.5°	196.2	210.9	234.5	257.4
65°	170.4	184.4	202.1	223.5
67.5°	146.8	159.3	173.3	190.3
70°	125.4	135.0	145.3	160.0
72.5°	102.5	112.8	122.4	134.2
75°	84.1	88.5	96.6	104.7
77.5°	64.9	70.8	75.2	81.9
80°	46.5	51.6	53.1	58.3
82.5°	31.0	33.9	36.9	38.4
85°	17.7	19.2	22.1	22.9
87.5°	6.6	7.4	8.9	10.3
90°	8.8	6.2	3.7	1.1
92.5°	23.5	24.4	25.4	26.3
95°	45.3	53.0	60.8	68.5
97.5°	65.7	84.8	104.0	123.2
100°	90.2	122.3	154.3	186.4
102.5°	254.5	255.0	255.4	255.9
105°	341.3	334.2	327.2	320.2
107.5°	412.5	406.7	400.8	395.0
110°	481.3	476.4	471.5	466.6

TEST NUMBER: P1009950

CATALOG NUMBER: S122RDIP-B485D1080UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	546.7	542.4	538.2	534.0
115°	617.5	613.6	609.6	605.6
117.5°	681.9	677.2	672.5	667.8
120°	747.8	744.3	740.8	737.3
122.5°	807.5	803.8	800.0	796.3
125°	865.4	862.4	859.3	856.3
127.5°	920.9	917.6	914.4	911.1
130°	974.0	970.2	966.5	962.7
132.5°	1024.5	1021.5	1018.4	1015.4
135°	1070.9	1067.1	1063.4	1059.6
137.5°	1114.4	1111.6	1108.8	1106.0
140°	1156.9	1155.0	1153.1	1151.2
142.5°	1194.1	1192.4	1190.8	1189.2
145°	1228.5	1228.7	1229.0	1229.2
147.5°	1261.8	1262.5	1263.2	1263.9
150°	1292.8	1294.4	1296.1	1297.7
152.5°	1320.5	1322.4	1324.2	1326.1
155°	1347.2	1349.3	1351.4	1353.5
157.5°	1370.0	1371.9	1373.7	1375.6
160°	1390.3	1391.8	1393.2	1394.6
162.5°	1407.2	1408.6	1410.0	1411.4
165°	1421.9	1423.4	1424.8	1426.2
167.5°	1433.5	1434.9	1436.3	1437.7
170°	1443.0	1444.4	1445.8	1447.2
172.5°	1449.3	1450.7	1452.1	1453.5
175°	1453.9	1455.5	1457.2	1458.8
177.5°	1456.0	1457.6	1459.3	1460.9
180°	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)