

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009976

Luminaire Tested: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009976
REPORT IS A COMBINATION OF REPORTS P988256 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5327.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009976

CATALOG NUMBER: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009976

CATALOG NUMBER: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	33	33	26
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	23
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	24	24	19
4	72	61	54	48	64	56	49	44	44	40	36	34	31	29	25	23	21	21	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19	19	19	15
6	61	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	16	16	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	16	15	15	15	12
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13	13	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	12	12	10
10	45	33	27	22	41	31	24	20	25	20	17	20	16	14	15	12	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12507	12507	12507
5°	12527	11900	11810
10°	12404	11285	10913
15°	12233	10561	9890
20°	12007	9738	8820
25°	11778	8893	7840
30°	11467	8069	6770
35°	11163	7240	5852
40°	10854	6424	4907
45°	10494	5582	4082
50°	10123	4772	3322
55°	9737	3961	2638
60°	9285	3168	1996
65°	8770	2414	1623
70°	8146	1751	1290
75°	7362	1336	986
80°	6219	904	662
85°	4337	415	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10494 cd/sqm

TEST NUMBER: P1009976

CATALOG NUMBER: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	1.4
10°-20°	203.3	3.8
20°-30°	285.4	5.4
30°-40°	311.1	5.8
40°-50°	285.9	5.4
50°-60°	224.6	4.2
60°-70°	146.2	2.7
70°-80°	75.2	1.4
80°-90°	23.0	0.4
90°-100°	81.8	1.5
100°-110°	260.1	4.9
110°-120°	445.1	8.4
120°-130°	585.4	11.0
130°-140°	657.1	12.3
140°-150°	644.4	12.1
150°-160°	540.5	10.1
160°-170°	358.5	6.7
170°-180°	125.3	2.4
0°-30°	562.8	10.6
0°-40°	873.9	16.4
0°-60°	1384.4	26.0
0°-90°	1628.8	30.6
90°-120°	787.0	14.8
90°-150°	2673.9	50.2
90°-180°	3698.0	69.4
0°-180°	5327.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	787	777	784	782	75
15°	752	744	719	706	699	212
25°	682	659	612	583	572	314
35°	588	551	488	443	428	368
45°	480	433	358	307	290	371
55°	365	310	232	190	176	326
65°	247	189	124	100	98	245
75°	132	82	57	52	52	139
85°	31	16	14	14	14	35
90°	1	14	39	37	38	5
95°	58	69	71	71	69	65
105°	240	243	246	248	248	253
115°	446	453	451	450	446	442
125°	650	660	656	653	652	581
135°	840	853	855	854	851	650
145°	1020	1028	1035	1036	1031	637
155°	1166	1170	1173	1179	1175	537
165°	1269	1268	1268	1276	1270	358
175°	1320	1317	1315	1323	1316	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P1009976

CATALOG NUMBER: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	790.1	790.1	790.1	790.1	790.1
2.5°	793.7	790.1	782.3	789.4	788.0
5°	790.1	786.6	777.3	783.7	781.5
7.5°	783.7	779.4	769.4	772.3	768.7
10°	775.1	770.1	755.8	753.7	749.4
12.5°	764.4	758.0	738.6	734.4	726.5
15°	751.5	743.6	719.3	705.8	698.6
17.5°	736.5	725.1	695.0	679.3	667.9
20°	719.3	705.0	669.3	651.4	635.7
22.5°	700.7	684.3	642.8	618.5	607.8
25°	682.2	659.3	612.1	582.8	572.0
27.5°	660.0	635.7	583.5	549.9	533.4
30°	636.4	609.2	552.0	515.5	496.2
32.5°	613.5	580.6	522.0	479.1	461.2
35°	587.8	551.3	488.4	443.3	427.6
37.5°	562.7	523.4	456.9	407.6	389.7
40°	536.3	493.4	424.0	373.3	354.7
42.5°	509.1	463.4	391.1	338.2	320.3
45°	480.5	432.6	357.5	306.8	289.6
47.5°	453.3	402.6	325.3	274.6	258.8
50°	423.3	372.5	293.9	244.5	229.5
52.5°	394.0	340.4	263.9	216.7	203.1
55°	365.4	309.6	232.4	189.5	175.9
57.5°	336.1	278.9	204.5	164.5	153.0
60°	306.0	248.8	175.2	138.7	127.3
62.5°	276.7	219.5	150.2	115.8	110.1
65°	246.7	188.8	124.4	100.1	98.0
67.5°	218.1	160.2	100.1	88.0	85.8
70°	188.1	132.3	82.9	75.8	72.9
72.5°	159.5	106.5	69.4	63.6	62.2
75°	131.6	81.5	57.2	52.2	51.5
77.5°	103.7	57.9	45.0	42.2	40.8
80°	77.9	41.5	34.3	31.5	31.5
82.5°	54.3	27.9	23.6	22.2	22.2
85°	30.7	15.7	13.6	13.6	13.6
87.5°	11.4	5.7	5.7	5.0	5.0
90°	1.1	14.5	39.1	36.8	38.0
92.5°	24.6	33.5	34.6	35.7	35.7
95°	58.0	69.2	71.4	71.4	69.2
97.5°	97.1	107.2	111.6	111.6	111.6
100°	141.8	150.7	154.0	154.0	152.9
102.5°	188.6	195.3	199.8	200.9	199.8
105°	240.0	243.3	245.6	247.8	247.8
107.5°	291.3	295.8	295.8	296.9	291.3
110°	340.5	347.2	347.2	347.2	343.8

TEST NUMBER: P1009976

CATALOG NUMBER: S122RDIP-B485D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	394.0	400.7	399.6	396.3	394.0
115°	446.5	453.2	451.0	449.9	446.5
117.5°	499.0	507.9	502.3	499.0	495.6
120°	551.4	560.4	551.4	551.4	548.1
122.5°	599.4	610.6	605.0	601.7	599.4
125°	649.7	659.7	656.4	653.0	651.9
127.5°	698.8	711.1	706.6	702.1	698.8
130°	744.6	759.1	756.8	754.6	750.1
132.5°	795.9	807.1	808.2	802.6	799.2
135°	840.5	852.8	855.1	853.9	850.6
137.5°	889.7	899.7	901.9	900.8	896.4
140°	933.2	943.2	948.8	948.8	944.4
142.5°	977.9	987.9	991.2	992.4	987.9
145°	1020.3	1028.1	1034.8	1035.9	1031.4
147.5°	1058.2	1068.3	1072.7	1075.0	1070.5
150°	1097.3	1104.0	1108.5	1111.8	1108.5
152.5°	1131.9	1138.6	1144.2	1148.6	1144.2
155°	1166.5	1169.8	1173.2	1178.8	1175.4
157.5°	1196.6	1198.9	1201.1	1208.9	1203.3
160°	1223.4	1225.7	1226.8	1233.5	1229.0
162.5°	1248.0	1248.0	1249.1	1256.9	1251.3
165°	1269.2	1268.1	1268.1	1275.9	1270.3
167.5°	1288.2	1284.8	1284.8	1292.6	1287.1
170°	1302.7	1299.3	1298.2	1306.0	1299.3
172.5°	1312.7	1309.4	1308.3	1316.1	1309.4
175°	1320.5	1317.2	1315.0	1322.8	1316.1
177.5°	1325.0	1321.7	1319.4	1326.1	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)