

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010054

Luminaire Tested: S122RDIP-B485D725UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010054
REPORT IS A COMBINATION OF REPORTS P988364 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D725UB35-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4241.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010054

CATALOG NUMBER: S122RDIP-B485D725UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1010054

CATALOG NUMBER: S122RDIP-B485D725UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13069	13069	13069
5°	13090	12434	12342
10°	12961	11793	11403
15°	12784	11036	10334
20°	12548	10176	9216
25°	12306	9292	8192
30°	11982	8432	7075
35°	11665	7564	6115
40°	11342	6713	5127
45°	10966	5834	4265
50°	10577	4986	3472
55°	10174	4138	2757
60°	9704	3310	2086
65°	9165	2523	1696
70°	8510	1831	1348
75°	7692	1397	1030
80°	6499	946	692
85°	4534	433	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10966 cd/sqm

TEST NUMBER: P1010054

CATALOG NUMBER: S122RDIP-B485D725UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	1.8
10°-20°	212.4	5.0
20°-30°	298.2	7.0
30°-40°	325.1	7.7
40°-50°	298.8	7.0
50°-60°	234.7	5.5
60°-70°	152.7	3.6
70°-80°	78.6	1.9
80°-90°	22.7	0.5
90°-100°	56.2	1.3
100°-110°	178.7	4.2
110°-120°	305.8	7.2
120°-130°	402.1	9.5
130°-140°	451.4	10.6
140°-150°	442.6	10.4
150°-160°	371.3	8.8
160°-170°	246.2	5.8
170°-180°	86.1	2.0
0°-30°	588.0	13.9
0°-40°	913.1	21.5
0°-60°	1446.5	34.1
0°-90°	1700.6	40.1
90°-120°	540.7	12.7
90°-150°	1836.8	43.3
90°-180°	2540.0	59.9
0°-180°	4241.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	826	826	826	826	826	
5°	826	822	812	819	817	78
15°	785	777	752	738	730	221
25°	713	689	640	609	598	328
35°	614	576	510	463	447	384
45°	502	452	374	320	303	388
55°	382	324	243	198	184	341
65°	258	197	130	105	102	256
75°	138	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	10	27	25	26	4
95°	40	48	49	49	48	45
105°	165	167	169	170	170	174
115°	307	311	310	309	307	303
125°	446	453	451	449	448	399
135°	577	586	587	587	584	446
145°	701	706	711	712	708	438
155°	801	804	806	810	807	369
165°	872	871	871	876	873	246
175°	907	905	903	909	904	86
180°	909	909	909	909	909	

TEST NUMBER: P1010054

CATALOG NUMBER: S122RDIP-B485D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	825.6	825.6	825.6	825.6	825.6
2.5°	829.4	825.6	817.4	824.9	823.4
5°	825.6	821.9	812.2	818.9	816.7
7.5°	818.9	814.4	804.0	806.9	803.2
10°	809.9	804.7	789.8	787.5	783.0
12.5°	798.7	792.0	771.8	767.3	759.1
15°	785.3	777.1	751.7	737.5	730.0
17.5°	769.6	757.6	726.2	709.8	697.9
20°	751.7	736.7	699.4	680.7	664.2
22.5°	732.2	715.0	671.7	646.3	635.1
25°	712.8	688.9	639.6	608.9	597.7
27.5°	689.6	664.2	609.7	574.6	557.4
30°	665.0	636.6	576.8	538.7	518.5
32.5°	641.1	606.7	545.4	500.6	481.9
35°	614.2	576.1	510.3	463.2	446.8
37.5°	588.0	546.9	477.4	425.9	407.2
40°	560.4	515.5	443.1	390.0	370.6
42.5°	532.0	484.2	408.7	353.4	334.7
45°	502.1	452.0	373.6	320.5	302.6
47.5°	473.7	420.7	340.0	286.9	270.5
50°	442.3	389.3	307.1	255.5	239.8
52.5°	411.7	355.7	275.7	226.4	212.2
55°	381.8	323.5	242.8	198.0	183.8
57.5°	351.2	291.4	213.7	171.8	159.9
60°	319.8	260.0	183.1	145.0	133.0
62.5°	289.2	229.4	156.9	121.0	115.1
65°	257.8	197.3	130.0	104.6	102.4
67.5°	227.9	167.4	104.6	91.9	89.7
70°	196.5	138.2	86.7	79.2	76.2
72.5°	166.6	111.3	72.5	66.5	65.0
75°	137.5	85.2	59.8	54.5	53.8
77.5°	108.3	60.5	47.1	44.1	42.6
80°	81.4	43.3	35.9	32.9	32.9
82.5°	56.8	29.1	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.8	10.0	26.8	25.3	26.1
92.5°	16.9	23.0	23.8	24.5	24.5
95°	39.9	47.5	49.1	49.1	47.5
97.5°	66.7	73.6	76.7	76.7	76.7
100°	97.4	103.5	105.8	105.8	105.1
102.5°	129.6	134.2	137.3	138.0	137.3
105°	164.9	167.2	168.7	170.2	170.2
107.5°	200.1	203.2	203.2	204.0	200.1
110°	233.9	238.5	238.5	238.5	236.2

TEST NUMBER: P1010054

CATALOG NUMBER: S122RDIP-B485D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	270.7	275.3	274.5	272.2	270.7
115°	306.7	311.3	309.8	309.0	306.7
117.5°	342.8	348.9	345.1	342.8	340.5
120°	378.8	384.9	378.8	378.8	376.5
122.5°	411.8	419.4	415.6	413.3	411.8
125°	446.3	453.2	450.9	448.6	447.8
127.5°	480.0	488.4	485.4	482.3	480.0
130°	511.5	521.4	519.9	518.4	515.3
132.5°	546.7	554.4	555.2	551.3	549.0
135°	577.4	585.8	587.4	586.6	584.3
137.5°	611.1	618.0	619.6	618.8	615.7
140°	641.0	647.9	651.8	651.8	648.7
142.5°	671.7	678.6	680.9	681.7	678.6
145°	700.8	706.2	710.8	711.6	708.5
147.5°	726.9	733.8	736.9	738.4	735.4
150°	753.8	758.4	761.4	763.7	761.4
152.5°	777.5	782.1	786.0	789.0	786.0
155°	801.3	803.6	805.9	809.7	807.4
157.5°	822.0	823.5	825.1	830.4	826.6
160°	840.4	841.9	842.7	847.3	844.2
162.5°	857.3	857.3	858.0	863.4	859.6
165°	871.8	871.1	871.1	876.4	872.6
167.5°	884.9	882.6	882.6	887.9	884.1
170°	894.8	892.5	891.8	897.1	892.5
172.5°	901.7	899.4	898.7	904.0	899.4
175°	907.1	904.8	903.3	908.7	904.0
177.5°	910.2	907.9	906.3	911.0	906.3
180°	908.7	908.7	908.7	908.7	908.7

(END OF REPORT)