

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010495

Luminaire Tested: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010495
REPORT IS A COMBINATION OF REPORTS P989399 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9535.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010495

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010495

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	50	48	47
2	89	82	75	70	82	75	70	65	64	60	57	53	50	48	44	42	40
3	81	72	64	58	75	66	60	55	56	51	47	47	44	41	39	36	34
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	32	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19719	19719	19719
5°	19769	19039	19011
10°	19593	18395	18206
15°	19321	17724	17330
20°	19008	16981	16460
25°	18604	16196	15531
30°	18162	15383	14554
35°	17699	14553	13583
40°	17214	13682	12629
45°	16681	12833	11630
50°	16138	11887	10629
55°	15441	10901	9615
60°	14725	9813	8534
65°	14052	8636	7407
70°	13081	7331	6093
75°	11686	5806	4730
80°	10092	4080	3345
85°	7867	2194	1676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16681 cd/sqm

TEST NUMBER: P1010495

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.8
10°-20°	487.7	5.1
20°-30°	720.3	7.6
30°-40°	841.2	8.8
40°-50°	845.7	8.9
50°-60°	742.9	7.8
60°-70°	553.3	5.8
70°-80°	314.9	3.3
80°-90°	92.6	1.0
90°-100°	55.1	0.6
100°-110°	266.4	2.8
110°-120°	652.9	6.8
120°-130°	828.8	8.7
130°-140°	885.4	9.3
140°-150°	827.9	8.7
150°-160°	667.8	7.0
160°-170°	431.0	4.5
170°-180°	148.5	1.6
0°-30°	1380.7	14.5
0°-40°	2221.8	23.3
0°-60°	3810.4	40.0
0°-90°	4771.1	50.0
90°-120°	974.4	10.2
90°-150°	3516.6	36.9
90°-180°	4764.0	50.0
0°-180°	9535.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1832	1832	1832	1832	1832	
5°	1834	1826	1808	1824	1821	174
15°	1745	1739	1719	1731	1722	492
25°	1585	1575	1555	1556	1552	730
35°	1370	1361	1341	1331	1323	857
45°	1123	1117	1096	1078	1070	867
55°	852	851	830	813	805	763
65°	581	573	558	545	540	573
75°	307	301	296	288	284	328
85°	82	79	79	76	76	88
90°	1	13	28	32	35	10
95°	71	23	36	44	44	85
105°	346	359	254	49	51	367
115°	649	656	666	678	683	641
125°	915	924	929	931	933	817
135°	1139	1146	1150	1154	1150	877
145°	1314	1322	1325	1327	1327	823
155°	1448	1445	1447	1452	1445	667
165°	1527	1523	1522	1531	1523	431
175°	1563	1557	1558	1566	1557	149
180°	1563	1563	1563	1563	1563	

TEST NUMBER: P1010495

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.0	1832.0	1832.0	1832.0	1832.0
2.5°	1839.9	1833.6	1816.3	1832.0	1830.5
5°	1833.6	1825.7	1808.4	1824.2	1821.0
7.5°	1819.4	1811.6	1794.2	1808.4	1806.8
10°	1800.5	1792.7	1772.2	1786.4	1783.2
12.5°	1775.3	1769.0	1750.1	1759.6	1758.0
15°	1745.4	1739.1	1718.6	1731.2	1721.8
17.5°	1712.3	1704.4	1684.0	1693.4	1690.3
20°	1674.5	1665.1	1644.6	1650.9	1646.2
22.5°	1632.0	1622.5	1602.1	1606.8	1600.5
25°	1584.7	1575.3	1554.8	1556.4	1551.6
27.5°	1535.9	1526.4	1504.4	1506.0	1501.2
30°	1482.3	1474.5	1452.4	1452.4	1441.4
32.5°	1428.8	1417.7	1402.0	1391.0	1386.2
35°	1370.5	1361.0	1340.6	1331.1	1323.2
37.5°	1312.2	1299.6	1279.1	1268.1	1263.4
40°	1250.8	1241.3	1219.3	1206.7	1200.4
42.5°	1189.3	1178.3	1156.3	1143.6	1137.3
45°	1123.2	1116.9	1096.4	1077.5	1069.6
47.5°	1058.6	1049.1	1030.2	1011.3	1005.0
50°	992.4	984.5	964.1	946.7	937.3
52.5°	923.1	918.4	896.3	882.2	872.7
55°	852.2	850.6	830.2	812.8	805.0
57.5°	786.1	779.8	764.0	748.3	738.8
60°	713.6	712.0	693.1	678.9	671.1
62.5°	649.0	644.3	625.4	611.2	606.5
65°	581.3	573.4	557.6	545.0	540.3
67.5°	508.8	502.5	489.9	478.9	472.6
70°	444.2	434.8	425.3	414.3	406.4
72.5°	376.5	370.2	359.2	349.7	346.6
75°	307.2	300.9	296.2	288.3	283.5
77.5°	245.7	242.6	236.3	230.0	230.0
80°	185.9	181.2	178.0	176.4	176.4
82.5°	127.6	127.6	127.6	124.4	122.9
85°	81.9	78.8	78.8	75.6	75.6
87.5°	41.0	36.2	34.7	33.1	33.1
90°	1.2	12.8	27.9	32.5	34.8
92.5°	26.7	19.7	30.2	38.3	39.5
95°	70.8	23.2	36.0	44.1	44.1
97.5°	128.9	96.4	37.2	46.4	47.6
100°	196.2	219.4	38.3	47.6	48.8
102.5°	272.8	287.9	85.9	47.6	49.9
105°	346.0	358.7	254.3	48.8	51.1
107.5°	423.8	434.2	451.6	272.8	120.7
110°	501.5	510.8	523.6	485.3	319.3



TEST NUMBER: P1010495

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.8	584.0	596.7	607.2	604.9
115°	649.0	655.9	666.4	678.0	682.6
117.5°	721.0	729.1	734.9	744.2	745.3
120°	787.1	797.6	801.1	810.4	810.4
122.5°	854.5	862.6	867.2	873.0	874.2
125°	914.8	924.1	928.8	931.1	933.4
127.5°	975.2	984.5	990.3	993.8	991.5
130°	1030.9	1040.2	1044.9	1049.5	1047.2
132.5°	1084.3	1093.6	1097.1	1101.8	1098.3
135°	1138.9	1145.9	1150.5	1154.0	1150.5
137.5°	1185.3	1194.6	1197.0	1202.8	1200.4
140°	1231.8	1238.7	1242.2	1246.9	1244.5
142.5°	1274.7	1281.7	1285.2	1288.7	1285.2
145°	1314.2	1322.3	1324.7	1327.0	1327.0
147.5°	1352.5	1358.3	1360.6	1363.0	1357.2
150°	1387.3	1390.8	1393.2	1395.5	1392.0
152.5°	1418.7	1419.9	1421.0	1425.7	1419.9
155°	1447.7	1445.4	1446.6	1452.4	1445.4
157.5°	1470.9	1470.9	1469.8	1476.7	1467.5
160°	1491.8	1490.7	1489.5	1496.5	1488.4
162.5°	1511.6	1508.1	1506.9	1515.1	1508.1
165°	1526.7	1523.2	1522.0	1531.3	1523.2
167.5°	1539.4	1534.8	1534.8	1544.1	1534.8
170°	1549.9	1545.2	1545.2	1554.5	1545.2
172.5°	1556.8	1551.0	1552.2	1561.5	1551.0
175°	1562.7	1556.8	1558.0	1566.1	1556.8
177.5°	1565.0	1559.2	1560.3	1569.6	1558.0
180°	1562.7	1562.7	1562.7	1562.7	1562.7

(END OF REPORT)