

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010496

Luminaire Tested: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010496
REPORT IS A COMBINATION OF REPORTS P989400 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9577.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010496

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010496

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	50	48	47	47	47	42
2	89	82	75	70	82	75	70	65	64	60	57	53	50	48	44	42	40	40	40	35
3	81	72	64	58	75	66	60	55	56	51	47	47	44	41	39	36	34	34	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	32	29	29	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	25	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	22	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	20	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	18	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	16	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19807	19807	19807
5°	19856	19123	19094
10°	19680	18476	18287
15°	19406	17803	17406
20°	19092	17055	16532
25°	18686	16267	15600
30°	18242	15451	14618
35°	17776	14618	13643
40°	17290	13742	12683
45°	16754	12889	11681
50°	16209	11939	10675
55°	15510	10948	9656
60°	14789	9857	8571
65°	14113	8675	7440
70°	13140	7364	6120
75°	11735	5832	4751
80°	10136	4098	3361
85°	7905	2203	1682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16754 cd/sqm

TEST NUMBER: P1010496

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	1.8
10°-20°	489.8	5.1
20°-30°	723.4	7.6
30°-40°	844.9	8.8
40°-50°	849.4	8.9
50°-60°	746.1	7.8
60°-70°	555.7	5.8
70°-80°	316.2	3.3
80°-90°	93.0	1.0
90°-100°	55.3	0.6
100°-110°	267.6	2.8
110°-120°	655.8	6.8
120°-130°	832.5	8.7
130°-140°	889.3	9.3
140°-150°	831.6	8.7
150°-160°	670.8	7.0
160°-170°	432.9	4.5
170°-180°	149.2	1.6
0°-30°	1386.7	14.5
0°-40°	2231.6	23.3
0°-60°	3827.2	40.0
0°-90°	4792.1	50.0
90°-120°	978.7	10.2
90°-150°	3532.1	36.9
90°-180°	4785.0	50.0
0°-180°	9577.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1840	1840	1840	1840	1840	
5°	1842	1834	1816	1832	1829	175
15°	1753	1747	1726	1739	1729	494
25°	1592	1582	1562	1563	1558	733
35°	1376	1367	1346	1337	1329	861
45°	1128	1122	1101	1082	1074	871
55°	856	854	834	816	808	767
65°	584	576	560	547	543	576
75°	308	302	298	290	285	330
85°	82	79	79	76	76	88
90°	1	13	28	33	35	10
95°	71	23	36	44	44	85
105°	348	360	255	49	51	368
115°	652	659	669	681	686	644
125°	919	928	933	935	938	821
135°	1144	1151	1156	1159	1156	881
145°	1320	1328	1330	1333	1333	826
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1010496

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1848.0	1841.7	1824.3	1840.1	1838.5
5°	1841.7	1833.8	1816.4	1832.2	1829.0
7.5°	1827.5	1819.5	1802.1	1816.4	1814.8
10°	1808.5	1800.6	1780.0	1794.2	1791.1
12.5°	1783.2	1776.8	1757.8	1767.3	1765.7
15°	1753.1	1746.8	1726.2	1738.9	1729.4
17.5°	1719.9	1712.0	1691.4	1700.9	1697.7
20°	1681.9	1672.4	1651.8	1658.2	1653.4
22.5°	1639.2	1629.7	1609.1	1613.9	1607.5
25°	1591.7	1582.2	1561.6	1563.2	1558.5
27.5°	1542.7	1533.2	1511.0	1512.6	1507.8
30°	1488.9	1481.0	1458.8	1458.8	1447.7
32.5°	1435.1	1424.0	1408.2	1397.1	1392.3
35°	1376.5	1367.0	1346.5	1337.0	1329.1
37.5°	1318.0	1305.3	1284.8	1273.7	1268.9
40°	1256.3	1246.8	1224.6	1212.0	1205.6
42.5°	1194.6	1183.5	1161.3	1148.7	1142.4
45°	1128.1	1121.8	1101.2	1082.2	1074.3
47.5°	1063.2	1053.8	1034.8	1015.8	1009.5
50°	996.8	988.9	968.3	950.9	941.4
52.5°	927.2	922.4	900.3	886.0	876.5
55°	856.0	854.4	833.8	816.4	808.5
57.5°	789.5	783.2	767.4	751.6	742.1
60°	716.7	715.2	696.2	681.9	674.0
62.5°	651.9	647.1	628.1	613.9	609.2
65°	583.8	575.9	560.1	547.4	542.7
67.5°	511.1	504.7	492.1	481.0	474.7
70°	446.2	436.7	427.2	416.1	408.2
72.5°	378.1	371.8	360.7	351.3	348.1
75°	308.5	302.2	297.5	289.5	284.8
77.5°	246.8	243.7	237.3	231.0	231.0
80°	186.7	182.0	178.8	177.2	177.2
82.5°	128.2	128.2	128.2	125.0	123.4
85°	82.3	79.1	79.1	75.9	75.9
87.5°	41.1	36.4	34.8	33.2	33.2
90°	1.2	12.8	28.0	32.7	35.0
92.5°	26.8	19.8	30.3	38.5	39.6
95°	71.1	23.3	36.1	44.3	44.3
97.5°	129.4	96.8	37.3	46.6	47.8
100°	197.1	220.4	38.5	47.8	49.0
102.5°	274.0	289.2	86.3	47.8	50.1
105°	347.5	360.3	255.4	49.0	51.3
107.5°	425.6	436.1	453.6	274.0	121.3
110°	503.7	513.1	525.9	487.4	320.7



TEST NUMBER: P1010496

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	586.5	599.4	609.9	607.5
115°	651.8	658.8	669.3	681.0	685.7
117.5°	724.1	732.3	738.1	747.5	748.6
120°	790.6	801.1	804.6	813.9	813.9
122.5°	858.2	866.4	871.1	876.9	878.1
125°	918.9	928.2	932.9	935.2	937.5
127.5°	979.5	988.8	994.7	998.2	995.8
130°	1035.5	1044.8	1049.5	1054.1	1051.8
132.5°	1089.1	1098.4	1101.9	1106.6	1103.1
135°	1143.9	1150.9	1155.6	1159.1	1155.6
137.5°	1190.6	1199.9	1202.2	1208.1	1205.7
140°	1237.2	1244.2	1247.7	1252.4	1250.0
142.5°	1280.4	1287.3	1290.8	1294.3	1290.8
145°	1320.0	1328.2	1330.5	1332.8	1332.8
147.5°	1358.5	1364.3	1366.6	1369.0	1363.1
150°	1393.5	1397.0	1399.3	1401.6	1398.1
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)