

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010096

Luminaire Tested: S122RDIP-B485D925UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010096
REPORT IS A COMBINATION OF REPORTS P988416 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D925UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4776.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010096

CATALOG NUMBER: S122RDIP-B485D925UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1010096

CATALOG NUMBER: S122RDIP-B485D925UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	42	42	42	34		
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36	29		
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30	25		
3	79	70	63	57	71	63	58	53	51	47	44	40	37	35	30	28	26	22		
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19		
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	17		
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15		
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16	13		
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14	12		
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11		
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12507	12507	12507
5°	12527	11900	11810
10°	12404	11285	10913
15°	12233	10561	9890
20°	12007	9738	8820
25°	11778	8893	7840
30°	11467	8069	6770
35°	11163	7240	5852
40°	10854	6424	4907
45°	10494	5582	4082
50°	10123	4772	3322
55°	9737	3961	2638
60°	9285	3168	1996
65°	8770	2414	1623
70°	8146	1751	1290
75°	7362	1336	986
80°	6219	904	662
85°	4337	415	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10494 cd/sqm

TEST NUMBER: P1010096

CATALOG NUMBER: S122RDIP-B485D925UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	1.6
10°-20°	203.3	4.3
20°-30°	285.4	6.0
30°-40°	311.1	6.5
40°-50°	285.9	6.0
50°-60°	224.6	4.7
60°-70°	146.2	3.1
70°-80°	75.2	1.6
80°-90°	22.4	0.5
90°-100°	69.6	1.5
100°-110°	221.4	4.6
110°-120°	378.9	7.9
120°-130°	498.3	10.4
130°-140°	559.3	11.7
140°-150°	548.5	11.5
150°-160°	460.1	9.6
160°-170°	305.1	6.4
170°-180°	106.6	2.2
0°-30°	562.8	11.8
0°-40°	873.9	18.3
0°-60°	1384.4	29.0
0°-90°	1628.2	34.1
90°-120°	669.9	14.0
90°-150°	2276.0	47.7
90°-180°	3148.0	65.9
0°-180°	4776.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	787	777	784	782	75
15°	752	744	719	706	699	212
25°	682	659	612	583	572	314
35°	588	551	488	443	428	368
45°	480	433	358	307	290	371
55°	365	310	232	190	176	326
65°	247	189	124	100	98	245
75°	132	82	57	52	52	139
85°	31	16	14	14	14	35
90°	1	12	33	31	32	5
95°	49	59	61	61	59	55
105°	204	207	209	211	211	216
115°	380	386	384	383	380	376
125°	553	562	559	556	555	494
135°	715	726	728	727	724	553
145°	868	875	881	882	878	543
155°	993	996	999	1003	1000	457
165°	1080	1079	1079	1086	1081	305
175°	1124	1121	1119	1126	1120	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P1010096

CATALOG NUMBER: S122RDIP-B485D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	790.1	790.1	790.1	790.1	790.1
2.5°	793.7	790.1	782.3	789.4	788.0
5°	790.1	786.6	777.3	783.7	781.5
7.5°	783.7	779.4	769.4	772.3	768.7
10°	775.1	770.1	755.8	753.7	749.4
12.5°	764.4	758.0	738.6	734.4	726.5
15°	751.5	743.6	719.3	705.8	698.6
17.5°	736.5	725.1	695.0	679.3	667.9
20°	719.3	705.0	669.3	651.4	635.7
22.5°	700.7	684.3	642.8	618.5	607.8
25°	682.2	659.3	612.1	582.8	572.0
27.5°	660.0	635.7	583.5	549.9	533.4
30°	636.4	609.2	552.0	515.5	496.2
32.5°	613.5	580.6	522.0	479.1	461.2
35°	587.8	551.3	488.4	443.3	427.6
37.5°	562.7	523.4	456.9	407.6	389.7
40°	536.3	493.4	424.0	373.3	354.7
42.5°	509.1	463.4	391.1	338.2	320.3
45°	480.5	432.6	357.5	306.8	289.6
47.5°	453.3	402.6	325.3	274.6	258.8
50°	423.3	372.5	293.9	244.5	229.5
52.5°	394.0	340.4	263.9	216.7	203.1
55°	365.4	309.6	232.4	189.5	175.9
57.5°	336.1	278.9	204.5	164.5	153.0
60°	306.0	248.8	175.2	138.7	127.3
62.5°	276.7	219.5	150.2	115.8	110.1
65°	246.7	188.8	124.4	100.1	98.0
67.5°	218.1	160.2	100.1	88.0	85.8
70°	188.1	132.3	82.9	75.8	72.9
72.5°	159.5	106.5	69.4	63.6	62.2
75°	131.6	81.5	57.2	52.2	51.5
77.5°	103.7	57.9	45.0	42.2	40.8
80°	77.9	41.5	34.3	31.5	31.5
82.5°	54.3	27.9	23.6	22.2	22.2
85°	30.7	15.7	13.6	13.6	13.6
87.5°	11.4	5.7	5.7	5.0	5.0
90°	1.0	12.4	33.3	31.4	32.3
92.5°	20.9	28.5	29.5	30.4	30.4
95°	49.4	58.9	60.8	60.8	58.9
97.5°	82.7	91.2	95.0	95.0	95.0
100°	120.7	128.3	131.1	131.1	130.2
102.5°	160.6	166.3	170.1	171.0	170.1
105°	204.3	207.1	209.0	210.9	210.9
107.5°	248.0	251.8	251.8	252.7	248.0
110°	289.8	295.5	295.5	295.5	292.6

TEST NUMBER: P1010096

CATALOG NUMBER: S122RDIP-B485D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.4	341.1	340.1	337.3	335.4
115°	380.0	385.8	383.9	382.9	380.0
117.5°	424.7	432.3	427.6	424.7	421.9
120°	469.4	477.0	469.4	469.4	466.5
122.5°	510.2	519.7	515.0	512.1	510.2
125°	553.0	561.5	558.7	555.8	554.9
127.5°	594.8	605.2	601.4	597.6	594.8
130°	633.7	646.1	644.2	642.3	638.5
132.5°	677.4	686.9	687.9	683.1	680.3
135°	715.4	725.9	727.8	726.8	724.0
137.5°	757.2	765.8	767.7	766.8	762.9
140°	794.3	802.9	807.6	807.6	803.8
142.5°	832.3	840.9	843.7	844.7	840.9
145°	868.4	875.1	880.8	881.7	877.9
147.5°	900.7	909.3	913.1	915.0	911.2
150°	934.0	939.7	943.5	946.3	943.5
152.5°	963.4	969.1	973.9	977.7	973.9
155°	992.9	995.7	998.6	1003.3	1000.5
157.5°	1018.5	1020.4	1022.3	1029.0	1024.2
160°	1041.3	1043.2	1044.2	1049.9	1046.1
162.5°	1062.2	1062.2	1063.2	1069.8	1065.1
165°	1080.3	1079.3	1079.3	1086.0	1081.2
167.5°	1096.4	1093.6	1093.6	1100.2	1095.5
170°	1108.8	1105.9	1105.0	1111.6	1105.9
172.5°	1117.3	1114.5	1113.5	1120.2	1114.5
175°	1124.0	1121.1	1119.2	1125.9	1120.2
177.5°	1127.8	1124.9	1123.0	1128.7	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9

(END OF REPORT)