

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010505

Luminaire Tested: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010505
REPORT IS A COMBINATION OF REPORTS P989454 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6320.1 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010505

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010505

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75
1	101	96	91	87	95	91	87	83	81	78	75	72	70	67	64	62	60
2	91	83	76	70	86	78	72	67	70	65	61	62	59	55	55	52	50
3	83	72	64	58	78	69	61	55	61	55	51	55	50	46	49	45	42
4	76	64	55	49	71	61	53	47	54	48	43	49	43	39	43	39	36
5	70	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31
6	64	51	42	36	60	48	40	35	44	37	32	39	34	29	35	31	27
7	59	46	38	32	56	44	36	30	40	33	28	36	30	26	32	27	24
8	55	42	34	28	52	40	32	27	36	30	25	33	27	23	29	25	21
9	51	38	30	25	48	37	29	24	33	27	22	30	25	21	27	23	19
10	48	35	28	22	45	34	27	22	31	25	20	28	23	19	25	21	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15566	15566	15566
5°	15608	15109	15097
10°	15462	14700	14588
15°	15258	14248	14048
20°	14967	13744	13467
25°	14610	13176	12866
30°	14243	12663	12263
35°	13834	12125	11772
40°	13442	11631	11252
45°	13007	11155	10825
50°	12578	10683	10361
55°	12102	10197	9933
60°	11636	9701	9496
65°	11159	9174	8984
70°	10437	8581	8455
75°	9529	7906	7911
80°	8469	7223	7290
85°	7415	6667	6844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13007 cd/sqm

TEST NUMBER: P1010505

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.2
10°-20°	391.1	6.2
20°-30°	584.8	9.3
30°-40°	698.2	11.0
40°-50°	730.6	11.6
50°-60°	685.6	10.8
60°-70°	572.6	9.1
70°-80°	409.5	6.5
80°-90°	244.6	3.9
90°-100°	170.0	2.7
100°-110°	194.1	3.1
110°-120°	275.1	4.4
120°-130°	296.7	4.7
130°-140°	290.4	4.6
140°-150°	257.6	4.1
150°-160°	204.6	3.2
160°-170°	132.0	2.1
170°-180°	45.5	0.7
0°-30°	1113.0	17.6
0°-40°	1811.3	28.7
0°-60°	3227.4	51.1
0°-90°	4454.1	70.5
90°-120°	639.2	10.1
90°-150°	1484.0	23.5
90°-180°	1866.0	29.5
0°-180°	6320.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1446	1446	1446	1446	1446	
5°	1448	1444	1435	1448	1446	137
15°	1378	1383	1382	1397	1396	388
25°	1244	1260	1265	1285	1285	574
35°	1071	1096	1117	1140	1147	670
45°	876	914	953	983	996	675
55°	668	720	777	819	832	598
65°	462	523	592	640	655	456
75°	250	324	403	455	474	268
85°	77	156	239	293	309	79
90°	21	102	186	242	258	16
95°	39	86	167	218	234	39
105°	119	160	196	177	192	125
115°	207	228	288	329	343	205
125°	285	288	335	369	380	255
135°	352	352	371	401	408	271
145°	404	405	406	419	425	253
155°	443	443	443	445	443	204
165°	468	466	466	469	466	132
175°	479	477	477	480	477	46
180°	479	479	479	479	479	

TEST NUMBER: P1010505

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1446.1	1446.1	1446.1	1446.1	1446.1
2.5°	1454.0	1449.2	1436.6	1449.2	1447.7
5°	1447.7	1444.5	1435.1	1447.7	1446.1
7.5°	1436.6	1436.6	1427.2	1442.9	1441.4
10°	1420.9	1424.0	1416.2	1431.9	1428.8
12.5°	1402.0	1406.7	1402.0	1416.2	1413.0
15°	1378.4	1383.1	1381.5	1397.3	1395.7
17.5°	1350.0	1359.5	1357.9	1372.1	1368.9
20°	1318.5	1327.9	1331.1	1345.3	1346.8
22.5°	1285.4	1294.9	1299.6	1318.5	1316.9
25°	1244.5	1260.2	1264.9	1285.4	1285.4
27.5°	1205.1	1222.4	1231.9	1249.2	1250.8
30°	1162.5	1183.0	1195.6	1214.5	1214.5
32.5°	1115.3	1138.9	1156.2	1176.7	1181.4
35°	1071.2	1096.4	1116.9	1140.5	1146.8
37.5°	1023.9	1052.3	1075.9	1102.7	1107.4
40°	976.7	1005.0	1036.5	1063.3	1069.6
42.5°	924.7	960.9	994.0	1023.9	1033.4
45°	875.8	913.7	953.0	983.0	995.6
47.5°	823.9	866.4	910.5	943.6	953.0
50°	773.5	817.6	866.4	902.6	913.7
52.5°	719.9	767.2	822.3	860.1	874.3
55°	667.9	719.9	776.6	819.1	831.7
57.5°	617.5	671.1	732.5	775.0	789.2
60°	563.9	620.7	685.2	729.3	746.7
62.5°	513.5	571.8	641.1	685.2	701.0
65°	461.6	523.0	592.3	639.6	655.3
67.5°	409.6	474.2	543.5	595.4	608.1
70°	354.4	422.2	497.8	548.2	563.9
72.5°	304.0	371.8	450.5	502.5	518.3
75°	250.5	324.5	403.3	455.3	474.2
77.5°	204.8	278.8	357.6	412.7	426.9
80°	156.0	233.1	315.1	368.6	384.4
82.5°	113.4	192.2	275.7	329.2	345.0
85°	77.2	156.0	239.4	293.0	308.8
87.5°	47.3	126.0	206.4	259.9	275.7
90°	20.9	101.6	186.5	241.6	258.0
92.5°	27.1	92.6	174.6	229.1	243.7
95°	39.0	85.9	167.0	218.3	234.0
97.5°	55.3	102.0	157.9	208.0	224.1
100°	74.3	131.8	148.7	197.3	213.4
102.5°	96.2	144.9	153.9	186.3	202.8
105°	118.6	160.3	196.0	177.2	192.0
107.5°	140.8	177.1	247.0	234.8	202.4
110°	163.1	194.3	261.2	290.4	252.2



TEST NUMBER: P1010505

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	185.9	210.4	274.2	316.7	330.2
115°	206.7	227.7	287.6	329.0	343.0
117.5°	228.7	243.8	299.1	339.7	352.7
120°	247.4	258.5	311.5	350.6	361.6
122.5°	268.0	273.7	323.9	360.3	371.7
125°	284.9	287.7	334.9	368.7	380.4
127.5°	303.4	304.7	345.8	378.4	388.8
130°	320.4	321.8	354.7	386.0	394.7
132.5°	335.3	338.1	362.8	392.5	402.6
135°	352.0	352.5	371.3	400.7	407.5
137.5°	366.2	367.5	379.2	406.2	413.4
140°	378.9	381.0	386.8	411.8	419.0
142.5°	392.0	392.5	393.6	415.2	422.0
145°	404.1	405.0	405.7	419.0	425.3
147.5°	414.2	416.0	416.7	422.1	426.7
150°	424.9	426.0	426.7	427.4	429.5
152.5°	434.5	434.9	435.2	436.6	434.9
155°	443.4	442.7	443.0	444.8	442.7
157.5°	450.5	450.5	450.2	452.3	449.4
160°	456.9	456.6	456.2	458.3	455.8
162.5°	463.0	461.9	461.5	464.0	461.9
165°	467.6	466.5	466.2	469.0	466.5
167.5°	471.5	470.1	470.1	472.9	470.1
170°	474.7	473.3	473.3	476.1	473.3
172.5°	476.8	475.0	475.4	478.2	475.0
175°	478.6	476.8	477.2	479.7	476.8
177.5°	479.3	477.5	477.9	480.7	477.2
180°	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)