

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010109

Luminaire Tested: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010109
REPORT IS A COMBINATION OF REPORTS P988439 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6544.8 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010109

CATALOG NUMBER: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1010109

CATALOG NUMBER: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36	36	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31	31	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26	26	26
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23	23	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20	20	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17	17	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15	15	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14	14	14
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12	12	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11	11	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10	10	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17949	17949	17949
5°	17978	17076	16950
10°	17800	16195	15661
15°	17557	15156	14192
20°	17232	13974	12656
25°	16900	12761	11251
30°	16456	11581	9716
35°	16019	10390	8398
40°	15576	9219	7042
45°	15061	8012	5858
50°	14527	6847	4769
55°	13973	5684	3785
60°	13327	4545	2865
65°	12584	3464	2329
70°	11689	2513	1852
75°	10562	1918	1414
80°	8934	1299	950
85°	6229	595	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15061 cd/sqm

TEST NUMBER: P1010109

CATALOG NUMBER: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	1.6
10°-20°	291.7	4.5
20°-30°	409.6	6.3
30°-40°	446.5	6.8
40°-50°	410.3	6.3
50°-60°	322.3	4.9
60°-70°	209.8	3.2
70°-80°	108.0	1.6
80°-90°	31.4	0.5
90°-100°	244.7	3.7
100°-110°	827.3	12.6
110°-120°	869.6	13.3
120°-130°	715.1	10.9
130°-140°	574.7	8.8
140°-150°	434.1	6.6
150°-160°	305.2	4.7
160°-170°	179.7	2.7
170°-180°	58.5	0.9
0°-30°	807.6	12.3
0°-40°	1254.0	19.2
0°-60°	1986.6	30.4
0°-90°	2335.8	35.7
90°-120°	1941.7	29.7
90°-150°	3665.6	56.0
90°-180°	4209.0	64.3
0°-180°	6544.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1134	1134	1134	1134	1134	
5°	1134	1129	1115	1125	1122	108
15°	1078	1067	1032	1013	1002	304
25°	979	946	878	836	821	450
35°	844	791	701	636	614	528
45°	690	621	513	440	416	533
55°	524	444	334	272	252	469
65°	354	271	178	144	141	351
75°	189	117	82	75	74	200
85°	44	23	20	20	20	51
90°	1	16	40	38	38	5
95°	41	100	455	172	132	42
105°	142	214	860	1538	1308	150
115°	250	315	720	1485	1722	248
125°	348	412	692	1203	1397	310
135°	409	488	684	1011	1158	316
145°	467	536	680	845	924	293
155°	531	573	661	747	777	244
165°	578	596	633	671	682	163
175°	602	603	608	616	614	57
180°	604	604	604	604	604	

TEST NUMBER: P1010109

CATALOG NUMBER: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1133.9	1133.9	1133.9	1133.9	1133.9
2.5°	1139.0	1133.9	1122.6	1132.9	1130.8
5°	1133.9	1128.8	1115.4	1124.7	1121.6
7.5°	1124.7	1118.5	1104.1	1108.2	1103.1
10°	1112.3	1105.2	1084.6	1081.6	1075.4
12.5°	1097.0	1087.7	1060.0	1053.9	1042.6
15°	1078.5	1067.2	1032.3	1012.8	1002.5
17.5°	1056.9	1040.5	997.4	974.8	958.4
20°	1032.3	1011.8	960.5	934.8	912.2
22.5°	1005.6	982.0	922.5	887.6	872.2
25°	978.9	946.1	878.4	836.3	820.9
27.5°	947.1	912.2	837.3	789.1	765.5
30°	913.3	874.3	792.2	739.9	712.1
32.5°	880.4	833.2	749.1	687.5	661.9
35°	843.5	791.2	700.9	636.2	613.6
37.5°	807.6	751.1	655.7	584.9	559.3
40°	769.6	708.0	608.5	535.6	509.0
42.5°	730.6	664.9	561.3	485.4	459.7
45°	689.6	620.8	513.1	440.2	415.6
47.5°	650.6	577.7	466.9	394.0	371.5
50°	607.5	534.6	421.7	350.9	329.4
52.5°	565.4	488.4	378.6	310.9	291.4
55°	524.4	444.3	333.5	271.9	252.4
57.5°	482.3	400.2	293.5	236.0	219.6
60°	439.2	357.1	251.4	199.1	182.7
62.5°	397.1	315.0	215.5	166.2	158.0
65°	354.0	270.9	178.5	143.7	140.6
67.5°	313.0	229.9	143.7	126.2	123.1
70°	269.9	189.8	119.0	108.8	104.7
72.5°	228.8	152.9	99.5	91.3	89.3
75°	188.8	117.0	82.1	74.9	73.9
77.5°	148.8	83.1	64.6	60.5	58.5
80°	111.9	59.5	49.3	45.2	45.2
82.5°	78.0	40.0	33.9	31.8	31.8
85°	44.1	22.6	19.5	19.5	19.5
87.5°	16.4	8.2	8.2	7.2	7.2
90°	1.2	15.6	39.5	37.8	38.3
92.5°	17.4	55.2	178.8	82.4	70.8
95°	40.6	99.8	455.1	171.8	132.3
97.5°	60.4	131.8	741.8	344.8	221.7
100°	89.4	161.4	917.1	686.7	415.6
102.5°	116.1	188.0	923.0	1161.0	810.3
105°	141.6	213.6	860.3	1537.6	1308.4
107.5°	169.5	239.2	802.2	1674.1	1643.9
110°	197.4	265.2	762.7	1652.0	1780.9

TEST NUMBER: P1010109

CATALOG NUMBER: S122RDIP-B675D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.9	290.2	737.2	1577.1	1778.6
115°	249.6	315.2	719.8	1485.4	1721.7
117.5°	277.5	340.2	710.5	1397.8	1635.8
120°	303.0	364.6	702.4	1319.4	1553.3
122.5°	327.4	389.5	697.7	1258.4	1467.4
125°	348.3	412.2	691.9	1203.4	1396.6
127.5°	365.7	433.6	688.4	1156.3	1330.4
130°	380.8	452.8	686.1	1108.7	1275.9
132.5°	394.7	471.4	685.0	1059.4	1219.0
135°	408.7	487.6	683.8	1011.2	1157.5
137.5°	421.4	501.5	683.8	962.4	1098.3
140°	436.5	514.3	682.6	919.4	1036.7
142.5°	451.6	524.8	682.6	878.2	975.2
145°	466.7	536.4	680.3	844.6	924.1
147.5°	483.0	545.6	676.8	815.0	878.8
150°	499.2	555.0	673.3	789.4	839.4
152.5°	515.5	564.2	667.5	768.0	805.7
155°	530.6	572.9	660.6	747.1	776.7
157.5°	543.3	579.8	653.6	727.4	751.1
160°	556.1	586.8	646.6	707.6	726.8
162.5°	568.9	592.0	640.8	689.0	703.5
165°	578.2	595.6	632.7	671.0	681.5
167.5°	586.3	599.0	625.7	654.8	660.6
170°	594.4	600.8	619.9	639.6	642.0
172.5°	599.0	602.6	613.0	626.3	626.9
175°	602.5	603.1	608.3	615.9	614.1
177.5°	604.9	603.7	603.7	608.3	604.9
180°	603.7	603.7	603.7	603.7	603.7

(END OF REPORT)