

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010511

Luminaire Tested: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010511
REPORT IS A COMBINATION OF REPORTS P989460 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6255.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010511

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010511

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81			77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	69	68			64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57			54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49			46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42			39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37			34
6	67	54	46	40	64	52	44	38	48	41	36	44	39	34	41	36	32			30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29			26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26			24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23			21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	25	21			19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19807	19807	19807
5°	19856	19123	19094
10°	19680	18476	18287
15°	19406	17803	17406
20°	19092	17055	16532
25°	18686	16267	15600
30°	18242	15451	14618
35°	17776	14618	13643
40°	17290	13742	12683
45°	16754	12889	11681
50°	16209	11939	10675
55°	15510	10948	9656
60°	14789	9857	8571
65°	14113	8675	7440
70°	13140	7364	6120
75°	11735	5832	4751
80°	10136	4098	3361
85°	7905	2203	1682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16754 cd/sqm

TEST NUMBER: P1010511

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	2.8
10°-20°	489.8	7.8
20°-30°	723.4	11.6
30°-40°	844.9	13.5
40°-50°	849.4	13.6
50°-60°	746.1	11.9
60°-70°	555.7	8.9
70°-80°	316.2	5.1
80°-90°	90.9	1.5
90°-100°	16.9	0.3
100°-110°	81.9	1.3
110°-120°	200.8	3.2
120°-130°	254.9	4.1
130°-140°	272.3	4.4
140°-150°	254.6	4.1
150°-160°	205.4	3.3
160°-170°	132.5	2.1
170°-180°	45.7	0.7
0°-30°	1386.7	22.2
0°-40°	2231.6	35.7
0°-60°	3827.2	61.2
0°-90°	4790.0	76.6
90°-120°	299.6	4.8
90°-150°	1081.4	17.3
90°-180°	1465.0	23.4
0°-180°	6255.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1840	1840	1840	1840	1840	
5°	1842	1834	1816	1832	1829	175
15°	1753	1747	1726	1739	1729	494
25°	1592	1582	1562	1563	1558	733
35°	1376	1367	1346	1337	1329	861
45°	1128	1122	1101	1082	1074	871
55°	856	854	834	816	808	767
65°	584	576	560	547	543	576
75°	308	302	298	290	285	330
85°	82	79	79	76	76	88
90°	0	4	9	10	11	7
95°	22	7	11	14	14	26
105°	106	110	78	15	16	113
115°	200	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	270
145°	404	407	407	408	408	253
155°	445	444	445	447	444	205
165°	470	468	468	471	468	133
175°	481	479	479	482	479	46
180°	481	481	481	481	481	

TEST NUMBER: P1010511

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1848.0	1841.7	1824.3	1840.1	1838.5
5°	1841.7	1833.8	1816.4	1832.2	1829.0
7.5°	1827.5	1819.5	1802.1	1816.4	1814.8
10°	1808.5	1800.6	1780.0	1794.2	1791.1
12.5°	1783.2	1776.8	1757.8	1767.3	1765.7
15°	1753.1	1746.8	1726.2	1738.9	1729.4
17.5°	1719.9	1712.0	1691.4	1700.9	1697.7
20°	1681.9	1672.4	1651.8	1658.2	1653.4
22.5°	1639.2	1629.7	1609.1	1613.9	1607.5
25°	1591.7	1582.2	1561.6	1563.2	1558.5
27.5°	1542.7	1533.2	1511.0	1512.6	1507.8
30°	1488.9	1481.0	1458.8	1458.8	1447.7
32.5°	1435.1	1424.0	1408.2	1397.1	1392.3
35°	1376.5	1367.0	1346.5	1337.0	1329.1
37.5°	1318.0	1305.3	1284.8	1273.7	1268.9
40°	1256.3	1246.8	1224.6	1212.0	1205.6
42.5°	1194.6	1183.5	1161.3	1148.7	1142.4
45°	1128.1	1121.8	1101.2	1082.2	1074.3
47.5°	1063.2	1053.8	1034.8	1015.8	1009.5
50°	996.8	988.9	968.3	950.9	941.4
52.5°	927.2	922.4	900.3	886.0	876.5
55°	856.0	854.4	833.8	816.4	808.5
57.5°	789.5	783.2	767.4	751.6	742.1
60°	716.7	715.2	696.2	681.9	674.0
62.5°	651.9	647.1	628.1	613.9	609.2
65°	583.8	575.9	560.1	547.4	542.7
67.5°	511.1	504.7	492.1	481.0	474.7
70°	446.2	436.7	427.2	416.1	408.2
72.5°	378.1	371.8	360.7	351.3	348.1
75°	308.5	302.2	297.5	289.5	284.8
77.5°	246.8	243.7	237.3	231.0	231.0
80°	186.7	182.0	178.8	177.2	177.2
82.5°	128.2	128.2	128.2	125.0	123.4
85°	82.3	79.1	79.1	75.9	75.9
87.5°	41.1	36.4	34.8	33.2	33.2
90°	0.4	3.9	8.6	10.0	10.7
92.5°	8.2	6.1	9.3	11.8	12.1
95°	21.8	7.1	11.1	13.6	13.6
97.5°	39.6	29.6	11.4	14.3	14.6
100°	60.3	67.5	11.8	14.6	15.0
102.5°	83.9	88.5	26.4	14.6	15.4
105°	106.4	110.3	78.2	15.0	15.7
107.5°	130.3	133.5	138.9	83.9	37.1
110°	154.2	157.1	161.0	149.2	98.2

TEST NUMBER: P1010511

CATALOG NUMBER: S123DIP-B1165D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.6	183.5	186.7	186.0
115°	199.6	201.7	204.9	208.5	209.9
117.5°	221.7	224.2	226.0	228.9	229.2
120°	242.1	245.3	246.4	249.2	249.2
122.5°	262.8	265.3	266.7	268.5	268.8
125°	281.3	284.2	285.6	286.3	287.1
127.5°	299.9	302.8	304.5	305.6	304.9
130°	317.0	319.9	321.3	322.8	322.0
132.5°	333.5	336.3	337.4	338.8	337.8
135°	350.2	352.4	353.8	354.9	353.8
137.5°	364.5	367.4	368.1	369.9	369.2
140°	378.8	381.0	382.0	383.5	382.7
142.5°	392.0	394.2	395.2	396.3	395.2
145°	404.2	406.7	407.4	408.1	408.1
147.5°	415.9	417.7	418.4	419.2	417.4
150°	426.7	427.7	428.4	429.2	428.1
152.5°	436.3	436.6	437.0	438.4	436.6
155°	445.2	444.5	444.9	446.6	444.5
157.5°	452.4	452.4	452.0	454.1	451.3
160°	458.8	458.4	458.1	460.2	457.7
162.5°	464.9	463.8	463.4	465.9	463.8
165°	469.5	468.4	468.1	470.9	468.4
167.5°	473.4	472.0	472.0	474.9	472.0
170°	476.6	475.2	475.2	478.1	475.2
172.5°	478.8	477.0	477.4	480.2	477.0
175°	480.6	478.8	479.1	481.6	478.8
177.5°	481.3	479.5	479.8	482.7	479.1
180°	480.6	480.6	480.6	480.6	480.6

(END OF REPORT)