

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010185

Luminaire Tested: S122RDIP-B675D530UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010185
REPORT IS A COMBINATION OF REPORTS P988537 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D530UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4236.2 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010185

CATALOG NUMBER: S122RDIP-B675D530UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1010185

CATALOG NUMBER: S122RDIP-B675D530UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51
2	91	83	77	73	84	78	72	68	67	63	59	56	54	51	47	45	43
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17256	17256	17256
5°	17284	16417	16295
10°	17114	15571	15057
15°	16879	14572	13645
20°	16568	13435	12168
25°	16249	12269	10817
30°	15820	11133	9342
35°	15400	9988	8075
40°	14975	8863	6769
45°	14480	7703	5632
50°	13965	6584	4585
55°	13432	5464	3640
60°	12811	4370	2754
65°	12101	3332	2239
70°	11238	2416	1780
75°	10153	1843	1359
80°	8583	1249	912
85°	5989	570	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14480 cd/sqm

TEST NUMBER: P1010185

CATALOG NUMBER: S122RDIP-B675D530UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.2	2.4
10°-20°	280.5	6.6
20°-30°	393.8	9.3
30°-40°	429.2	10.1
40°-50°	394.5	9.3
50°-60°	309.8	7.3
60°-70°	201.7	4.8
70°-80°	103.8	2.5
80°-90°	28.3	0.7
90°-100°	115.8	2.7
100°-110°	391.6	9.2
110°-120°	411.7	9.7
120°-130°	338.5	8.0
130°-140°	272.0	6.4
140°-150°	205.5	4.9
150°-160°	144.5	3.4
160°-170°	85.1	2.0
170°-180°	27.7	0.7
0°-30°	776.4	18.3
0°-40°	1205.7	28.5
0°-60°	1910.0	45.1
0°-90°	2243.8	53.0
90°-120°	919.2	21.7
90°-150°	1735.2	41.0
90°-180°	1992.0	47.0
0°-180°	4236.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1090	1085	1072	1081	1078	103
15°	1037	1026	992	974	964	292
25°	941	910	844	804	789	433
35°	811	761	674	612	590	508
45°	663	597	493	423	400	512
55°	504	427	321	261	243	450
65°	340	260	172	138	135	337
75°	182	112	79	72	71	192
85°	42	22	19	19	19	49
90°	0	7	19	18	18	3
95°	19	47	215	81	63	20
105°	67	101	407	728	619	71
115°	118	149	341	703	815	117
125°	165	195	328	570	661	147
135°	193	231	324	479	548	149
145°	221	254	322	400	438	139
155°	251	271	313	354	368	116
165°	274	282	300	318	323	77
175°	285	286	288	292	291	27
180°	286	286	286	286	286	

TEST NUMBER: P1010185

CATALOG NUMBER: S122RDIP-B675D530UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.1	1090.1	1090.1	1090.1	1090.1
2.5°	1095.1	1090.1	1079.3	1089.1	1087.2
5°	1090.1	1085.2	1072.4	1081.3	1078.3
7.5°	1081.3	1075.3	1061.5	1065.5	1060.5
10°	1069.4	1062.5	1042.8	1039.8	1033.9
12.5°	1054.6	1045.7	1019.1	1013.2	1002.3
15°	1036.9	1026.0	992.5	973.7	963.9
17.5°	1016.1	1000.4	958.9	937.2	921.4
20°	992.5	972.7	923.4	898.7	877.0
22.5°	966.8	944.1	886.9	853.4	838.6
25°	941.2	909.6	844.5	804.0	789.2
27.5°	910.6	877.0	805.0	758.7	736.0
30°	878.0	840.5	761.6	711.3	684.7
32.5°	846.5	801.1	720.2	661.0	636.3
35°	810.9	760.6	673.8	611.7	590.0
37.5°	776.4	722.2	630.4	562.3	537.7
40°	739.9	680.7	585.0	515.0	489.3
42.5°	702.4	639.3	539.6	466.6	442.0
45°	663.0	596.9	493.3	423.2	399.6
47.5°	625.5	555.4	448.9	378.8	357.1
50°	584.0	514.0	405.5	337.4	316.7
52.5°	543.6	469.6	364.0	298.9	280.2
55°	504.1	427.2	320.6	261.4	242.7
57.5°	463.7	384.8	282.2	226.9	211.1
60°	422.2	343.3	241.7	191.4	175.6
62.5°	381.8	302.9	207.2	159.8	151.9
65°	340.4	260.4	171.7	138.1	135.2
67.5°	300.9	221.0	138.1	121.3	118.4
70°	259.5	182.5	114.4	104.6	100.6
72.5°	220.0	147.0	95.7	87.8	85.8
75°	181.5	112.5	78.9	72.0	71.0
77.5°	143.0	79.9	62.2	58.2	56.2
80°	107.5	57.2	47.4	43.4	43.4
82.5°	75.0	38.5	32.6	30.6	30.6
85°	42.4	21.7	18.7	18.7	18.7
87.5°	15.8	7.9	7.9	6.9	6.9
90°	0.5	7.4	18.7	17.8	18.1
92.5°	8.2	26.1	84.6	39.0	33.5
95°	19.2	47.3	215.4	81.4	62.7
97.5°	28.6	62.4	351.2	163.2	105.0
100°	42.3	76.4	434.2	325.0	196.7
102.5°	55.0	89.0	436.9	549.6	383.6
105°	67.0	101.1	407.2	727.9	619.4
107.5°	80.2	113.2	379.8	792.5	778.2
110°	93.4	125.6	361.1	782.0	843.0



TEST NUMBER: P1010185

CATALOG NUMBER: S122RDIP-B675D530UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.5	137.4	349.0	746.6	841.9
115°	118.2	149.2	340.7	703.2	815.0
117.5°	131.3	161.0	336.3	661.7	774.3
120°	143.4	172.6	332.5	624.6	735.3
122.5°	155.0	184.4	330.3	595.8	694.7
125°	164.9	195.1	327.5	569.6	661.1
127.5°	173.1	205.2	325.9	547.4	629.8
130°	180.3	214.3	324.8	524.8	604.0
132.5°	186.9	223.1	324.2	501.4	577.1
135°	193.4	230.8	323.7	478.7	547.9
137.5°	199.5	237.4	323.7	455.6	519.9
140°	206.6	243.4	323.1	435.3	490.8
142.5°	213.8	248.4	323.1	415.8	461.6
145°	220.9	253.9	322.0	399.8	437.5
147.5°	228.6	258.3	320.4	385.8	416.0
150°	236.3	262.6	318.8	373.8	397.3
152.5°	244.0	267.1	316.0	363.5	381.4
155°	251.2	271.2	312.7	353.6	367.7
157.5°	257.2	274.5	309.4	344.3	355.6
160°	263.2	277.8	306.1	335.0	344.0
162.5°	269.3	280.3	303.4	326.2	333.0
165°	273.7	282.0	299.5	317.7	322.6
167.5°	277.5	283.6	296.2	310.0	312.7
170°	281.4	284.4	293.5	302.8	303.9
172.5°	283.6	285.2	290.2	296.5	296.8
175°	285.2	285.5	288.0	291.6	290.7
177.5°	286.3	285.8	285.8	288.0	286.3
180°	285.8	285.8	285.8	285.8	285.8

(END OF REPORT)