

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010544

Luminaire Tested: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010544
REPORT IS A COMBINATION OF REPORTS P989628 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5424.0 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29
2	84	77	71	67	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	68	61	55	50	48	44	40	35	33	30	24	22	21
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	20	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16
6	59	48	40	35	53	43	36	31	34	29	26	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4997	4997	4997	4997
5°	4999	5757	5014	4297
10°	4968	6966	4973	3752
15°	4899	8262	4939	3377
20°	4840	9512	4850	3108
25°	4752	9752	4763	2967
30°	4690	8057	4690	2875
35°	4612	5388	4583	2793
40°	4520	3889	4463	2669
45°	4402	3081	4276	2514
50°	4117	2616	3971	2362
55°	3807	2299	3651	2192
60°	3489	2002	3304	2013
65°	3143	1714	2990	1775
70°	2783	1423	2597	1498
75°	2377	1073	2225	1156
80°	1878	717	1732	759
85°	1297	328	1037	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8059 cd/sqm

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	0.8
10°-20°	146.6	2.7
20°-30°	246.7	4.5
30°-40°	278.8	5.1
40°-50°	249.7	4.6
50°-60°	201.6	3.7
60°-70°	140.5	2.6
70°-80°	73.7	1.4
80°-90°	20.3	0.4
90°-100°	46.5	0.9
100°-110°	224.8	4.1
110°-120°	551.0	10.2
120°-130°	699.5	12.9
130°-140°	747.2	13.8
140°-150°	698.7	12.9
150°-160°	563.6	10.4
160°-170°	363.7	6.7
170°-180°	125.3	2.3
0°-30°	439.0	8.1
0°-40°	717.8	13.2
0°-60°	1169.1	21.6
0°-90°	1403.6	25.9
90°-120°	822.3	15.2
90°-150°	2967.7	54.7
90°-180°	4020.0	74.1
0°-180°	5424.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	464	464	464	464	464	
5°	464	552	465	412	464	44
15°	443	821	446	336	443	125
25°	405	974	406	296	405	187
35°	357	525	355	272	357	224
45°	296	283	288	231	296	227
55°	210	192	202	184	210	188
65°	130	125	124	130	130	129
75°	62	64	58	69	62	67
85°	14	15	11	14	14	16
90°	1	29	1	29	1	4
95°	60	37	60	37	60	71
105°	292	43	292	43	292	310
115°	548	576	548	576	548	541
125°	772	788	772	788	772	690
135°	961	971	961	971	961	740
145°	1109	1120	1109	1120	1109	694
155°	1222	1220	1222	1220	1222	563
165°	1288	1286	1288	1286	1288	364
175°	1319	1314	1319	1314	1319	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	465.5	469.1	470.9	473.6	476.3	480.4	481.7	484.0	483.1	484.9	485.8
5°	463.7	470.0	475.4	482.2	488.5	493.0	497.5	504.7	510.1	511.0	515.0
7.5°	460.6	469.6	479.0	488.5	500.6	507.8	515.9	525.8	533.9	547.0	551.9
10°	456.5	469.1	482.6	495.7	512.3	523.6	533.5	550.1	566.7	580.2	592.8
12.5°	450.2	466.0	483.5	502.9	524.5	537.5	551.0	573.0	598.2	618.9	632.4
15°	442.6	462.4	484.9	505.6	529.4	553.7	568.1	592.8	628.8	648.2	682.8
17.5°	436.3	456.5	479.0	511.4	543.8	568.1	578.4	623.9	648.6	681.0	720.1
20°	426.4	452.0	480.8	513.2	555.0	569.9	591.0	636.9	667.5	709.8	757.9
22.5°	416.1	443.5	478.1	511.9	558.6	574.4	603.2	639.6	688.2	730.0	783.1
25°	404.8	434.5	469.6	509.6	555.5	578.4	605.4	650.4	703.0	755.7	804.7
27.5°	393.6	426.0	462.4	502.4	547.0	573.9	600.9	647.7	715.2	772.3	834.8
30°	382.8	415.2	451.6	492.5	539.3	565.4	591.0	649.5	724.6	788.9	851.9
32.5°	371.1	404.4	442.6	476.8	524.0	551.9	580.7	649.5	730.5	798.8	856.4
35°	357.1	391.3	424.2	458.3	505.1	536.2	568.5	645.0	735.9	802.0	837.5
37.5°	343.6	373.8	402.1	435.4	484.4	517.7	555.0	639.6	733.2	788.5	798.4
40°	328.4	358.5	381.4	412.5	464.2	502.9	540.7	632.4	721.5	756.6	727.8
42.5°	313.5	337.3	357.1	387.3	443.5	481.3	522.2	619.4	698.5	705.7	641.0
45°	296.4	313.5	331.1	365.2	421.0	459.7	505.1	600.5	661.7	641.0	559.1
47.5°	274.4	289.7	309.0	340.5	397.2	437.2	480.4	576.2	608.1	564.9	475.4
50°	253.2	266.3	284.3	314.9	372.0	411.1	457.0	538.0	553.7	485.8	409.8
52.5°	232.1	242.0	259.5	290.1	347.2	385.0	426.9	498.8	489.8	417.0	349.5
55°	210.1	218.6	235.2	265.4	318.5	354.4	394.5	450.7	427.3	358.0	304.1
57.5°	188.5	197.5	214.6	239.7	289.7	324.8	356.7	400.8	365.7	310.4	262.7
60°	169.1	176.8	189.8	214.6	260.0	288.3	317.6	347.7	318.5	264.9	228.5
62.5°	148.9	156.1	168.2	190.7	229.8	255.0	278.4	303.2	270.8	231.6	199.3
65°	130.0	135.8	147.1	167.8	199.7	220.4	239.3	256.4	230.3	194.3	170.0
67.5°	112.9	117.8	127.3	145.7	172.7	187.6	202.9	217.3	195.2	166.4	145.7
70°	94.5	98.5	107.1	120.5	142.1	157.4	168.7	179.5	159.7	136.7	122.8
72.5°	78.3	82.3	87.7	101.7	116.5	125.9	138.1	143.9	132.7	113.8	99.9
75°	62.5	65.7	70.6	79.6	93.6	99.9	107.5	112.0	101.7	89.1	80.5
77.5°	49.0	50.4	54.0	60.3	69.7	76.9	82.8	85.5	78.3	70.2	63.0
80°	34.6	36.4	39.1	44.5	51.7	54.0	57.6	60.7	56.2	49.0	44.5
82.5°	22.9	25.2	26.5	28.8	33.3	36.0	36.9	39.6	35.5	32.8	31.0
85°	13.5	14.4	14.8	16.2	18.4	19.8	21.1	21.6	20.7	20.2	18.4
87.5°	6.7	6.7	6.7	7.6	8.1	9.0	9.4	9.4	9.4	9.0	8.5
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.0	17.9	20.7	23.5
92.5°	22.5	21.2	19.9	18.6	17.3	16.7	17.7	19.6	21.6	23.5	25.5
95°	59.8	50.9	41.9	33.0	24.1	19.6	20.8	23.2	25.6	28.0	30.4
97.5°	108.8	102.7	96.6	90.5	84.4	81.3	75.8	64.7	53.6	42.5	31.4
100°	165.6	170.0	174.3	178.7	183.0	185.2	168.2	134.2	100.3	66.3	32.3
102.5°	230.2	233.0	235.9	238.7	241.6	243.0	224.1	186.2	148.3	110.4	72.5
105°	292.0	294.4	296.8	299.1	301.5	302.7	292.9	273.3	253.8	234.2	214.6
107.5°	357.6	359.6	361.5	363.5	365.4	366.4	368.0	371.3	374.6	377.8	381.1
110°	423.3	425.0	426.8	428.5	430.2	431.1	432.3	434.7	437.1	439.5	441.9

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	486.0	487.5	489.0	490.5	492.0	492.8	494.0	496.4	498.8	501.2	503.6
115°	547.7	549.0	550.3	551.6	552.9	553.6	554.6	556.5	558.5	560.4	562.4
117.5°	608.4	609.9	611.5	613.0	614.5	615.3	615.8	616.9	618.0	619.1	620.2
120°	664.3	666.3	668.2	670.2	672.1	673.1	673.4	674.1	674.7	675.4	676.0
122.5°	721.1	722.6	724.2	725.7	727.2	728.0	728.4	729.3	730.2	731.0	731.9
125°	772.1	773.8	775.6	777.3	779.0	779.9	780.3	781.2	782.1	782.9	783.8
127.5°	823.0	824.7	826.5	828.2	829.9	830.8	831.3	832.4	833.5	834.6	835.7
130°	870.0	871.8	873.5	875.3	877.0	877.9	878.3	879.2	880.1	880.9	881.8
132.5°	915.1	916.8	918.6	920.3	922.0	922.9	923.2	923.9	924.6	925.2	925.9
135°	961.2	962.5	963.8	965.1	966.4	967.0	967.4	968.3	969.2	970.0	970.9
137.5°	1000.3	1002.1	1003.8	1005.6	1007.3	1008.2	1008.4	1008.8	1009.3	1009.7	1010.1
140°	1039.5	1040.8	1042.1	1043.4	1044.7	1045.4	1045.7	1046.4	1047.0	1047.7	1048.3
142.5°	1075.8	1077.1	1078.4	1079.7	1081.0	1081.7	1082.0	1082.7	1083.3	1084.0	1084.6
145°	1109.1	1110.6	1112.2	1113.7	1115.2	1116.0	1116.2	1116.6	1117.1	1117.5	1117.9
147.5°	1141.4	1142.5	1143.6	1144.7	1145.8	1146.3	1146.5	1147.0	1147.4	1147.9	1148.3
150°	1170.8	1171.5	1172.1	1172.8	1173.5	1173.8	1174.0	1174.4	1174.9	1175.3	1175.7
152.5°	1197.3	1197.5	1197.7	1198.0	1198.2	1198.3	1198.4	1198.6	1198.8	1199.0	1199.2
155°	1221.8	1221.4	1220.9	1220.5	1220.0	1219.8	1219.9	1220.1	1220.4	1220.6	1220.8
157.5°	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.3	1241.1	1240.8	1240.6	1240.4
160°	1259.0	1258.8	1258.6	1258.3	1258.1	1258.0	1257.9	1257.7	1257.4	1257.2	1257.0
162.5°	1275.7	1275.0	1274.4	1273.7	1273.0	1272.7	1272.6	1272.4	1272.1	1271.9	1271.7
165°	1288.4	1287.8	1287.1	1286.5	1285.8	1285.5	1285.4	1285.2	1284.9	1284.7	1284.5
167.5°	1299.2	1298.3	1297.5	1296.6	1295.7	1295.3	1295.3	1295.3	1295.3	1295.3	1295.3
170°	1308.0	1307.1	1306.3	1305.4	1304.5	1304.1	1304.1	1304.1	1304.1	1304.1	1304.1
172.5°	1313.9	1312.8	1311.7	1310.6	1309.5	1309.0	1309.1	1309.3	1309.5	1309.7	1309.9
175°	1318.8	1317.7	1316.6	1315.5	1314.4	1313.9	1314.0	1314.2	1314.4	1314.6	1314.8
177.5°	1320.7	1319.6	1318.5	1317.4	1316.3	1315.8	1315.9	1316.1	1316.4	1316.6	1316.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	488.9	489.8	493.0	495.2	499.7	499.3	499.3	498.8	497.5	499.7	501.1
5°	523.1	530.8	531.7	541.6	542.0	546.1	548.8	546.5	551.9	551.5	547.4
7.5°	565.4	575.7	580.7	590.1	600.9	598.2	608.6	610.4	609.5	614.0	617.1
10°	611.7	629.7	642.3	659.9	664.3	667.0	673.8	679.6	691.3	682.3	688.2
12.5°	664.8	677.8	694.5	722.4	736.3	745.3	748.5	752.5	760.6	755.7	756.1
15°	709.3	726.9	755.2	789.8	793.9	805.1	802.4	826.7	838.4	820.9	830.8
17.5°	755.7	779.0	812.8	842.9	860.0	867.7	874.9	898.2	897.3	894.6	896.9
20°	785.3	823.6	865.4	905.4	910.4	916.2	935.6	945.5	943.7	951.3	956.3
22.5°	827.2	867.7	912.2	938.7	950.0	956.7	972.0	978.3	981.0	982.8	979.7
25°	862.3	905.4	938.3	961.7	968.4	972.0	977.0	978.8	977.4	974.3	977.0
27.5°	886.1	920.7	943.2	954.0	950.4	944.6	935.1	928.8	914.9	908.1	916.2
30°	896.0	911.3	918.0	900.0	882.1	867.7	849.7	816.4	790.3	797.9	787.6
32.5°	880.3	870.4	838.0	791.6	777.7	754.3	703.5	664.3	665.7	645.0	653.6
35°	833.9	788.9	727.8	657.6	639.2	626.6	570.8	562.2	544.3	524.9	530.3
37.5°	752.1	686.4	612.2	560.4	533.0	505.6	474.1	455.2	444.4	436.3	442.6
40°	652.2	572.1	511.0	464.6	441.3	423.7	402.1	383.2	371.1	369.7	372.0
42.5°	554.1	486.7	430.5	386.4	378.7	358.0	344.1	329.3	325.7	319.8	323.0
45°	469.1	414.3	367.9	331.9	323.0	317.6	300.5	291.0	287.0	283.4	288.8
47.5°	407.5	349.9	316.2	294.6	285.6	276.6	267.2	260.9	257.7	258.2	257.7
50°	348.1	305.9	276.2	259.5	254.1	247.8	240.2	236.1	234.8	230.7	233.9
52.5°	299.6	269.0	248.3	232.5	228.5	224.0	217.7	215.5	212.3	211.4	211.4
55°	260.4	236.6	220.0	209.6	204.7	201.1	197.5	194.8	192.5	192.5	192.5
57.5°	229.8	209.2	197.0	188.0	186.2	182.6	178.6	178.6	175.4	175.0	176.3
60°	203.8	185.3	175.9	168.2	165.5	164.6	160.6	160.6	159.7	157.4	159.2
62.5°	177.2	163.7	155.6	149.8	147.1	147.1	143.9	141.7	141.7	142.1	141.2
65°	152.9	143.0	135.8	131.3	130.0	128.2	127.7	125.9	124.6	125.0	124.6
67.5°	131.3	123.7	118.7	115.1	112.9	112.0	110.6	110.6	109.8	110.2	108.0
70°	112.0	104.4	100.3	96.7	95.8	95.8	94.0	94.5	93.6	94.9	94.0
72.5°	92.2	86.4	83.2	81.9	81.0	80.5	79.6	78.7	78.3	79.2	78.7
75°	74.7	69.7	67.5	66.6	65.7	65.7	65.2	64.8	64.3	64.3	64.3
77.5°	58.0	54.9	52.2	53.1	51.7	52.2	50.8	50.8	51.3	50.8	50.8
80°	42.7	40.5	40.5	39.6	37.8	38.7	38.7	37.3	36.9	37.8	36.4
82.5°	28.3	27.9	27.0	26.5	25.6	26.1	25.6	25.2	24.7	25.6	24.7
85°	16.6	16.6	16.2	15.3	16.2	15.7	15.3	15.3	14.8	14.8	14.8
87.5°	8.5	7.6	7.6	7.2	7.6	6.7	7.2	6.7	6.3	6.7	6.3
90°	24.4	25.2	26.1	27.0	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	27.0	28.5	30.0	31.5	32.3	32.4	32.6	32.9	33.1	33.3	33.1
95°	31.9	33.4	34.9	36.4	37.2	37.2	37.2	37.2	37.2	37.2	37.2
97.5°	33.1	34.9	36.6	38.3	39.2	39.3	39.5	39.8	40.0	40.2	40.0
100°	34.1	35.8	37.6	39.3	40.2	40.3	40.5	40.8	41.0	41.2	41.0
102.5°	65.3	58.1	51.0	43.8	40.2	40.4	40.8	41.3	41.7	42.1	41.7
105°	176.1	137.5	99.0	60.5	41.2	41.4	41.8	42.3	42.7	43.1	42.7
107.5°	347.6	314.0	280.5	247.0	230.2	215.9	187.4	158.9	130.4	101.9	130.4
110°	434.7	427.5	420.3	413.1	409.5	393.9	362.8	331.7	300.5	269.4	300.5

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	505.6	507.5	509.5	511.4	512.4	512.2	511.8	511.3	510.9	510.5	510.9
115°	564.6	566.8	568.9	571.1	572.2	572.6	573.5	574.4	575.2	576.1	575.2
117.5°	621.9	623.7	625.4	627.1	628.0	628.1	628.3	628.6	628.8	629.0	628.8
120°	677.8	679.5	681.3	683.0	683.9	683.9	683.9	683.9	683.9	683.9	683.9
122.5°	733.0	734.1	735.2	736.3	736.8	736.9	737.1	737.4	737.6	737.8	737.6
125°	784.2	784.7	785.1	785.6	785.8	786.0	786.4	786.9	787.3	787.7	787.3
127.5°	836.4	837.0	837.7	838.4	838.7	838.5	838.0	837.6	837.1	836.7	837.1
130°	882.7	883.5	884.4	885.3	885.7	885.5	885.0	884.6	884.1	883.7	884.1
132.5°	926.8	927.6	928.5	929.4	929.8	929.5	928.8	928.2	927.5	926.9	927.5
135°	971.6	972.2	972.9	973.6	973.9	973.6	972.9	972.2	971.6	970.9	971.6
137.5°	1011.2	1012.3	1013.4	1014.5	1015.0	1014.8	1014.4	1013.9	1013.5	1013.1	1013.5
140°	1049.2	1050.1	1051.0	1051.9	1052.3	1052.1	1051.6	1051.2	1050.7	1050.3	1050.7
142.5°	1085.2	1085.9	1086.5	1087.2	1087.5	1087.2	1086.5	1085.9	1085.2	1084.6	1085.2
145°	1118.3	1118.8	1119.2	1119.7	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9
147.5°	1148.7	1149.1	1149.6	1150.0	1150.2	1149.7	1148.6	1147.5	1146.4	1145.3	1146.4
150°	1176.1	1176.6	1177.0	1177.5	1177.7	1177.4	1176.7	1176.0	1175.4	1174.7	1175.4
152.5°	1200.1	1201.0	1201.9	1202.8	1203.2	1202.7	1201.6	1200.5	1199.4	1198.3	1199.4
155°	1221.9	1223.0	1224.1	1225.2	1225.7	1225.0	1223.7	1222.4	1221.1	1219.8	1221.1
157.5°	1241.7	1243.0	1244.3	1245.6	1246.3	1245.4	1243.7	1241.9	1240.2	1238.4	1240.2
160°	1258.3	1259.6	1260.9	1262.2	1262.9	1262.1	1260.6	1259.1	1257.6	1256.1	1257.6
162.5°	1273.2	1274.8	1276.3	1277.8	1278.6	1277.9	1276.6	1275.3	1274.0	1272.7	1274.0
165°	1286.2	1288.0	1289.7	1291.4	1292.3	1291.5	1290.0	1288.5	1287.0	1285.5	1287.0
167.5°	1297.0	1298.8	1300.5	1302.2	1303.1	1302.2	1300.5	1298.8	1297.0	1295.3	1297.0
170°	1305.8	1307.6	1309.3	1311.0	1311.9	1311.0	1309.3	1307.6	1305.8	1304.1	1305.8
172.5°	1311.7	1313.4	1315.2	1316.9	1317.8	1316.8	1314.9	1312.9	1311.0	1309.0	1311.0
175°	1316.3	1317.9	1319.4	1320.9	1321.7	1320.8	1319.1	1317.4	1315.6	1313.9	1315.6
177.5°	1318.5	1320.3	1322.0	1323.7	1324.6	1323.5	1321.3	1319.2	1317.0	1314.8	1317.0
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	497.5	498.8	495.2	494.3	494.3	496.1	494.8	482.6	484.9	482.2	481.3
5°	552.4	549.7	546.1	544.3	542.0	535.7	535.3	521.3	518.6	509.6	505.6
7.5°	612.6	610.4	599.6	598.2	597.3	591.5	576.6	561.8	551.0	540.7	530.8
10°	681.4	674.7	669.7	659.9	654.9	646.8	627.5	613.5	595.1	579.3	558.6
12.5°	764.2	756.6	739.9	732.7	726.4	703.9	684.6	668.8	632.9	622.1	596.4
15°	824.9	808.7	806.9	791.2	790.3	765.6	728.7	711.6	683.7	644.1	617.6
17.5°	890.6	876.2	865.0	846.1	843.4	820.0	793.0	751.2	720.6	682.8	649.1
20°	938.7	931.1	911.7	904.1	888.3	868.6	840.7	788.9	751.6	713.8	672.4
22.5°	977.0	969.3	954.0	943.7	934.7	909.0	875.8	831.7	780.4	730.9	688.2
25°	976.5	974.3	968.0	963.0	956.3	937.4	909.5	867.2	810.1	755.7	696.3
27.5°	921.2	927.5	938.3	943.7	942.3	939.6	923.9	888.3	837.1	772.3	705.7
30°	806.0	829.0	849.2	876.2	884.3	904.1	913.1	892.8	851.9	791.6	717.9
32.5°	668.4	701.7	745.8	760.6	786.2	824.5	867.2	874.9	849.2	802.9	725.5
35°	548.3	575.7	609.9	633.3	656.3	718.3	772.3	819.1	827.6	797.0	723.7
37.5°	453.8	473.2	503.3	523.1	544.3	597.3	672.9	733.6	776.3	777.2	718.8
40°	385.5	394.0	420.1	434.5	454.7	500.6	568.1	647.3	709.8	738.6	705.7
42.5°	326.6	337.8	359.4	370.2	383.2	423.3	467.8	542.9	620.3	681.9	681.4
45°	291.5	299.6	309.5	318.5	333.3	357.1	408.0	464.2	538.4	608.1	635.6
47.5°	260.4	268.1	278.0	280.7	290.6	313.1	344.1	393.1	462.4	531.7	583.4
50°	234.3	240.6	247.4	252.3	256.8	275.3	298.7	340.0	395.4	462.4	526.7
52.5°	214.1	218.6	224.4	227.1	231.2	244.7	262.7	293.3	338.7	399.9	462.4
55°	195.2	198.4	202.0	206.5	208.3	218.2	232.1	258.2	291.9	346.8	406.2
57.5°	177.7	179.0	181.3	184.0	186.2	194.8	206.9	224.4	254.1	296.4	352.6
60°	157.9	161.5	162.8	165.5	166.9	173.6	183.1	197.9	220.9	257.3	299.6
62.5°	141.2	143.5	145.7	147.1	150.2	152.5	160.1	173.6	192.5	219.5	257.7
65°	126.4	127.3	128.6	130.0	130.9	133.6	140.8	149.8	164.2	188.0	217.7
67.5°	109.3	110.2	112.0	112.4	113.3	116.9	121.0	128.6	140.8	158.8	183.1
70°	92.7	94.0	94.9	95.8	97.2	98.5	103.0	109.3	118.7	131.3	150.2
72.5°	78.3	79.6	79.6	80.5	80.1	81.9	86.4	90.9	97.2	107.5	124.1
75°	63.9	63.9	64.8	65.2	65.7	67.5	69.3	72.9	77.8	85.9	96.3
77.5°	50.4	49.9	50.8	50.8	50.8	52.2	54.0	55.8	58.9	64.8	72.9
80°	36.9	36.9	37.8	38.2	37.3	37.8	38.7	40.5	42.7	46.8	51.3
82.5°	24.3	26.1	25.6	26.1	25.6	26.5	27.0	27.4	28.3	30.1	33.3
85°	14.8	14.8	14.8	15.3	14.8	15.3	15.3	15.3	15.7	16.6	18.0
87.5°	6.3	6.3	6.3	6.7	6.3	6.3	6.7	6.3	6.7	6.7	7.2
90°	28.5	28.1	27.6	27.4	27.0	26.1	25.2	24.4	23.5	20.7	17.9
92.5°	32.9	32.6	32.4	32.3	31.5	30.0	28.5	27.0	25.5	23.5	21.6
95°	37.2	37.2	37.2	37.2	36.4	34.9	33.4	31.9	30.4	28.0	25.6
97.5°	39.8	39.5	39.3	39.2	38.3	36.6	34.9	33.1	31.4	42.5	53.6
100°	40.8	40.5	40.3	40.2	39.3	37.6	35.8	34.1	32.3	66.3	100.3
102.5°	41.3	40.8	40.4	40.2	43.8	51.0	58.1	65.3	72.5	110.4	148.3
105°	42.3	41.8	41.4	41.2	60.5	99.0	137.5	176.1	214.6	234.2	253.8
107.5°	158.9	187.4	215.9	230.2	247.0	280.5	314.0	347.6	381.1	377.8	374.6
110°	331.7	362.8	393.9	409.5	413.1	420.3	427.5	434.7	441.9	439.5	437.1

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	511.3	511.8	512.2	512.4	511.4	509.5	507.5	505.6	503.6	501.2	498.8
115°	574.4	573.5	572.6	572.2	571.1	568.9	566.8	564.6	562.4	560.4	558.5
117.5°	628.6	628.3	628.1	628.0	627.1	625.4	623.7	621.9	620.2	619.1	618.0
120°	683.9	683.9	683.9	683.9	683.0	681.3	679.5	677.8	676.0	675.4	674.7
122.5°	737.4	737.1	736.9	736.8	736.3	735.2	734.1	733.0	731.9	731.0	730.2
125°	786.9	786.4	786.0	785.8	785.6	785.1	784.7	784.2	783.8	782.9	782.1
127.5°	837.6	838.0	838.5	838.7	838.4	837.7	837.0	836.4	835.7	834.6	833.5
130°	884.6	885.0	885.5	885.7	885.3	884.4	883.5	882.7	881.8	880.9	880.1
132.5°	928.2	928.8	929.5	929.8	929.4	928.5	927.6	926.8	925.9	925.2	924.6
135°	972.2	972.9	973.6	973.9	973.6	972.9	972.2	971.6	970.9	970.0	969.2
137.5°	1013.9	1014.4	1014.8	1015.0	1014.5	1013.4	1012.3	1011.2	1010.1	1009.7	1009.3
140°	1051.2	1051.6	1052.1	1052.3	1051.9	1051.0	1050.1	1049.2	1048.3	1047.7	1047.0
142.5°	1085.9	1086.5	1087.2	1087.5	1087.2	1086.5	1085.9	1085.2	1084.6	1084.0	1083.3
145°	1119.9	1119.9	1119.9	1119.9	1119.7	1119.2	1118.8	1118.3	1117.9	1117.5	1117.1
147.5°	1147.5	1148.6	1149.7	1150.2	1150.0	1149.6	1149.1	1148.7	1148.3	1147.9	1147.4
150°	1176.0	1176.7	1177.4	1177.7	1177.5	1177.0	1176.6	1176.1	1175.7	1175.3	1174.9
152.5°	1200.5	1201.6	1202.7	1203.2	1202.8	1201.9	1201.0	1200.1	1199.2	1199.0	1198.8
155°	1222.4	1223.7	1225.0	1225.7	1225.2	1224.1	1223.0	1221.9	1220.8	1220.6	1220.4
157.5°	1241.9	1243.7	1245.4	1246.3	1245.6	1244.3	1243.0	1241.7	1240.4	1240.6	1240.8
160°	1259.1	1260.6	1262.1	1262.9	1262.2	1260.9	1259.6	1258.3	1257.0	1257.2	1257.4
162.5°	1275.3	1276.6	1277.9	1278.6	1277.8	1276.3	1274.8	1273.2	1271.7	1271.9	1272.1
165°	1288.5	1290.0	1291.5	1292.3	1291.4	1289.7	1288.0	1286.2	1284.5	1284.7	1284.9
167.5°	1298.8	1300.5	1302.2	1303.1	1302.2	1300.5	1298.8	1297.0	1295.3	1295.3	1295.3
170°	1307.6	1309.3	1311.0	1311.9	1311.0	1309.3	1307.6	1305.8	1304.1	1304.1	1304.1
172.5°	1312.9	1314.9	1316.8	1317.8	1316.9	1315.2	1313.4	1311.7	1309.9	1309.7	1309.5
175°	1317.4	1319.1	1320.8	1321.7	1320.9	1319.4	1317.9	1316.3	1314.8	1314.6	1314.4
177.5°	1319.2	1321.3	1323.5	1324.6	1323.7	1322.0	1320.3	1318.5	1316.8	1316.6	1316.4
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	476.8	475.4	475.4	474.5	471.8	466.9	466.4	467.3	464.6	461.9	457.9
5°	500.2	491.6	488.9	486.2	480.8	471.8	468.2	465.1	460.1	454.3	448.0
7.5°	520.0	507.8	504.2	499.3	488.5	475.9	467.8	461.0	454.3	446.2	438.6
10°	544.7	527.2	518.6	511.4	496.6	479.0	466.9	457.0	446.2	436.3	426.4
12.5°	572.6	544.3	541.6	524.0	506.9	480.8	466.0	451.6	437.2	425.1	414.7
15°	596.0	564.9	553.7	542.0	509.2	476.8	462.4	446.2	429.6	416.5	401.2
17.5°	610.8	585.2	561.3	545.6	511.4	482.6	454.7	436.3	418.8	400.8	388.2
20°	628.8	591.5	570.8	549.7	515.9	478.1	450.2	427.3	405.7	389.5	374.2
22.5°	646.8	596.4	579.3	556.4	516.8	473.6	442.1	419.2	394.5	378.3	361.6
25°	645.0	603.6	575.3	555.9	507.8	469.6	432.7	405.7	382.8	362.1	345.4
27.5°	646.4	595.5	566.7	544.3	501.5	463.7	422.8	394.5	370.6	349.0	331.5
30°	646.8	583.4	558.2	531.2	489.8	449.8	411.6	382.8	357.6	334.2	318.5
32.5°	645.5	573.5	542.0	517.7	471.4	436.3	398.5	367.9	342.3	320.7	305.9
35°	642.3	561.8	525.4	494.8	452.5	417.0	386.4	354.9	327.5	307.7	290.6
37.5°	633.8	549.2	507.8	477.7	430.5	394.5	367.5	341.4	314.9	291.5	277.1
40°	627.5	532.1	490.3	457.4	406.6	371.5	349.0	324.3	298.2	277.1	263.1
42.5°	613.1	515.9	472.3	433.2	383.2	347.2	326.1	306.3	283.8	263.1	250.5
45°	589.7	498.4	450.2	410.7	357.6	323.4	304.1	287.9	268.1	248.3	235.7
47.5°	556.8	473.2	426.9	387.3	332.4	297.8	278.4	266.3	250.5	233.9	223.1
50°	521.3	445.7	403.0	363.9	308.1	274.4	255.5	244.2	233.9	218.6	208.3
52.5°	475.0	416.5	375.6	338.2	282.0	249.6	233.0	224.9	214.1	203.3	194.3
55°	430.0	378.7	345.0	309.5	256.4	226.2	210.1	201.5	195.2	186.2	179.0
57.5°	377.8	343.6	312.6	280.2	232.5	205.1	189.8	179.5	175.4	171.4	164.6
60°	329.7	303.6	278.4	251.4	207.8	183.1	168.2	160.1	156.1	153.4	148.9
62.5°	285.6	265.4	243.8	222.2	182.6	160.1	148.9	140.8	137.2	136.7	132.7
65°	243.3	228.9	211.4	190.3	159.2	139.4	128.6	123.7	119.6	119.6	116.5
67.5°	201.1	191.2	177.2	162.4	138.1	119.6	109.8	105.3	103.0	103.0	100.8
70°	167.3	160.6	148.0	134.9	113.8	99.9	92.2	88.2	86.8	87.3	85.5
72.5°	135.8	128.6	118.3	108.9	93.1	82.8	77.4	72.9	70.6	71.1	70.6
75°	105.3	101.7	92.7	85.5	72.9	65.7	60.7	58.5	56.7	57.1	56.2
77.5°	79.2	73.8	68.8	63.9	56.2	50.4	46.3	44.1	42.7	42.7	42.7
80°	54.0	53.1	49.0	46.3	40.0	35.5	32.4	31.9	30.6	30.6	30.6
82.5°	35.1	32.8	30.6	28.8	25.2	22.5	21.1	20.2	19.8	19.3	20.2
85°	19.3	18.0	17.1	15.3	13.9	12.6	11.2	10.8	10.3	10.8	10.3
87.5°	7.6	6.3	6.3	5.8	5.4	4.9	4.9	4.0	4.0	3.6	3.6
90°	15.0	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	19.6	17.7	16.7	17.3	18.6	19.9	21.2	22.5	21.2	19.9	18.6
95°	23.2	20.8	19.6	24.1	33.0	41.9	50.9	59.8	50.9	41.9	33.0
97.5°	64.7	75.8	81.3	84.4	90.5	96.6	102.7	108.8	102.7	96.6	90.5
100°	134.2	168.2	185.2	183.0	178.7	174.3	170.0	165.6	170.0	174.3	178.7
102.5°	186.2	224.1	243.0	241.6	238.7	235.9	233.0	230.2	233.0	235.9	238.7
105°	273.3	292.9	302.7	301.5	299.1	296.8	294.4	292.0	294.4	296.8	299.1
107.5°	371.3	368.0	366.4	365.4	363.5	361.5	359.6	357.6	359.6	361.5	363.5
110°	434.7	432.3	431.1	430.2	428.5	426.8	425.0	423.3	425.0	426.8	428.5

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	496.4	494.0	492.8	492.0	490.5	489.0	487.5	486.0	487.5	489.0	490.5
115°	556.5	554.6	553.6	552.9	551.6	550.3	549.0	547.7	549.0	550.3	551.6
117.5°	616.9	615.8	615.3	614.5	613.0	611.5	609.9	608.4	609.9	611.5	613.0
120°	674.1	673.4	673.1	672.1	670.2	668.2	666.3	664.3	666.3	668.2	670.2
122.5°	729.3	728.4	728.0	727.2	725.7	724.2	722.6	721.1	722.6	724.2	725.7
125°	781.2	780.3	779.9	779.0	777.3	775.6	773.8	772.1	773.8	775.6	777.3
127.5°	832.4	831.3	830.8	829.9	828.2	826.5	824.7	823.0	824.7	826.5	828.2
130°	879.2	878.3	877.9	877.0	875.3	873.5	871.8	870.0	871.8	873.5	875.3
132.5°	923.9	923.2	922.9	922.0	920.3	918.6	916.8	915.1	916.8	918.6	920.3
135°	968.3	967.4	967.0	966.4	965.1	963.8	962.5	961.2	962.5	963.8	965.1
137.5°	1008.8	1008.4	1008.2	1007.3	1005.6	1003.8	1002.1	1000.3	1002.1	1003.8	1005.6
140°	1046.4	1045.7	1045.4	1044.7	1043.4	1042.1	1040.8	1039.5	1040.8	1042.1	1043.4
142.5°	1082.7	1082.0	1081.7	1081.0	1079.7	1078.4	1077.1	1075.8	1077.1	1078.4	1079.7
145°	1116.6	1116.2	1116.0	1115.2	1113.7	1112.2	1110.6	1109.1	1110.6	1112.2	1113.7
147.5°	1147.0	1146.5	1146.3	1145.8	1144.7	1143.6	1142.5	1141.4	1142.5	1143.6	1144.7
150°	1174.4	1174.0	1173.8	1173.5	1172.8	1172.1	1171.5	1170.8	1171.5	1172.1	1172.8
152.5°	1198.6	1198.4	1198.3	1198.2	1198.0	1197.7	1197.5	1197.3	1197.5	1197.7	1198.0
155°	1220.1	1219.9	1219.8	1220.0	1220.5	1220.9	1221.4	1221.8	1221.4	1220.9	1220.5
157.5°	1241.1	1241.3	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4
160°	1257.7	1257.9	1258.0	1258.1	1258.3	1258.6	1258.8	1259.0	1258.8	1258.6	1258.3
162.5°	1272.4	1272.6	1272.7	1273.0	1273.7	1274.4	1275.0	1275.7	1275.0	1274.4	1273.7
165°	1285.2	1285.4	1285.5	1285.8	1286.5	1287.1	1287.8	1288.4	1287.8	1287.1	1286.5
167.5°	1295.3	1295.3	1295.3	1295.7	1296.6	1297.5	1298.3	1299.2	1298.3	1297.5	1296.6
170°	1304.1	1304.1	1304.1	1304.5	1305.4	1306.3	1307.1	1308.0	1307.1	1306.3	1305.4
172.5°	1309.3	1309.1	1309.0	1309.5	1310.6	1311.7	1312.8	1313.9	1312.8	1311.7	1310.6
175°	1314.2	1314.0	1313.9	1314.4	1315.5	1316.6	1317.7	1318.8	1317.7	1316.6	1315.5
177.5°	1316.1	1315.9	1315.8	1316.3	1317.4	1318.5	1319.6	1320.7	1319.6	1318.5	1317.4
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	457.0	456.5	457.4	454.7	450.2	448.0	441.7	440.4	439.9	440.4	440.8
5°	444.4	443.9	442.6	438.1	432.7	428.7	421.0	420.6	417.9	415.2	416.5
7.5°	432.3	430.5	427.8	421.9	414.7	410.2	403.9	399.4	395.8	393.6	391.8
10°	420.1	417.4	414.7	407.1	398.1	391.3	383.7	380.1	376.0	374.2	372.4
12.5°	404.4	401.7	396.7	387.7	382.3	373.8	366.1	362.5	360.3	356.7	354.4
15°	391.8	386.4	383.7	374.2	363.0	362.1	348.1	347.2	342.7	342.7	339.1
17.5°	377.4	373.3	368.4	358.9	350.8	342.7	335.5	332.8	328.8	327.9	326.1
20°	363.4	358.0	356.2	346.8	338.2	328.4	320.7	318.0	316.2	314.4	315.8
22.5°	349.0	344.5	340.0	331.5	325.2	315.3	310.8	308.1	305.4	304.5	305.0
25°	335.1	331.1	326.6	318.0	311.3	303.2	299.1	297.8	296.4	296.4	296.0
27.5°	321.6	317.6	313.5	305.9	299.1	293.3	290.1	288.8	287.4	288.3	289.2
30°	307.7	304.1	300.5	293.7	288.3	282.9	281.1	280.2	279.8	282.0	282.0
32.5°	295.1	291.9	289.2	282.9	277.5	273.0	271.7	272.1	272.6	273.9	274.8
35°	282.0	279.8	277.1	271.7	267.2	263.1	263.6	263.6	264.5	266.7	268.5
37.5°	270.3	267.2	264.9	260.4	256.8	253.2	254.6	255.9	256.8	259.5	260.4
40°	256.4	255.0	253.2	248.7	245.6	245.1	245.6	246.5	248.3	249.6	251.0
42.5°	245.1	243.3	241.1	237.5	234.8	235.2	235.7	236.6	237.5	239.7	241.1
45°	232.5	231.2	229.4	226.2	224.0	224.4	224.9	224.9	225.8	228.5	229.4
47.5°	218.6	219.1	216.8	213.7	212.3	212.3	212.3	213.2	215.5	216.4	216.8
50°	205.1	204.2	203.8	200.6	199.7	199.3	199.7	200.2	203.3	202.9	204.2
52.5°	190.7	190.7	190.3	188.5	187.1	187.1	186.2	188.5	189.4	190.3	191.6
55°	176.8	175.4	175.0	174.1	172.3	171.8	172.7	175.4	176.3	177.2	178.6
57.5°	161.5	161.5	160.6	159.2	159.2	159.2	159.2	161.0	162.4	163.3	166.0
60°	147.5	145.7	144.4	144.4	144.4	143.9	146.6	146.6	149.3	149.8	150.7
62.5°	130.9	130.0	129.1	129.5	129.1	130.0	130.9	132.7	133.1	134.5	135.8
65°	115.1	115.1	114.2	116.9	115.1	115.1	117.4	117.4	118.3	119.6	121.4
67.5°	99.9	100.3	99.4	99.4	100.3	100.8	101.2	103.0	103.5	105.3	107.5
70°	84.1	85.0	85.5	84.6	85.5	86.4	87.3	87.7	89.5	90.4	91.8
72.5°	70.2	71.1	69.7	70.2	70.6	71.5	72.0	72.9	73.8	76.5	77.4
75°	56.2	55.8	55.3	57.1	56.2	58.0	58.5	58.5	59.4	61.6	62.5
77.5°	43.2	43.2	43.6	42.7	44.1	43.6	44.1	45.4	46.8	46.8	50.4
80°	30.1	31.0	31.0	31.0	31.5	31.9	31.0	33.3	33.7	33.7	35.1
82.5°	19.3	19.8	19.3	20.2	20.2	21.1	20.7	21.1	22.0	22.9	23.4
85°	10.3	10.3	11.2	11.2	10.8	11.2	10.8	11.2	12.1	12.1	12.6
87.5°	3.6	3.6	3.6	3.6	4.0	3.6	4.0	4.0	3.6	3.6	4.9
90°	9.7	10.8	12.2	15.0	17.9	20.7	23.5	24.4	25.2	26.1	27.0
92.5°	17.3	16.7	17.7	19.6	21.6	23.5	25.5	27.0	28.5	30.0	31.5
95°	24.1	19.6	20.8	23.2	25.6	28.0	30.4	31.9	33.4	34.9	36.4
97.5°	84.4	81.3	75.8	64.7	53.6	42.5	31.4	33.1	34.9	36.6	38.3
100°	183.0	185.2	168.2	134.2	100.3	66.3	32.3	34.1	35.8	37.6	39.3
102.5°	241.6	243.0	224.1	186.2	148.3	110.4	72.5	65.3	58.1	51.0	43.8
105°	301.5	302.7	292.9	273.3	253.8	234.2	214.6	176.1	137.5	99.0	60.5
107.5°	365.4	366.4	368.0	371.3	374.6	377.8	381.1	347.6	314.0	280.5	247.0
110°	430.2	431.1	432.3	434.7	437.1	439.5	441.9	434.7	427.5	420.3	413.1

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	492.0	492.8	494.0	496.4	498.8	501.2	503.6	505.6	507.5	509.5	511.4
115°	552.9	553.6	554.6	556.5	558.5	560.4	562.4	564.6	566.8	568.9	571.1
117.5°	614.5	615.3	615.8	616.9	618.0	619.1	620.2	621.9	623.7	625.4	627.1
120°	672.1	673.1	673.4	674.1	674.7	675.4	676.0	677.8	679.5	681.3	683.0
122.5°	727.2	728.0	728.4	729.3	730.2	731.0	731.9	733.0	734.1	735.2	736.3
125°	779.0	779.9	780.3	781.2	782.1	782.9	783.8	784.2	784.7	785.1	785.6
127.5°	829.9	830.8	831.3	832.4	833.5	834.6	835.7	836.4	837.0	837.7	838.4
130°	877.0	877.9	878.3	879.2	880.1	880.9	881.8	882.7	883.5	884.4	885.3
132.5°	922.0	922.9	923.2	923.9	924.6	925.2	925.9	926.8	927.6	928.5	929.4
135°	966.4	967.0	967.4	968.3	969.2	970.0	970.9	971.6	972.2	972.9	973.6
137.5°	1007.3	1008.2	1008.4	1008.8	1009.3	1009.7	1010.1	1011.2	1012.3	1013.4	1014.5
140°	1044.7	1045.4	1045.7	1046.4	1047.0	1047.7	1048.3	1049.2	1050.1	1051.0	1051.9
142.5°	1081.0	1081.7	1082.0	1082.7	1083.3	1084.0	1084.6	1085.2	1085.9	1086.5	1087.2
145°	1115.2	1116.0	1116.2	1116.6	1117.1	1117.5	1117.9	1118.3	1118.8	1119.2	1119.7
147.5°	1145.8	1146.3	1146.5	1147.0	1147.4	1147.9	1148.3	1148.7	1149.1	1149.6	1150.0
150°	1173.5	1173.8	1174.0	1174.4	1174.9	1175.3	1175.7	1176.1	1176.6	1177.0	1177.5
152.5°	1198.2	1198.3	1198.4	1198.6	1198.8	1199.0	1199.2	1200.1	1201.0	1201.9	1202.8
155°	1220.0	1219.8	1219.9	1220.1	1220.4	1220.6	1220.8	1221.9	1223.0	1224.1	1225.2
157.5°	1241.4	1241.4	1241.3	1241.1	1240.8	1240.6	1240.4	1241.7	1243.0	1244.3	1245.6
160°	1258.1	1258.0	1257.9	1257.7	1257.4	1257.2	1257.0	1258.3	1259.6	1260.9	1262.2
162.5°	1273.0	1272.7	1272.6	1272.4	1272.1	1271.9	1271.7	1273.2	1274.8	1276.3	1277.8
165°	1285.8	1285.5	1285.4	1285.2	1284.9	1284.7	1284.5	1286.2	1288.0	1289.7	1291.4
167.5°	1295.7	1295.3	1295.3	1295.3	1295.3	1295.3	1295.3	1297.0	1298.8	1300.5	1302.2
170°	1304.5	1304.1	1304.1	1304.1	1304.1	1304.1	1304.1	1305.8	1307.6	1309.3	1311.0
172.5°	1309.5	1309.0	1309.1	1309.3	1309.5	1309.7	1309.9	1311.7	1313.4	1315.2	1316.9
175°	1314.4	1313.9	1314.0	1314.2	1314.4	1314.6	1314.8	1316.3	1317.9	1319.4	1320.9
177.5°	1316.3	1315.8	1315.9	1316.1	1316.4	1316.6	1316.8	1318.5	1320.3	1322.0	1323.7
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	440.4	440.8	439.0	437.7	441.3	439.0	439.0	439.5	438.6	439.9	439.5
5°	415.6	416.1	412.9	413.8	412.0	411.6	411.1	413.8	413.4	412.9	413.8
7.5°	391.3	391.3	390.0	389.1	389.1	387.7	389.5	389.1	390.0	390.0	391.3
10°	371.1	372.0	369.7	367.5	367.0	367.5	367.5	367.9	368.4	371.5	371.1
12.5°	354.4	353.1	352.6	351.3	349.0	348.1	347.2	352.2	350.8	350.8	350.8
15°	336.0	339.1	338.7	334.6	333.7	335.5	334.6	334.6	339.1	338.7	338.2
17.5°	326.1	325.2	324.3	322.1	322.5	322.1	322.5	322.5	325.2	325.2	325.2
20°	314.9	313.1	313.1	312.2	312.2	310.8	312.6	313.1	314.9	314.9	315.3
22.5°	305.0	303.6	303.6	303.2	304.1	302.3	304.1	304.5	304.5	305.9	305.9
25°	296.4	295.5	295.5	296.4	296.4	296.4	296.4	298.2	296.9	297.3	296.9
27.5°	288.8	289.2	289.7	290.1	289.7	290.1	290.6	291.5	291.9	291.5	290.6
30°	281.6	282.9	283.4	283.4	284.3	284.7	285.2	285.2	285.6	284.3	285.2
32.5°	276.2	276.2	277.1	277.5	278.4	278.9	278.9	279.8	279.3	278.0	278.4
35°	268.5	268.5	270.3	271.2	272.6	272.1	272.6	272.6	273.0	272.1	270.8
37.5°	260.9	261.8	261.8	263.6	264.0	264.5	264.0	264.9	264.5	263.6	263.1
40°	251.9	251.4	251.9	253.2	253.7	253.7	253.7	254.6	254.6	254.6	254.1
42.5°	240.6	242.0	241.5	242.9	242.4	242.4	243.3	244.2	244.7	243.3	243.8
45°	229.8	229.8	230.7	230.7	231.2	231.2	233.0	232.1	233.0	232.1	232.5
47.5°	218.2	218.6	218.6	219.1	220.0	220.9	220.0	220.4	220.4	220.9	220.0
50°	205.1	205.1	206.0	207.4	209.2	208.3	207.8	209.6	208.3	208.3	207.4
52.5°	191.6	193.0	193.4	194.8	196.1	196.6	197.0	196.1	196.6	195.2	195.7
55°	178.6	179.0	180.8	182.2	183.5	183.5	183.1	183.5	184.0	182.2	182.2
57.5°	165.5	166.9	168.7	168.7	170.5	170.5	170.0	170.0	170.5	169.1	168.7
60°	151.6	152.9	155.2	155.2	157.9	158.3	157.4	156.5	156.5	155.2	155.6
62.5°	136.7	138.1	139.4	141.7	143.5	142.6	144.4	142.6	143.0	140.3	140.3
65°	123.7	124.1	126.4	128.6	128.6	129.5	128.6	129.1	127.7	127.7	125.9
67.5°	108.4	108.4	110.6	112.9	115.1	115.1	115.1	113.8	113.8	112.4	112.4
70°	94.9	94.5	96.7	98.1	99.4	99.9	99.0	98.5	97.6	96.3	95.8
72.5°	78.3	79.2	81.4	82.3	84.6	84.1	86.4	83.7	83.7	81.4	81.0
75°	63.4	64.3	66.6	67.9	69.3	69.3	70.6	69.3	67.5	66.6	66.1
77.5°	50.4	49.9	51.7	54.0	54.4	54.0	54.9	54.4	52.6	52.6	51.7
80°	36.0	37.3	39.1	38.7	40.5	40.0	40.0	39.1	39.1	37.8	38.7
82.5°	23.8	25.2	25.6	25.2	25.6	26.5	27.0	26.5	26.5	25.6	26.1
85°	12.6	12.6	13.5	13.9	13.5	13.5	13.9	15.3	14.4	13.5	14.4
87.5°	4.0	3.6	3.6	4.0	3.6	3.6	4.0	4.0	4.5	4.5	4.5
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	32.3	32.4	32.6	32.9	33.1	33.3	33.1	32.9	32.6	32.4	32.3
95°	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2
97.5°	39.2	39.3	39.5	39.8	40.0	40.2	40.0	39.8	39.5	39.3	39.2
100°	40.2	40.3	40.5	40.8	41.0	41.2	41.0	40.8	40.5	40.3	40.2
102.5°	40.2	40.4	40.8	41.3	41.7	42.1	41.7	41.3	40.8	40.4	40.2
105°	41.2	41.4	41.8	42.3	42.7	43.1	42.7	42.3	41.8	41.4	41.2
107.5°	230.2	215.9	187.4	158.9	130.4	101.9	130.4	158.9	187.4	215.9	230.2
110°	409.5	393.9	362.8	331.7	300.5	269.4	300.5	331.7	362.8	393.9	409.5

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	512.4	512.2	511.8	511.3	510.9	510.5	510.9	511.3	511.8	512.2	512.4
115°	572.2	572.6	573.5	574.4	575.2	576.1	575.2	574.4	573.5	572.6	572.2
117.5°	628.0	628.1	628.3	628.6	628.8	629.0	628.8	628.6	628.3	628.1	628.0
120°	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9
122.5°	736.8	736.9	737.1	737.4	737.6	737.8	737.6	737.4	737.1	736.9	736.8
125°	785.8	786.0	786.4	786.9	787.3	787.7	787.3	786.9	786.4	786.0	785.8
127.5°	838.7	838.5	838.0	837.6	837.1	836.7	837.1	837.6	838.0	838.5	838.7
130°	885.7	885.5	885.0	884.6	884.1	883.7	884.1	884.6	885.0	885.5	885.7
132.5°	929.8	929.5	928.8	928.2	927.5	926.9	927.5	928.2	928.8	929.5	929.8
135°	973.9	973.6	972.9	972.2	971.6	970.9	971.6	972.2	972.9	973.6	973.9
137.5°	1015.0	1014.8	1014.4	1013.9	1013.5	1013.1	1013.5	1013.9	1014.4	1014.8	1015.0
140°	1052.3	1052.1	1051.6	1051.2	1050.7	1050.3	1050.7	1051.2	1051.6	1052.1	1052.3
142.5°	1087.5	1087.2	1086.5	1085.9	1085.2	1084.6	1085.2	1085.9	1086.5	1087.2	1087.5
145°	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9
147.5°	1150.2	1149.7	1148.6	1147.5	1146.4	1145.3	1146.4	1147.5	1148.6	1149.7	1150.2
150°	1177.7	1177.4	1176.7	1176.0	1175.4	1174.7	1175.4	1176.0	1176.7	1177.4	1177.7
152.5°	1203.2	1202.7	1201.6	1200.5	1199.4	1198.3	1199.4	1200.5	1201.6	1202.7	1203.2
155°	1225.7	1225.0	1223.7	1222.4	1221.1	1219.8	1221.1	1222.4	1223.7	1225.0	1225.7
157.5°	1246.3	1245.4	1243.7	1241.9	1240.2	1238.4	1240.2	1241.9	1243.7	1245.4	1246.3
160°	1262.9	1262.1	1260.6	1259.1	1257.6	1256.1	1257.6	1259.1	1260.6	1262.1	1262.9
162.5°	1278.6	1277.9	1276.6	1275.3	1274.0	1272.7	1274.0	1275.3	1276.6	1277.9	1278.6
165°	1292.3	1291.5	1290.0	1288.5	1287.0	1285.5	1287.0	1288.5	1290.0	1291.5	1292.3
167.5°	1303.1	1302.2	1300.5	1298.8	1297.0	1295.3	1297.0	1298.8	1300.5	1302.2	1303.1
170°	1311.9	1311.0	1309.3	1307.6	1305.8	1304.1	1305.8	1307.6	1309.3	1311.0	1311.9
172.5°	1317.8	1316.8	1314.9	1312.9	1311.0	1309.0	1311.0	1312.9	1314.9	1316.8	1317.8
175°	1321.7	1320.8	1319.1	1317.4	1315.6	1313.9	1315.6	1317.4	1319.1	1320.8	1321.7
177.5°	1324.6	1323.5	1321.3	1319.2	1317.0	1314.8	1317.0	1319.2	1321.3	1323.5	1324.6
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	440.8	441.7	442.1	440.4	439.0	441.3	444.4	446.6	448.4	450.7	452.0
5°	414.7	417.9	417.9	418.8	420.1	422.4	428.2	432.3	435.9	438.6	440.8
7.5°	392.7	394.9	396.3	398.5	400.8	403.9	410.7	416.5	421.9	425.1	428.7
10°	372.9	374.7	376.9	378.3	382.3	386.8	395.4	400.3	406.6	411.6	416.1
12.5°	354.0	360.3	361.6	361.2	364.8	369.7	378.3	385.9	392.7	397.6	402.6
15°	340.5	342.7	345.4	345.0	352.6	354.0	361.2	370.2	379.2	382.3	386.8
17.5°	325.7	329.3	331.9	333.3	335.5	340.5	347.2	354.0	365.7	366.1	377.8
20°	314.0	317.6	319.4	321.2	322.5	328.4	334.2	341.8	351.3	356.2	362.5
22.5°	306.3	308.1	309.5	310.8	312.6	315.8	323.0	331.5	337.8	343.2	347.2
25°	297.3	299.1	300.9	301.8	303.2	305.0	310.4	317.1	326.1	329.7	333.7
27.5°	291.0	291.0	291.9	291.9	293.7	295.5	299.6	305.9	313.1	317.6	323.0
30°	284.3	283.8	284.3	283.8	283.4	286.1	289.7	295.1	300.0	305.4	309.0
32.5°	277.5	277.1	277.1	277.5	275.7	277.1	278.9	283.8	289.2	291.9	296.0
35°	270.3	269.4	269.4	269.4	268.5	267.6	269.4	273.9	277.5	281.1	284.3
37.5°	263.1	261.8	261.8	260.9	260.0	258.6	258.6	262.2	267.2	268.5	272.6
40°	253.2	253.2	252.3	251.9	251.0	250.1	248.7	251.9	256.4	257.7	260.9
42.5°	243.3	242.0	241.5	241.5	241.5	240.2	239.3	241.5	244.2	246.5	248.3
45°	232.1	231.2	231.6	231.2	230.3	229.8	229.4	230.3	233.4	234.3	236.6
47.5°	220.0	219.5	219.5	219.1	218.6	219.1	217.3	219.5	220.4	221.3	223.1
50°	207.4	206.9	206.5	206.0	206.0	206.5	206.0	206.0	207.8	208.7	210.5
52.5°	194.8	193.4	193.4	193.0	193.0	192.1	193.0	193.4	194.3	195.2	196.1
55°	181.3	181.3	179.9	179.9	179.0	179.0	179.5	179.0	180.8	181.7	181.7
57.5°	168.2	166.4	166.9	166.0	165.1	164.6	164.6	165.5	166.4	166.4	167.3
60°	154.3	152.5	152.0	150.2	151.1	149.8	150.2	150.2	152.0	151.1	152.0
62.5°	140.3	138.1	136.7	135.8	135.8	136.3	135.4	134.9	135.8	136.7	138.5
65°	125.5	124.1	122.8	121.4	121.4	121.0	121.9	120.5	120.1	120.5	121.4
67.5°	110.2	108.9	107.5	106.2	106.6	105.3	104.4	105.7	104.8	105.3	106.2
70°	95.4	94.5	91.8	90.9	90.4	90.9	90.4	89.5	90.9	90.4	90.9
72.5°	80.5	79.6	78.3	76.0	76.0	75.6	75.1	75.1	74.7	74.7	74.7
75°	66.1	64.3	63.0	62.5	61.6	61.2	60.7	59.8	60.3	60.7	59.8
77.5°	51.3	49.0	48.6	48.6	47.2	47.2	47.7	47.2	46.8	46.8	46.8
80°	37.8	36.0	36.0	35.1	34.2	34.2	34.2	34.2	33.7	33.3	33.7
82.5°	24.3	23.8	23.4	23.4	24.3	22.5	23.4	22.9	22.5	22.5	22.0
85°	13.5	13.9	13.5	13.9	13.0	13.5	13.5	13.5	13.0	13.5	12.6
87.5°	4.9	4.9	4.9	5.4	5.4	5.4	5.4	5.4	5.8	5.4	5.4
90°	27.0	26.1	25.2	24.4	23.5	20.7	17.9	15.0	12.2	10.8	9.7
92.5°	31.5	30.0	28.5	27.0	25.5	23.5	21.6	19.6	17.7	16.7	17.3
95°	36.4	34.9	33.4	31.9	30.4	28.0	25.6	23.2	20.8	19.6	24.1
97.5°	38.3	36.6	34.9	33.1	31.4	42.5	53.6	64.7	75.8	81.3	84.4
100°	39.3	37.6	35.8	34.1	32.3	66.3	100.3	134.2	168.2	185.2	183.0
102.5°	43.8	51.0	58.1	65.3	72.5	110.4	148.3	186.2	224.1	243.0	241.6
105°	60.5	99.0	137.5	176.1	214.6	234.2	253.8	273.3	292.9	302.7	301.5
107.5°	247.0	280.5	314.0	347.6	381.1	377.8	374.6	371.3	368.0	366.4	365.4
110°	413.1	420.3	427.5	434.7	441.9	439.5	437.1	434.7	432.3	431.1	430.2

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	511.4	509.5	507.5	505.6	503.6	501.2	498.8	496.4	494.0	492.8	492.0
115°	571.1	568.9	566.8	564.6	562.4	560.4	558.5	556.5	554.6	553.6	552.9
117.5°	627.1	625.4	623.7	621.9	620.2	619.1	618.0	616.9	615.8	615.3	614.5
120°	683.0	681.3	679.5	677.8	676.0	675.4	674.7	674.1	673.4	673.1	672.1
122.5°	736.3	735.2	734.1	733.0	731.9	731.0	730.2	729.3	728.4	728.0	727.2
125°	785.6	785.1	784.7	784.2	783.8	782.9	782.1	781.2	780.3	779.9	779.0
127.5°	838.4	837.7	837.0	836.4	835.7	834.6	833.5	832.4	831.3	830.8	829.9
130°	885.3	884.4	883.5	882.7	881.8	880.9	880.1	879.2	878.3	877.9	877.0
132.5°	929.4	928.5	927.6	926.8	925.9	925.2	924.6	923.9	923.2	922.9	922.0
135°	973.6	972.9	972.2	971.6	970.9	970.0	969.2	968.3	967.4	967.0	966.4
137.5°	1014.5	1013.4	1012.3	1011.2	1010.1	1009.7	1009.3	1008.8	1008.4	1008.2	1007.3
140°	1051.9	1051.0	1050.1	1049.2	1048.3	1047.7	1047.0	1046.4	1045.7	1045.4	1044.7
142.5°	1087.2	1086.5	1085.9	1085.2	1084.6	1084.0	1083.3	1082.7	1082.0	1081.7	1081.0
145°	1119.7	1119.2	1118.8	1118.3	1117.9	1117.5	1117.1	1116.6	1116.2	1116.0	1115.2
147.5°	1150.0	1149.6	1149.1	1148.7	1148.3	1147.9	1147.4	1147.0	1146.5	1146.3	1145.8
150°	1177.5	1177.0	1176.6	1176.1	1175.7	1175.3	1174.9	1174.4	1174.0	1173.8	1173.5
152.5°	1202.8	1201.9	1201.0	1200.1	1199.2	1199.0	1198.8	1198.6	1198.4	1198.3	1198.2
155°	1225.2	1224.1	1223.0	1221.9	1220.8	1220.6	1220.4	1220.1	1219.9	1219.8	1220.0
157.5°	1245.6	1244.3	1243.0	1241.7	1240.4	1240.6	1240.8	1241.1	1241.3	1241.4	1241.4
160°	1262.2	1260.9	1259.6	1258.3	1257.0	1257.2	1257.4	1257.7	1257.9	1258.0	1258.1
162.5°	1277.8	1276.3	1274.8	1273.2	1271.7	1271.9	1272.1	1272.4	1272.6	1272.7	1273.0
165°	1291.4	1289.7	1288.0	1286.2	1284.5	1284.7	1284.9	1285.2	1285.4	1285.5	1285.8
167.5°	1302.2	1300.5	1298.8	1297.0	1295.3	1295.3	1295.3	1295.3	1295.3	1295.3	1295.7
170°	1311.0	1309.3	1307.6	1305.8	1304.1	1304.1	1304.1	1304.1	1304.1	1304.1	1304.5
172.5°	1316.9	1315.2	1313.4	1311.7	1309.9	1309.7	1309.5	1309.3	1309.1	1309.0	1309.5
175°	1320.9	1319.4	1317.9	1316.3	1314.8	1314.6	1314.4	1314.2	1314.0	1313.9	1314.4
177.5°	1323.7	1322.0	1320.3	1318.5	1316.8	1316.6	1316.4	1316.1	1315.9	1315.8	1316.3
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	464.2	464.2	464.2	464.2
2.5°	454.3	455.6	460.1	465.5
5°	445.3	448.9	455.2	463.7
7.5°	435.4	440.8	449.8	460.6
10°	424.2	431.8	443.0	456.5
12.5°	412.0	421.9	436.3	450.2
15°	404.4	414.3	427.3	442.6
17.5°	389.5	401.2	414.7	436.3
20°	374.2	387.3	404.8	426.4
22.5°	362.5	376.5	393.1	416.1
25°	348.6	363.0	381.0	404.8
27.5°	333.7	348.1	368.4	393.6
30°	322.5	336.4	355.8	382.8
32.5°	309.0	322.5	342.7	371.1
35°	293.7	309.0	328.4	357.1
37.5°	282.0	296.0	316.2	343.6
40°	269.4	281.6	301.4	328.4
42.5°	255.9	269.4	286.5	313.5
45°	243.3	253.2	270.8	296.4
47.5°	229.8	241.1	254.6	274.4
50°	215.5	224.9	239.7	253.2
52.5°	201.5	209.2	221.7	232.1
55°	186.7	194.3	203.8	210.1
57.5°	172.7	178.1	184.4	188.5
60°	155.6	161.0	165.1	169.1
62.5°	140.3	144.4	146.6	148.9
65°	124.6	126.8	128.2	130.0
67.5°	107.5	109.8	110.2	112.9
70°	91.8	92.2	93.1	94.5
72.5°	76.9	77.8	77.4	78.3
75°	61.6	62.5	61.6	62.5
77.5°	46.8	47.7	47.7	49.0
80°	33.7	34.2	34.6	34.6
82.5°	22.0	23.4	22.5	22.9
85°	12.6	13.0	13.0	13.5
87.5°	5.8	6.3	5.8	6.7
90°	7.5	5.4	3.2	1.0
92.5°	18.6	19.9	21.2	22.5
95°	33.0	41.9	50.9	59.8
97.5°	90.5	96.6	102.7	108.8
100°	178.7	174.3	170.0	165.6
102.5°	238.7	235.9	233.0	230.2
105°	299.1	296.8	294.4	292.0
107.5°	363.5	361.5	359.6	357.6
110°	428.5	426.8	425.0	423.3

TEST NUMBER: P1010544

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	490.5	489.0	487.5	486.0
115°	551.6	550.3	549.0	547.7
117.5°	613.0	611.5	609.9	608.4
120°	670.2	668.2	666.3	664.3
122.5°	725.7	724.2	722.6	721.1
125°	777.3	775.6	773.8	772.1
127.5°	828.2	826.5	824.7	823.0
130°	875.3	873.5	871.8	870.0
132.5°	920.3	918.6	916.8	915.1
135°	965.1	963.8	962.5	961.2
137.5°	1005.6	1003.8	1002.1	1000.3
140°	1043.4	1042.1	1040.8	1039.5
142.5°	1079.7	1078.4	1077.1	1075.8
145°	1113.7	1112.2	1110.6	1109.1
147.5°	1144.7	1143.6	1142.5	1141.4
150°	1172.8	1172.1	1171.5	1170.8
152.5°	1198.0	1197.7	1197.5	1197.3
155°	1220.5	1220.9	1221.4	1221.8
157.5°	1241.4	1241.4	1241.4	1241.4
160°	1258.3	1258.6	1258.8	1259.0
162.5°	1273.7	1274.4	1275.0	1275.7
165°	1286.5	1287.1	1287.8	1288.4
167.5°	1296.6	1297.5	1298.3	1299.2
170°	1305.4	1306.3	1307.1	1308.0
172.5°	1310.6	1311.7	1312.8	1313.9
175°	1315.5	1316.6	1317.7	1318.8
177.5°	1317.4	1318.5	1319.6	1320.7
180°	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)