

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010552

Luminaire Tested: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010552
REPORT IS A COMBINATION OF REPORTS P989636 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5425.0 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010552

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010552

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	91	87	83	80	81	77	74	71	59	57	55	43	41	40	27	27	26
2	83	76	70	64	73	67	62	58	52	48	45	37	35	33	24	22	21
3	75	66	59	53	67	59	53	48	45	41	38	33	30	28	21	19	18
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	18	17	15
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	35	30	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9
9	46	34	27	22	41	31	24	20	24	19	16	17	14	12	11	10	8
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4455	4455	4455
5°	4467	4324	4321
10°	4426	4207	4175
15°	4367	4078	4021
20°	4284	3934	3855
25°	4182	3771	3683
30°	4076	3624	3510
35°	3960	3471	3369
40°	3847	3329	3220
45°	3723	3193	3098
50°	3600	3058	2965
55°	3464	2919	2844
60°	3330	2776	2718
65°	3193	2625	2572
70°	2986	2456	2420
75°	2727	2262	2264
80°	2421	2068	2086
85°	2123	1908	1959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3723 cd/sqm

TEST NUMBER: P1010552

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	0.7
10°-20°	111.9	2.1
20°-30°	167.4	3.1
30°-40°	199.8	3.7
40°-50°	209.1	3.9
50°-60°	196.2	3.6
60°-70°	163.9	3.0
70°-80°	117.2	2.2
80°-90°	72.4	1.3
90°-100°	90.4	1.7
100°-110°	257.7	4.7
110°-120°	574.0	10.6
120°-130°	713.7	13.2
130°-140°	754.8	13.9
140°-150°	701.8	12.9
150°-160°	565.1	10.4
160°-170°	364.7	6.7
170°-180°	125.7	2.3
0°-30°	318.6	5.9
0°-40°	518.4	9.6
0°-60°	923.7	17.0
0°-90°	1277.2	23.5
90°-120°	922.1	17.0
90°-150°	3092.3	57.0
90°-180°	4148.0	76.5
0°-180°	5425.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	414	414	414	414	414	
5°	414	413	411	414	414	39
15°	394	396	395	400	400	111
25°	356	361	362	368	368	164
35°	307	314	320	326	328	192
45°	251	262	273	281	285	193
55°	191	206	222	234	238	171
65°	132	150	170	183	188	131
75°	72	93	115	130	136	77
85°	22	45	68	84	88	23
90°	7	39	74	94	100	8
95°	65	42	75	96	100	75
105°	296	318	249	88	94	314
115°	552	563	588	608	616	545
125°	776	783	800	812	817	693
135°	965	970	979	990	989	743
145°	1113	1119	1121	1126	1128	696
155°	1225	1223	1224	1229	1223	564
165°	1292	1289	1288	1296	1289	365
175°	1322	1318	1318	1325	1318	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1010552

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.9	413.9	413.9	413.9	413.9
2.5°	416.1	414.8	411.2	414.8	414.3
5°	414.3	413.4	410.7	414.3	413.9
7.5°	411.2	411.2	408.5	413.0	412.5
10°	406.7	407.6	405.3	409.8	408.9
12.5°	401.3	402.6	401.3	405.3	404.4
15°	394.5	395.9	395.4	399.9	399.5
17.5°	386.4	389.1	388.6	392.7	391.8
20°	377.4	380.1	381.0	385.0	385.5
22.5°	367.9	370.6	372.0	377.4	376.9
25°	356.2	360.7	362.0	367.9	367.9
27.5°	344.9	349.9	352.6	357.5	358.0
30°	332.7	338.6	342.2	347.6	347.6
32.5°	319.2	326.0	330.9	336.8	338.1
35°	306.6	313.8	319.7	326.4	328.2
37.5°	293.1	301.2	307.9	315.6	317.0
40°	279.5	287.7	296.7	304.3	306.1
42.5°	264.7	275.0	284.5	293.1	295.8
45°	250.7	261.5	272.8	281.3	284.9
47.5°	235.8	248.0	260.6	270.1	272.8
50°	221.4	234.0	248.0	258.3	261.5
52.5°	206.0	219.6	235.4	246.2	250.2
55°	191.2	206.0	222.3	234.4	238.1
57.5°	176.7	192.1	209.7	221.8	225.9
60°	161.4	177.6	196.1	208.7	213.7
62.5°	147.0	163.7	183.5	196.1	200.6
65°	132.1	149.7	169.5	183.1	187.6
67.5°	117.2	135.7	155.5	170.4	174.0
70°	101.4	120.8	142.5	156.9	161.4
72.5°	87.0	106.4	128.9	143.8	148.3
75°	71.7	92.9	115.4	130.3	135.7
77.5°	58.6	79.8	102.3	118.1	122.2
80°	44.6	66.7	90.2	105.5	110.0
82.5°	32.5	55.0	78.9	94.2	98.7
85°	22.1	44.6	68.5	83.9	88.4
87.5°	13.5	36.1	59.1	74.4	78.9
90°	6.9	38.8	74.5	93.8	100.3
92.5°	28.0	41.5	72.8	94.6	99.7
95°	64.9	42.1	75.1	95.9	100.4
97.5°	113.6	102.2	73.3	94.8	100.3
100°	170.1	204.2	71.6	92.6	98.1
102.5°	234.5	259.8	109.2	89.4	95.9
105°	296.4	318.0	249.0	87.7	93.7
107.5°	361.8	380.0	413.3	274.2	149.5
110°	427.1	443.1	472.0	451.3	314.4

TEST NUMBER: P1010552

CATALOG NUMBER: S123DIP-B340D1025UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.0	503.2	531.2	551.2	553.4
115°	551.5	562.8	587.8	608.4	616.0
117.5°	612.4	622.9	643.1	661.7	666.3
120°	667.9	679.0	696.8	715.0	718.2
122.5°	724.9	732.7	750.6	765.4	769.6
125°	775.6	783.4	800.4	811.8	817.0
127.5°	826.7	834.0	850.2	862.2	863.3
130°	873.8	881.2	894.1	906.6	907.4
132.5°	918.5	926.4	936.1	948.1	948.3
135°	964.7	970.2	979.0	990.1	989.4
137.5°	1004.0	1011.4	1016.5	1028.6	1028.9
140°	1042.9	1048.8	1053.0	1063.7	1064.0
142.5°	1079.2	1084.6	1087.6	1096.4	1095.7
145°	1112.6	1119.0	1121.0	1126.5	1128.3
147.5°	1144.5	1149.5	1151.4	1154.8	1151.7
150°	1174.0	1177.0	1178.9	1180.9	1178.9
152.5°	1200.5	1201.5	1202.5	1206.4	1201.5
155°	1225.1	1223.1	1224.1	1229.0	1223.1
157.5°	1244.8	1244.8	1243.8	1249.7	1241.8
160°	1262.4	1261.5	1260.5	1266.4	1259.5
162.5°	1279.1	1276.2	1275.2	1282.1	1276.2
165°	1291.9	1289.0	1288.0	1295.8	1289.0
167.5°	1302.7	1298.8	1298.8	1306.7	1298.8
170°	1311.6	1307.6	1307.6	1315.5	1307.6
172.5°	1317.5	1312.5	1313.5	1321.4	1312.5
175°	1322.4	1317.5	1318.4	1325.3	1317.5
177.5°	1324.3	1319.4	1320.4	1328.3	1318.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)