

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010356

Luminaire Tested: S122RDIP-B865D725UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010356
REPORT IS A COMBINATION OF REPORTS P988771 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D725UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5498.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010356

CATALOG NUMBER: S122RDIP-B865D725UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1010356

CATALOG NUMBER: S122RDIP-B865D725UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54	54	54
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47	47	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40	40	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	35	35	35
4	76	66	58	52	71	62	55	50	53	48	44	46	42	39	39	36	34	30	30	30
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30	26	26	26
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24	24	24
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	30	26	24	21	21	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19	19	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	23	20	18	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1010356

CATALOG NUMBER: S122RDIP-B865D725UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.5
10°-20°	372.9	6.8
20°-30°	523.6	9.5
30°-40°	570.7	10.4
40°-50°	524.5	9.5
50°-60°	412.0	7.5
60°-70°	268.1	4.9
70°-80°	138.0	2.5
80°-90°	37.8	0.7
90°-100°	55.6	1.0
100°-110°	176.9	3.2
110°-120°	302.6	5.5
120°-130°	398.0	7.2
130°-140°	446.8	8.1
140°-150°	438.1	8.0
150°-160°	367.5	6.7
160°-170°	243.7	4.4
170°-180°	85.2	1.5
0°-30°	1032.3	18.8
0°-40°	1603.1	29.2
0°-60°	2539.6	46.2
0°-90°	2983.6	54.3
90°-120°	535.2	9.7
90°-150°	1818.0	33.1
90°-180°	2514.0	45.7
0°-180°	5498.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	1	10	27	25	26	5
95°	40	47	49	49	47	44
105°	163	166	167	168	168	172
115°	304	308	307	306	304	300
125°	442	448	446	444	443	395
135°	572	580	581	581	578	442
145°	694	699	704	704	701	433
155°	793	795	798	802	799	365
165°	863	862	862	868	864	243
175°	898	896	894	899	895	85
180°	899	899	899	899	899	

TEST NUMBER: P1010356

CATALOG NUMBER: S122RDIP-B865D725UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	0.8	9.9	26.6	25.0	25.8
92.5°	16.7	22.8	23.5	24.3	24.3
95°	39.5	47.1	48.6	48.6	47.1
97.5°	66.0	72.9	75.9	75.9	75.9
100°	96.4	102.5	104.7	104.7	104.0
102.5°	128.3	132.8	135.9	136.6	135.9
105°	163.2	165.5	167.0	168.5	168.5
107.5°	198.1	201.1	201.1	201.9	198.1
110°	231.5	236.0	236.0	236.0	233.8



TEST NUMBER: P1010356

CATALOG NUMBER: S122RDIP-B865D725UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.9	272.5	271.7	269.4	267.9
115°	303.6	308.1	306.6	305.9	303.6
117.5°	339.3	345.3	341.5	339.3	337.0
120°	374.9	381.0	374.9	374.9	372.6
122.5°	407.6	415.1	411.4	409.1	407.6
125°	441.7	448.5	446.3	444.0	443.2
127.5°	475.1	483.5	480.4	477.4	475.1
130°	506.2	516.1	514.6	513.1	510.0
132.5°	541.1	548.7	549.5	545.7	543.4
135°	571.5	579.8	581.4	580.6	578.3
137.5°	604.9	611.7	613.2	612.5	609.4
140°	634.5	641.3	645.1	645.1	642.1
142.5°	664.8	671.7	674.0	674.7	671.7
145°	693.7	699.0	703.6	704.3	701.3
147.5°	719.5	726.3	729.4	730.9	727.8
150°	746.1	750.6	753.6	755.9	753.6
152.5°	769.6	774.1	777.9	781.0	777.9
155°	793.1	795.4	797.7	801.5	799.2
157.5°	813.6	815.1	816.6	821.9	818.2
160°	831.8	833.3	834.1	838.6	835.6
162.5°	848.5	848.5	849.3	854.6	850.8
165°	862.9	862.2	862.2	867.5	863.7
167.5°	875.8	873.6	873.6	878.9	875.1
170°	885.7	883.4	882.7	888.0	883.4
172.5°	892.5	890.3	889.5	894.8	890.3
175°	897.8	895.6	894.0	899.4	894.8
177.5°	900.9	898.6	897.1	901.6	897.1
180°	899.4	899.4	899.4	899.4	899.4

(END OF REPORT)