

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010569

Luminaire Tested: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010569
REPORT IS A COMBINATION OF REPORTS P989698 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6087.0 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010569

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010569

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	87	84	80	81	78	75	72	59	57	55	43	41	40	27	26	26			19
2	83	76	70	65	74	68	63	59	52	49	46	37	35	34	24	23	22			16
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	20	18			13
4	69	59	52	46	61	53	46	41	41	36	33	29	26	24	19	17	16			11
5	64	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14			10
6	58	47	39	34	52	42	35	30	32	28	24	24	20	18	15	13	12			9
7	54	42	35	29	48	38	31	26	29	25	21	21	18	16	14	12	11			8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10			7
9	46	35	27	23	41	31	25	21	24	20	17	18	15	13	12	10	9			6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5628	5628	5628
5°	5643	5435	5427
10°	5593	5251	5197
15°	5515	5060	4947
20°	5426	4847	4699
25°	5311	4623	4433
30°	5184	4391	4154
35°	5052	4155	3877
40°	4913	3905	3604
45°	4761	3664	3320
50°	4607	3393	3033
55°	4408	3112	2745
60°	4203	2800	2437
65°	4010	2466	2114
70°	3734	2093	1739
75°	3336	1656	1350
80°	2883	1164	956
85°	2248	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4761 cd/sqm

TEST NUMBER: P1010569

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	0.8
10°-20°	139.2	2.3
20°-30°	205.6	3.4
30°-40°	240.1	3.9
40°-50°	241.4	4.0
50°-60°	212.1	3.5
60°-70°	157.9	2.6
70°-80°	89.9	1.5
80°-90°	28.6	0.5
90°-100°	54.6	0.9
100°-110°	264.1	4.3
110°-120°	647.3	10.6
120°-130°	821.7	13.5
130°-140°	877.8	14.4
140°-150°	820.8	13.5
150°-160°	662.1	10.9
160°-170°	427.3	7.0
170°-180°	147.2	2.4
0°-30°	394.1	6.5
0°-40°	634.2	10.4
0°-60°	1087.7	17.9
0°-90°	1364.1	22.4
90°-120°	966.0	15.9
90°-150°	3486.3	57.3
90°-180°	4723.0	77.6
0°-180°	6087.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	523	523	523	523	523	
5°	523	521	516	521	520	50
15°	498	496	491	494	492	140
25°	452	450	444	444	443	208
35°	391	388	383	380	378	245
45°	321	319	313	308	305	248
55°	243	243	237	232	230	218
65°	166	164	159	156	154	164
75°	88	86	84	82	81	94
85°	23	22	22	22	22	25
90°	1	13	28	32	34	6
95°	70	23	36	44	44	84
105°	343	356	252	48	51	364
115°	643	650	661	672	677	635
125°	907	916	921	923	925	810
135°	1129	1136	1141	1144	1141	869
145°	1303	1311	1313	1316	1316	816
155°	1435	1433	1434	1440	1433	661
165°	1514	1510	1509	1518	1510	428
175°	1549	1544	1545	1553	1544	147
180°	1549	1549	1549	1549	1549	

TEST NUMBER: P1010569

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	522.9	522.9	522.9	522.9	522.9
2.5°	525.2	523.4	518.5	522.9	522.5
5°	523.4	521.1	516.2	520.7	519.8
7.5°	519.4	517.1	512.2	516.2	515.8
10°	514.0	511.7	505.9	509.9	509.0
12.5°	506.8	505.0	499.6	502.3	501.8
15°	498.2	496.4	490.6	494.2	491.5
17.5°	488.8	486.5	480.7	483.4	482.5
20°	478.0	475.3	469.4	471.2	469.9
22.5°	465.8	463.1	457.3	458.6	456.8
25°	452.4	449.7	443.8	444.3	442.9
27.5°	438.4	435.7	429.4	429.9	428.5
30°	423.1	420.9	414.6	414.6	411.4
32.5°	407.8	404.7	400.2	397.0	395.7
35°	391.2	388.5	382.7	380.0	377.7
37.5°	374.6	371.0	365.1	362.0	360.6
40°	357.0	354.3	348.0	344.4	342.6
42.5°	339.5	336.3	330.0	326.4	324.6
45°	320.6	318.8	313.0	307.6	305.3
47.5°	302.2	299.5	294.1	288.7	286.9
50°	283.3	281.0	275.2	270.2	267.5
52.5°	263.5	262.1	255.9	251.8	249.1
55°	243.3	242.8	237.0	232.0	229.8
57.5°	224.4	222.6	218.1	213.6	210.9
60°	203.7	203.2	197.8	193.8	191.6
62.5°	185.3	183.9	178.5	174.5	173.1
65°	165.9	163.7	159.2	155.6	154.2
67.5°	145.2	143.4	139.8	136.7	134.9
70°	126.8	124.1	121.4	118.3	116.0
72.5°	107.5	105.7	102.5	99.8	98.9
75°	87.7	85.9	84.5	82.3	80.9
77.5°	70.1	69.2	67.4	65.6	65.6
80°	53.1	51.7	50.8	50.4	50.4
82.5°	36.4	36.4	36.4	35.5	35.1
85°	23.4	22.5	22.5	21.6	21.6
87.5°	11.7	10.3	9.9	9.4	9.4
90°	1.2	12.7	27.6	32.2	34.5
92.5°	26.5	19.6	29.9	38.0	39.1
95°	70.2	23.0	35.7	43.7	43.7
97.5°	127.8	95.5	36.8	46.0	47.2
100°	194.5	217.5	38.0	47.2	48.3
102.5°	270.5	285.4	85.2	47.2	49.5
105°	343.0	355.7	252.1	48.3	50.6
107.5°	420.1	430.5	447.7	270.5	119.7
110°	497.2	506.4	519.1	481.1	316.5

TEST NUMBER: P1010569

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.9	578.9	591.6	602.0	599.7
115°	643.4	650.3	660.7	672.2	676.8
117.5°	714.8	722.8	728.6	737.8	738.9
120°	780.4	790.7	794.2	803.4	803.4
122.5°	847.1	855.2	859.8	865.5	866.7
125°	907.0	916.2	920.8	923.1	925.4
127.5°	966.8	976.0	981.8	985.2	982.9
130°	1022.1	1031.3	1035.9	1040.5	1038.2
132.5°	1075.0	1084.2	1087.7	1092.3	1088.8
135°	1129.1	1136.0	1140.6	1144.1	1140.6
137.5°	1175.1	1184.4	1186.7	1192.4	1190.1
140°	1221.2	1228.1	1231.5	1236.1	1233.8
142.5°	1263.8	1270.7	1274.1	1277.6	1274.1
145°	1302.9	1311.0	1313.3	1315.6	1315.6
147.5°	1340.9	1346.6	1348.9	1351.2	1345.5
150°	1375.4	1378.9	1381.2	1383.5	1380.0
152.5°	1406.5	1407.6	1408.8	1413.4	1407.6
155°	1435.3	1433.0	1434.1	1439.9	1433.0
157.5°	1458.3	1458.3	1457.1	1464.0	1454.8
160°	1479.0	1477.9	1476.7	1483.6	1475.6
162.5°	1498.6	1495.1	1494.0	1502.0	1495.1
165°	1513.5	1510.1	1508.9	1518.1	1510.1
167.5°	1526.2	1521.6	1521.6	1530.8	1521.6
170°	1536.6	1531.9	1531.9	1541.2	1531.9
172.5°	1543.5	1537.7	1538.9	1548.1	1537.7
175°	1549.2	1543.5	1544.6	1552.7	1543.5
177.5°	1551.5	1545.8	1546.9	1556.1	1544.6
180°	1549.2	1549.2	1549.2	1549.2	1549.2

(END OF REPORT)