

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010387

Luminaire Tested: S122RDIP-B865D925UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010387
REPORT IS A COMBINATION OF REPORTS P988812 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D925UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6546.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010387

CATALOG NUMBER: S122RDIP-B865D925UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1010387

CATALOG NUMBER: S122RDIP-B865D925UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46		
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39		
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34		
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29		
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25		
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	30	28	26	22		
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20		
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20	18		
8	54	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16		
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	15		
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1010387

CATALOG NUMBER: S122RDIP-B865D925UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.1
10°-20°	372.9	5.7
20°-30°	523.6	8.0
30°-40°	570.7	8.7
40°-50°	524.5	8.0
50°-60°	412.0	6.3
60°-70°	268.1	4.1
70°-80°	138.0	2.1
80°-90°	38.5	0.6
90°-100°	207.1	3.2
100°-110°	700.1	10.7
110°-120°	735.9	11.2
120°-130°	605.2	9.2
130°-140°	486.3	7.4
140°-150°	367.4	5.6
150°-160°	258.3	3.9
160°-170°	152.1	2.3
170°-180°	49.5	0.8
0°-30°	1032.3	15.8
0°-40°	1603.1	24.5
0°-60°	2539.6	38.8
0°-90°	2984.3	45.6
90°-120°	1643.2	25.1
90°-150°	3102.0	47.4
90°-180°	3562.0	54.4
0°-180°	6546.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	1	13	33	32	32	5
95°	34	84	385	145	112	36
105°	120	181	728	1301	1107	127
115°	211	267	609	1257	1457	209
125°	295	349	586	1018	1182	262
135°	346	413	579	856	980	267
145°	395	454	576	715	782	248
155°	449	485	559	632	657	207
165°	489	504	535	568	577	138
175°	510	510	515	521	520	48
180°	511	511	511	511	511	

TEST NUMBER: P1010387

CATALOG NUMBER: S122RDIP-B865D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	1.0	13.2	33.4	31.9	32.4
92.5°	14.7	46.7	151.3	69.8	59.9
95°	34.4	84.5	385.1	145.4	112.0
97.5°	51.1	111.5	627.8	291.8	187.6
100°	75.6	136.6	776.1	581.2	351.7
102.5°	98.2	159.2	781.0	982.4	685.7
105°	119.9	180.8	728.0	1301.2	1107.2
107.5°	143.4	202.4	678.9	1416.6	1391.1
110°	167.0	224.4	645.5	1398.0	1507.1

TEST NUMBER: P1010387

CATALOG NUMBER: S122RDIP-B865D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.6	245.6	623.9	1334.6	1505.1
115°	211.2	266.8	609.1	1257.0	1457.0
117.5°	234.8	287.8	601.3	1182.8	1384.3
120°	256.4	308.4	594.4	1116.5	1314.5
122.5°	277.0	329.6	590.4	1065.0	1241.8
125°	294.7	348.8	585.5	1018.3	1181.9
127.5°	309.5	367.0	582.6	978.5	1125.9
130°	322.2	383.2	580.6	938.2	1079.7
132.5°	334.0	398.8	579.6	896.4	1031.6
135°	345.8	412.6	578.7	855.7	979.5
137.5°	356.6	424.4	578.7	814.4	929.4
140°	369.4	435.2	577.7	778.1	877.3
142.5°	382.2	444.1	577.7	743.2	825.3
145°	394.9	453.9	575.7	714.8	782.0
147.5°	408.7	461.8	572.8	689.7	743.7
150°	422.5	469.6	569.8	668.0	710.3
152.5°	436.2	477.4	564.9	649.9	681.8
155°	449.0	484.8	559.0	632.2	657.3
157.5°	459.8	490.7	553.1	615.5	635.6
160°	470.6	496.6	547.2	598.8	615.0
162.5°	481.4	501.0	542.3	583.0	595.4
165°	489.3	504.0	535.4	567.8	576.7
167.5°	496.1	507.0	529.5	554.1	559.0
170°	503.0	508.4	524.6	541.3	543.3
172.5°	506.9	509.9	518.7	530.0	530.5
175°	509.9	510.4	514.8	521.2	519.7
177.5°	511.9	510.9	510.9	514.8	511.9
180°	510.9	510.9	510.9	510.9	510.9

(END OF REPORT)