

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010570

Luminaire Tested: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010570
REPORT IS A COMBINATION OF REPORTS P989699 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6140.0 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010570

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010570

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	87	84	80	81	78	75	72	59	57	55	43	41	40	27	26	26			19
2	83	76	70	65	74	68	63	59	52	49	46	37	35	34	24	23	22			16
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	20	18			13
4	69	59	52	46	61	53	46	41	41	36	33	29	26	24	19	17	16			11
5	64	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14			10
6	58	47	39	34	52	42	35	30	32	28	24	24	20	18	15	13	12			9
7	54	42	35	29	48	38	31	26	29	25	21	21	18	16	14	12	11			8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10			7
9	46	35	27	23	41	31	25	21	24	20	17	18	15	13	12	10	9			6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1010570

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	0.8
10°-20°	140.4	2.3
20°-30°	207.4	3.4
30°-40°	242.2	3.9
40°-50°	243.5	4.0
50°-60°	213.9	3.5
60°-70°	159.3	2.6
70°-80°	90.7	1.5
80°-90°	28.9	0.5
90°-100°	55.1	0.9
100°-110°	266.4	4.3
110°-120°	652.9	10.6
120°-130°	828.8	13.5
130°-140°	885.4	14.4
140°-150°	827.9	13.5
150°-160°	667.8	10.9
160°-170°	431.0	7.0
170°-180°	148.5	2.4
0°-30°	397.6	6.5
0°-40°	639.8	10.4
0°-60°	1097.2	17.9
0°-90°	1376.1	22.4
90°-120°	974.4	15.9
90°-150°	3516.6	57.3
90°-180°	4764.0	77.6
0°-180°	6140.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	1	13	28	32	35	6
95°	71	23	36	44	44	85
105°	346	359	254	49	51	367
115°	649	656	666	678	683	641
125°	915	924	929	931	933	817
135°	1139	1146	1150	1154	1150	877
145°	1314	1322	1325	1327	1327	823
155°	1448	1445	1447	1452	1445	667
165°	1527	1523	1522	1531	1523	431
175°	1563	1557	1558	1566	1557	149
180°	1563	1563	1563	1563	1563	

TEST NUMBER: P1010570

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	1.2	12.8	27.9	32.5	34.8
92.5°	26.7	19.7	30.2	38.3	39.5
95°	70.8	23.2	36.0	44.1	44.1
97.5°	128.9	96.4	37.2	46.4	47.6
100°	196.2	219.4	38.3	47.6	48.8
102.5°	272.8	287.9	85.9	47.6	49.9
105°	346.0	358.7	254.3	48.8	51.1
107.5°	423.8	434.2	451.6	272.8	120.7
110°	501.5	510.8	523.6	485.3	319.3

TEST NUMBER: P1010570

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.8	584.0	596.7	607.2	604.9
115°	649.0	655.9	666.4	678.0	682.6
117.5°	721.0	729.1	734.9	744.2	745.3
120°	787.1	797.6	801.1	810.4	810.4
122.5°	854.5	862.6	867.2	873.0	874.2
125°	914.8	924.1	928.8	931.1	933.4
127.5°	975.2	984.5	990.3	993.8	991.5
130°	1030.9	1040.2	1044.9	1049.5	1047.2
132.5°	1084.3	1093.6	1097.1	1101.8	1098.3
135°	1138.9	1145.9	1150.5	1154.0	1150.5
137.5°	1185.3	1194.6	1197.0	1202.8	1200.4
140°	1231.8	1238.7	1242.2	1246.9	1244.5
142.5°	1274.7	1281.7	1285.2	1288.7	1285.2
145°	1314.2	1322.3	1324.7	1327.0	1327.0
147.5°	1352.5	1358.3	1360.6	1363.0	1357.2
150°	1387.3	1390.8	1393.2	1395.5	1392.0
152.5°	1418.7	1419.9	1421.0	1425.7	1419.9
155°	1447.7	1445.4	1446.6	1452.4	1445.4
157.5°	1470.9	1470.9	1469.8	1476.7	1467.5
160°	1491.8	1490.7	1489.5	1496.5	1488.4
162.5°	1511.6	1508.1	1506.9	1515.1	1508.1
165°	1526.7	1523.2	1522.0	1531.3	1523.2
167.5°	1539.4	1534.8	1534.8	1544.1	1534.8
170°	1549.9	1545.2	1545.2	1554.5	1545.2
172.5°	1556.8	1551.0	1552.2	1561.5	1551.0
175°	1562.7	1556.8	1558.0	1566.1	1556.8
177.5°	1565.0	1559.2	1560.3	1569.6	1558.0
180°	1562.7	1562.7	1562.7	1562.7	1562.7

(END OF REPORT)