

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010571

Luminaire Tested: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010571
REPORT IS A COMBINATION OF REPORTS P989700 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6167.0 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010571

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010571

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	87	84	80	81	78	75	72	59	57	55	43	41	40	27	26	26			19
2	83	76	70	65	74	68	63	59	52	49	46	37	35	34	24	23	22			16
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	20	18			13
4	69	59	52	46	61	53	46	41	41	36	33	29	26	24	19	17	16			11
5	64	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14			10
6	58	47	39	34	52	42	35	30	32	28	24	24	20	18	15	13	12			9
7	54	42	35	29	48	38	31	26	29	25	21	21	18	16	14	12	11			8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10			7
9	46	35	27	23	41	31	25	21	24	20	17	18	15	13	12	10	9			6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1010571

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	0.8
10°-20°	141.0	2.3
20°-30°	208.3	3.4
30°-40°	243.3	3.9
40°-50°	244.6	4.0
50°-60°	214.8	3.5
60°-70°	160.0	2.6
70°-80°	91.1	1.5
80°-90°	29.0	0.5
90°-100°	55.3	0.9
100°-110°	267.6	4.3
110°-120°	655.8	10.6
120°-130°	832.5	13.5
130°-140°	889.3	14.4
140°-150°	831.6	13.5
150°-160°	670.8	10.9
160°-170°	432.9	7.0
170°-180°	149.2	2.4
0°-30°	399.3	6.5
0°-40°	642.6	10.4
0°-60°	1102.0	17.9
0°-90°	1382.1	22.4
90°-120°	978.7	15.9
90°-150°	3532.1	57.3
90°-180°	4785.0	77.6
0°-180°	6167.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	13	28	33	35	6
95°	71	23	36	44	44	85
105°	348	360	255	49	51	368
115°	652	659	669	681	686	644
125°	919	928	933	935	938	821
135°	1144	1151	1156	1159	1156	881
145°	1320	1328	1330	1333	1333	826
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1010571

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	1.2	12.8	28.0	32.7	35.0
92.5°	26.8	19.8	30.3	38.5	39.6
95°	71.1	23.3	36.1	44.3	44.3
97.5°	129.4	96.8	37.3	46.6	47.8
100°	197.1	220.4	38.5	47.8	49.0
102.5°	274.0	289.2	86.3	47.8	50.1
105°	347.5	360.3	255.4	49.0	51.3
107.5°	425.6	436.1	453.6	274.0	121.3
110°	503.7	513.1	525.9	487.4	320.7

TEST NUMBER: P1010571

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	586.5	599.4	609.9	607.5
115°	651.8	658.8	669.3	681.0	685.7
117.5°	724.1	732.3	738.1	747.5	748.6
120°	790.6	801.1	804.6	813.9	813.9
122.5°	858.2	866.4	871.1	876.9	878.1
125°	918.9	928.2	932.9	935.2	937.5
127.5°	979.5	988.8	994.7	998.2	995.8
130°	1035.5	1044.8	1049.5	1054.1	1051.8
132.5°	1089.1	1098.4	1101.9	1106.6	1103.1
135°	1143.9	1150.9	1155.6	1159.1	1155.6
137.5°	1190.6	1199.9	1202.2	1208.1	1205.7
140°	1237.2	1244.2	1247.7	1252.4	1250.0
142.5°	1280.4	1287.3	1290.8	1294.3	1290.8
145°	1320.0	1328.2	1330.5	1332.8	1332.8
147.5°	1358.5	1364.3	1366.6	1369.0	1363.1
150°	1393.5	1397.0	1399.3	1401.6	1398.1
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)