

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007326

Luminaire Tested: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K
Description: Define 2 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3702.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007326

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007326

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007326

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.8	0.1
90°-100°	81.8	2.2
100°-110°	260.1	7.0
110°-120°	445.1	12.0
120°-130°	585.4	15.8
130°-140°	657.1	17.7
140°-150°	644.4	17.4
150°-160°	540.5	14.6
160°-170°	358.5	9.7
170°-180°	125.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.8	0.1
90°-120°	787.0	21.3
90°-150°	2673.9	72.2
90°-180°	3698.0	99.9
0°-180°	3702.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	14	39	37	38	4
95°	58	69	71	71	69	65
105°	240	243	246	248	248	253
115°	446	453	451	450	446	442
125°	650	660	656	653	652	581
135°	840	853	855	854	851	650
145°	1020	1028	1035	1036	1031	637
155°	1166	1170	1173	1179	1175	537
165°	1269	1268	1268	1276	1270	358
175°	1320	1317	1315	1323	1316	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P1007326

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	14.5	39.1	36.8	38.0
92.5°	24.6	33.5	34.6	35.7	35.7
95°	58.0	69.2	71.4	71.4	69.2
97.5°	97.1	107.2	111.6	111.6	111.6
100°	141.8	150.7	154.0	154.0	152.9
102.5°	188.6	195.3	199.8	200.9	199.8
105°	240.0	243.3	245.6	247.8	247.8
107.5°	291.3	295.8	295.8	296.9	291.3
110°	340.5	347.2	347.2	347.2	343.8

TEST NUMBER: P1007326

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	394.0	400.7	399.6	396.3	394.0
115°	446.5	453.2	451.0	449.9	446.5
117.5°	499.0	507.9	502.3	499.0	495.6
120°	551.4	560.4	551.4	551.4	548.1
122.5°	599.4	610.6	605.0	601.7	599.4
125°	649.7	659.7	656.4	653.0	651.9
127.5°	698.8	711.1	706.6	702.1	698.8
130°	744.6	759.1	756.8	754.6	750.1
132.5°	795.9	807.1	808.2	802.6	799.2
135°	840.5	852.8	855.1	853.9	850.6
137.5°	889.7	899.7	901.9	900.8	896.4
140°	933.2	943.2	948.8	948.8	944.4
142.5°	977.9	987.9	991.2	992.4	987.9
145°	1020.3	1028.1	1034.8	1035.9	1031.4
147.5°	1058.2	1068.3	1072.7	1075.0	1070.5
150°	1097.3	1104.0	1108.5	1111.8	1108.5
152.5°	1131.9	1138.6	1144.2	1148.6	1144.2
155°	1166.5	1169.8	1173.2	1178.8	1175.4
157.5°	1196.6	1198.9	1201.1	1208.9	1203.3
160°	1223.4	1225.7	1226.8	1233.5	1229.0
162.5°	1248.0	1248.0	1249.1	1256.9	1251.3
165°	1269.2	1268.1	1268.1	1275.9	1270.3
167.5°	1288.2	1284.8	1284.8	1292.6	1287.1
170°	1302.7	1299.3	1298.2	1306.0	1299.3
172.5°	1312.7	1309.4	1308.3	1316.1	1309.4
175°	1320.5	1317.2	1315.0	1322.8	1316.1
177.5°	1325.0	1321.7	1319.4	1326.1	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)