

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010597

Luminaire Tested: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010597
REPORT IS A COMBINATION OF REPORTS P989816 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3724.0 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010597

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010597

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34			
1	94	89	85	81	84	80	77	74	64	62	60	49	48	46	36	35	34	27			
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	28	22			
3	77	68	60	54	69	61	55	50	49	44	41	38	34	32	27	25	23	19			
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20	16			
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14			
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15	12			
7	55	43	35	29	49	39	32	27	31	26	22	24	21	18	18	15	13	10			
8	51	38	31	26	46	35	28	24	28	23	20	22	18	16	16	14	12	9			
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	11	8			
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	14	11	10	8			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4455	4455	4455
5°	4467	4324	4321
10°	4426	4207	4175
15°	4367	4078	4021
20°	4284	3934	3855
25°	4182	3771	3683
30°	4076	3624	3510
35°	3960	3471	3369
40°	3847	3329	3220
45°	3723	3193	3098
50°	3600	3058	2965
55°	3464	2919	2844
60°	3330	2776	2718
65°	3193	2625	2572
70°	2986	2456	2420
75°	2727	2262	2264
80°	2421	2068	2086
85°	2123	1908	1959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3723 cd/sqm

TEST NUMBER: P1010597

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	1.1
10°-20°	111.9	3.0
20°-30°	167.4	4.5
30°-40°	199.8	5.4
40°-50°	209.1	5.6
50°-60°	196.2	5.3
60°-70°	163.9	4.4
70°-80°	117.2	3.1
80°-90°	71.3	1.9
90°-100°	70.8	1.9
100°-110°	162.6	4.4
110°-120°	341.0	9.2
120°-130°	417.9	11.2
130°-140°	438.8	11.8
140°-150°	406.4	10.9
150°-160°	326.8	8.8
160°-170°	210.9	5.7
170°-180°	72.7	2.0
0°-30°	318.6	8.6
0°-40°	518.4	13.9
0°-60°	923.7	24.8
0°-90°	1276.0	34.3
90°-120°	574.4	15.4
90°-150°	1837.5	49.3
90°-180°	2448.0	65.7
0°-180°	3724.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	414	414	414	414	414	
5°	414	413	411	414	414	39
15°	394	396	395	400	400	111
25°	356	361	362	368	368	164
35°	307	314	320	326	328	192
45°	251	262	273	281	285	193
55°	191	206	222	234	238	171
65°	132	150	170	183	188	131
75°	72	93	115	130	136	77
85°	22	45	68	84	88	23
90°	6	34	64	82	88	6
95°	40	34	62	80	85	45
105°	173	190	158	70	76	183
115°	320	329	350	366	372	316
125°	449	454	469	480	484	401
135°	558	561	568	578	579	430
145°	644	647	648	653	655	403
155°	708	707	708	711	707	326
165°	747	746	745	749	746	211
175°	765	762	762	766	762	73
180°	765	765	765	765	765	

TEST NUMBER: P1010597

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.9	413.9	413.9	413.9	413.9
2.5°	416.1	414.8	411.2	414.8	414.3
5°	414.3	413.4	410.7	414.3	413.9
7.5°	411.2	411.2	408.5	413.0	412.5
10°	406.7	407.6	405.3	409.8	408.9
12.5°	401.3	402.6	401.3	405.3	404.4
15°	394.5	395.9	395.4	399.9	399.5
17.5°	386.4	389.1	388.6	392.7	391.8
20°	377.4	380.1	381.0	385.0	385.5
22.5°	367.9	370.6	372.0	377.4	376.9
25°	356.2	360.7	362.0	367.9	367.9
27.5°	344.9	349.9	352.6	357.5	358.0
30°	332.7	338.6	342.2	347.6	347.6
32.5°	319.2	326.0	330.9	336.8	338.1
35°	306.6	313.8	319.7	326.4	328.2
37.5°	293.1	301.2	307.9	315.6	317.0
40°	279.5	287.7	296.7	304.3	306.1
42.5°	264.7	275.0	284.5	293.1	295.8
45°	250.7	261.5	272.8	281.3	284.9
47.5°	235.8	248.0	260.6	270.1	272.8
50°	221.4	234.0	248.0	258.3	261.5
52.5°	206.0	219.6	235.4	246.2	250.2
55°	191.2	206.0	222.3	234.4	238.1
57.5°	176.7	192.1	209.7	221.8	225.9
60°	161.4	177.6	196.1	208.7	213.7
62.5°	147.0	163.7	183.5	196.1	200.6
65°	132.1	149.7	169.5	183.1	187.6
67.5°	117.2	135.7	155.5	170.4	174.0
70°	101.4	120.8	142.5	156.9	161.4
72.5°	87.0	106.4	128.9	143.8	148.3
75°	71.7	92.9	115.4	130.3	135.7
77.5°	58.6	79.8	102.3	118.1	122.2
80°	44.6	66.7	90.2	105.5	110.0
82.5°	32.5	55.0	78.9	94.2	98.7
85°	22.1	44.6	68.5	83.9	88.4
87.5°	13.5	36.1	59.1	74.4	78.9
90°	6.5	34.2	64.5	82.2	87.8
92.5°	18.5	34.5	62.1	80.9	85.6
95°	39.7	33.9	62.2	80.2	84.7
97.5°	67.6	67.9	60.1	78.2	83.3
100°	100.1	125.9	57.9	75.6	80.7
102.5°	137.1	157.1	78.5	72.4	78.1
105°	172.9	190.0	158.2	70.3	75.5
107.5°	210.6	225.1	252.1	176.8	106.4
110°	248.2	260.8	285.1	278.1	200.4

TEST NUMBER: P1010597

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.5	294.8	318.2	334.6	337.5
115°	319.9	328.7	350.0	366.5	372.4
117.5°	355.1	362.7	380.9	396.2	400.4
120°	387.0	394.4	410.9	425.9	429.1
122.5°	420.0	424.9	441.1	453.9	457.6
125°	449.1	453.7	468.9	479.6	483.9
127.5°	478.7	482.7	496.9	507.6	509.5
130°	505.9	510.0	521.3	532.1	533.7
132.5°	531.6	536.1	544.6	555.0	556.4
135°	558.3	561.3	568.5	578.3	578.9
137.5°	581.0	585.2	589.4	599.4	600.6
140°	603.3	606.7	609.8	618.8	619.9
142.5°	624.4	627.3	629.0	636.6	637.1
145°	643.7	647.2	648.3	653.0	654.8
147.5°	661.9	664.8	665.9	668.4	667.4
150°	679.0	680.7	681.8	683.0	682.1
152.5°	694.3	694.9	695.5	697.7	694.9
155°	708.5	707.4	708.0	710.8	707.4
157.5°	719.9	719.9	719.3	722.7	718.2
160°	730.1	729.5	729.0	732.4	728.4
162.5°	739.8	738.1	737.5	741.5	738.1
165°	747.2	745.5	744.9	749.4	745.5
167.5°	753.4	751.1	751.1	755.7	751.1
170°	758.5	756.2	756.2	760.8	756.2
172.5°	761.9	759.1	759.7	764.2	759.1
175°	764.8	761.9	762.5	766.5	761.9
177.5°	765.9	763.1	763.6	768.2	762.5
180°	764.8	764.8	764.8	764.8	764.8

(END OF REPORT)