

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010600

Luminaire Tested: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010600
REPORT IS A COMBINATION OF REPORTS P989819 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3720.0 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010600

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010600

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	33	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	27
4	72	61	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1010600

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	1.3
10°-20°	140.4	3.8
20°-30°	207.4	5.6
30°-40°	242.2	6.5
40°-50°	243.5	6.5
50°-60°	213.9	5.8
60°-70°	159.3	4.3
70°-80°	90.7	2.4
80°-90°	27.3	0.7
90°-100°	27.1	0.7
100°-110°	131.2	3.5
110°-120°	321.4	8.6
120°-130°	408.1	11.0
130°-140°	435.9	11.7
140°-150°	407.6	11.0
150°-160°	328.8	8.8
160°-170°	212.2	5.7
170°-180°	73.1	2.0
0°-30°	397.6	10.7
0°-40°	639.8	17.2
0°-60°	1097.2	29.5
0°-90°	1374.5	36.9
90°-120°	479.7	12.9
90°-150°	1731.3	46.5
90°-180°	2345.0	63.0
0°-180°	3720.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	1	6	14	16	17	4
95°	35	11	18	22	22	42
105°	170	177	125	24	25	181
115°	320	323	328	334	336	316
125°	450	455	457	458	460	402
135°	561	564	566	568	566	432
145°	647	651	652	653	653	405
155°	713	712	712	715	712	328
165°	752	750	749	754	750	212
175°	769	766	767	771	766	73
180°	769	769	769	769	769	

TEST NUMBER: P1010600

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	0.6	6.3	13.7	16.0	17.1
92.5°	13.1	9.7	14.9	18.9	19.4
95°	34.9	11.4	17.7	21.7	21.7
97.5°	63.4	47.4	18.3	22.9	23.4
100°	96.6	108.0	18.9	23.4	24.0
102.5°	134.3	141.8	42.3	23.4	24.6
105°	170.3	176.6	125.2	24.0	25.2
107.5°	208.6	213.8	222.3	134.3	59.4
110°	246.9	251.5	257.8	238.9	157.2

TEST NUMBER: P1010600

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	287.5	293.8	298.9	297.8
115°	319.5	322.9	328.1	333.8	336.1
117.5°	355.0	359.0	361.8	366.4	367.0
120°	387.5	392.7	394.4	399.0	399.0
122.5°	420.7	424.7	427.0	429.8	430.4
125°	450.4	455.0	457.3	458.4	459.6
127.5°	480.1	484.7	487.6	489.3	488.1
130°	507.6	512.1	514.4	516.7	515.6
132.5°	533.9	538.4	540.2	542.4	540.7
135°	560.7	564.2	566.4	568.2	566.4
137.5°	583.6	588.2	589.3	592.2	591.0
140°	606.5	609.9	611.6	613.9	612.7
142.5°	627.6	631.0	632.8	634.5	632.8
145°	647.0	651.0	652.2	653.3	653.3
147.5°	665.9	668.8	669.9	671.0	668.2
150°	683.1	684.8	685.9	687.1	685.3
152.5°	698.5	699.1	699.6	701.9	699.1
155°	712.8	711.6	712.2	715.1	711.6
157.5°	724.2	724.2	723.6	727.1	722.5
160°	734.5	733.9	733.4	736.8	732.8
162.5°	744.2	742.5	741.9	745.9	742.5
165°	751.6	749.9	749.4	753.9	749.9
167.5°	757.9	755.6	755.6	760.2	755.6
170°	763.1	760.8	760.8	765.4	760.8
172.5°	766.5	763.6	764.2	768.8	763.6
175°	769.4	766.5	767.1	771.1	766.5
177.5°	770.5	767.6	768.2	772.8	767.1
180°	769.4	769.4	769.4	769.4	769.4

(END OF REPORT)