

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010613

Luminaire Tested: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010613
REPORT IS A COMBINATION OF REPORTS P989877 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4361.0 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010613

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010613

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	92	88	84	80	82	79	75	72	61	59	57	46	44	43	31	30	29
2	84	76	70	65	75	68	63	59	53	50	47	40	37	35	27	25	24
3	76	67	60	54	68	60	54	49	47	43	39	35	32	29	24	22	20
4	70	59	51	45	62	53	46	41	41	37	33	31	28	25	21	19	17
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	59	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	15	13	12
8	50	38	30	25	45	34	28	23	27	22	19	20	17	14	14	12	10
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9
10	43	31	24	20	39	28	22	18	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4311	4311	4311
5°	4322	4184	4181
10°	4282	4071	4040
15°	4225	3946	3890
20°	4146	3807	3730
25°	4047	3649	3563
30°	3945	3507	3397
35°	3832	3358	3260
40°	3723	3222	3116
45°	3603	3089	2998
50°	3483	2959	2869
55°	3352	2824	2752
60°	3223	2687	2630
65°	3089	2540	2488
70°	2892	2377	2342
75°	2640	2190	2191
80°	2345	2001	2020
85°	2056	1846	1895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3603 cd/sqm

TEST NUMBER: P1010613

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	0.9
10°-20°	108.3	2.5
20°-30°	162.0	3.7
30°-40°	193.4	4.4
40°-50°	202.3	4.6
50°-60°	189.9	4.4
60°-70°	158.6	3.6
70°-80°	113.4	2.6
80°-90°	69.4	1.6
90°-100°	77.3	1.8
100°-110°	199.7	4.6
110°-120°	433.7	9.9
120°-130°	536.1	12.3
130°-140°	565.3	13.0
140°-150°	524.8	12.0
150°-160°	422.4	9.7
160°-170°	272.6	6.3
170°-180°	93.9	2.2
0°-30°	308.3	7.1
0°-40°	501.6	11.5
0°-60°	893.8	20.5
0°-90°	1235.3	28.3
90°-120°	710.7	16.3
90°-150°	2336.8	53.6
90°-180°	3126.0	71.7
0°-180°	4361.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	400	400	400	400	400	
5°	401	400	397	401	400	38
15°	382	383	383	387	386	108
25°	345	349	350	356	356	159
35°	297	304	309	316	318	186
45°	243	253	264	272	276	187
55°	185	199	215	227	230	166
65°	128	145	164	177	182	126
75°	69	90	112	126	131	74
85°	21	43	66	81	86	22
90°	6	35	67	85	90	7
95°	50	36	66	85	89	57
105°	222	241	194	76	81	236
115°	413	422	445	462	469	408
125°	580	586	601	612	617	518
135°	721	725	733	743	743	555
145°	832	836	838	843	844	521
155°	916	914	915	919	914	422
165°	966	963	963	968	963	273
175°	988	985	985	990	985	94
180°	988	988	988	988	988	

TEST NUMBER: P1010613

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	400.5	400.5	400.5	400.5	400.5
2.5°	402.7	401.4	397.9	401.4	400.9
5°	400.9	400.1	397.4	400.9	400.5
7.5°	397.9	397.9	395.3	399.6	399.2
10°	393.5	394.4	392.2	396.6	395.7
12.5°	388.3	389.6	388.3	392.2	391.3
15°	381.7	383.1	382.6	387.0	386.5
17.5°	373.9	376.5	376.1	380.0	379.1
20°	365.2	367.8	368.7	372.6	373.0
22.5°	356.0	358.6	359.9	365.2	364.7
25°	344.7	349.0	350.3	356.0	356.0
27.5°	333.8	338.6	341.2	346.0	346.4
30°	322.0	327.6	331.1	336.4	336.4
32.5°	308.9	315.4	320.2	325.9	327.2
35°	296.7	303.6	309.3	315.9	317.6
37.5°	283.6	291.4	298.0	305.4	306.7
40°	270.5	278.3	287.1	294.5	296.2
42.5°	256.1	266.1	275.3	283.6	286.2
45°	242.6	253.0	263.9	272.2	275.7
47.5°	228.2	240.0	252.2	261.3	263.9
50°	214.2	226.4	240.0	250.0	253.0
52.5°	199.4	212.5	227.7	238.2	242.1
55°	185.0	199.4	215.1	226.9	230.4
57.5°	171.0	185.9	202.9	214.6	218.6
60°	156.2	171.9	189.8	202.0	206.8
62.5°	142.2	158.4	177.6	189.8	194.1
65°	127.8	144.8	164.0	177.1	181.5
67.5°	113.4	131.3	150.5	164.9	168.4
70°	98.2	116.9	137.9	151.8	156.2
72.5°	84.2	103.0	124.8	139.2	143.5
75°	69.4	89.9	111.7	126.1	131.3
77.5°	56.7	77.2	99.0	114.3	118.2
80°	43.2	64.6	87.3	102.1	106.5
82.5°	31.4	53.2	76.3	91.2	95.5
85°	21.4	43.2	66.3	81.1	85.5
87.5°	13.1	34.9	57.2	72.0	76.3
90°	6.4	35.1	66.9	84.7	90.5
92.5°	22.1	36.5	64.9	84.4	89.1
95°	49.6	36.5	66.0	84.6	89.0
97.5°	85.9	81.0	64.1	83.1	88.1
100°	128.0	156.7	62.2	80.7	85.8
102.5°	176.1	197.8	89.6	77.7	83.5
105°	222.3	240.9	193.5	75.7	81.2
107.5°	271.1	286.8	315.7	214.5	122.2
110°	319.8	333.6	359.1	346.2	244.7

TEST NUMBER: P1010613

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	366.8	378.0	402.7	420.2	422.7
115°	412.7	422.3	444.6	462.4	468.9
117.5°	458.2	466.8	485.3	501.7	505.9
120°	499.5	508.3	525.0	540.9	543.9
122.5°	542.1	548.2	564.6	577.9	581.7
125°	579.9	585.8	601.4	612.0	616.6
127.5°	618.1	623.6	638.1	649.0	650.7
130°	653.3	658.8	670.4	681.7	682.8
132.5°	686.7	692.6	701.3	712.1	712.9
135°	721.2	725.1	732.9	743.0	743.0
137.5°	750.6	756.0	760.5	771.2	771.9
140°	779.5	783.9	787.4	796.9	797.6
142.5°	806.6	810.6	812.8	820.7	820.7
145°	831.6	836.3	837.8	842.8	844.5
147.5°	855.4	859.1	860.6	863.3	861.5
150°	877.5	879.7	881.1	882.6	881.3
152.5°	897.3	898.0	898.8	901.7	898.0
155°	915.6	914.2	914.9	918.6	914.2
157.5°	930.3	930.3	929.6	934.0	928.1
160°	943.5	942.8	942.1	946.5	941.3
162.5°	956.0	953.8	953.1	958.2	953.8
165°	965.6	963.4	962.6	968.5	963.4
167.5°	973.7	970.7	970.7	976.6	970.7
170°	980.3	977.3	977.3	983.2	977.3
172.5°	984.7	981.0	981.7	987.6	981.0
175°	988.3	984.7	985.4	990.5	984.7
177.5°	989.8	986.1	986.9	992.7	985.4
180°	988.3	988.3	988.3	988.3	988.3

(END OF REPORT)