

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007336

Luminaire Tested: S122IP-B1080UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B1080UB2750-4F0-XX-W2A_5000K
Description: Define 2 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4141.0 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007336

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007336

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007336

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.5	0.1
90°-100°	46.6	1.1
100°-110°	173.5	4.2
110°-120°	460.2	11.1
120°-130°	763.3	18.4
130°-140°	810.8	19.6
140°-150°	753.6	18.2
150°-160°	605.8	14.6
160°-170°	390.4	9.4
170°-180°	134.4	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.5	0.1
90°-120°	680.3	16.4
90°-150°	3007.9	72.6
90°-180°	4139.0	100.0
0°-180°	4141.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	12	20	26	28	4
95°	66	33	40	45	44	79
105°	310	341	62	74	78	332
115°	587	605	630	157	84	578
125°	830	844	863	870	873	741
135°	1028	1044	1053	1063	1061	794
145°	1192	1191	1208	1216	1210	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P1007336

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	12.3	20.4	25.5	27.6
92.5°	25.5	21.5	24.5	26.6	27.6
95°	66.4	32.7	39.8	44.9	43.9
97.5°	119.5	35.8	52.1	55.2	56.2
100°	180.8	40.9	58.2	66.4	68.4
102.5°	248.2	246.2	60.3	71.5	74.6
105°	310.5	341.2	62.3	73.5	77.6
107.5°	383.1	408.6	64.4	75.6	79.7
110°	452.5	474.0	178.8	76.6	80.7

TEST NUMBER: P1007336

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.9	536.3	518.9	78.7	81.7
115°	587.3	604.7	630.2	157.3	83.8
117.5°	647.6	668.0	685.4	539.3	271.7
120°	715.0	730.3	748.7	761.0	623.1
122.5°	772.2	788.6	809.0	815.1	816.2
125°	830.5	843.7	863.1	870.3	873.4
127.5°	883.6	897.9	913.2	923.4	924.4
130°	933.6	950.0	961.2	972.4	971.4
132.5°	984.7	998.0	1009.2	1018.4	1017.4
135°	1027.6	1043.9	1053.1	1063.3	1061.3
137.5°	1072.5	1084.8	1095.0	1105.2	1102.2
140°	1116.5	1124.6	1135.9	1145.1	1140.0
142.5°	1153.2	1160.4	1173.7	1181.8	1176.7
145°	1192.1	1191.0	1208.4	1215.5	1210.4
147.5°	1225.8	1222.7	1240.1	1245.2	1241.1
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

(END OF REPORT)