

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007352

Luminaire Tested: S122IP-B330UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B330UB2750-4F0-XX-W2A-1_2700K
Description: Define 2 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1169.0 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007352

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007352

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007352

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.2	0.1
90°-100°	25.8	2.2
100°-110°	82.1	7.0
110°-120°	140.6	12.0
120°-130°	184.8	15.8
130°-140°	207.5	17.8
140°-150°	203.5	17.4
150°-160°	170.7	14.6
160°-170°	113.2	9.7
170°-180°	39.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.2	0.1
90°-120°	248.5	21.3
90°-150°	844.4	72.2
90°-180°	1168.0	99.9
0°-180°	1169.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	5	12	12	12	1
95°	18	22	23	23	22	20
105°	76	77	78	78	78	80
115°	141	143	142	142	141	139
125°	205	208	207	206	206	183
135°	265	269	270	270	269	205
145°	322	325	327	327	326	201
155°	368	369	370	372	371	170
165°	401	400	400	403	401	113
175°	417	416	415	418	416	40
180°	418	418	418	418	418	

TEST NUMBER: P1007352

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	4.6	12.3	11.6	12.0
92.5°	7.8	10.6	10.9	11.3	11.3
95°	18.3	21.9	22.6	22.6	21.9
97.5°	30.7	33.8	35.2	35.2	35.2
100°	44.8	47.6	48.6	48.6	48.3
102.5°	59.6	61.7	63.1	63.4	63.1
105°	75.8	76.8	77.5	78.3	78.3
107.5°	92.0	93.4	93.4	93.8	92.0
110°	107.5	109.6	109.6	109.6	108.6

TEST NUMBER: P1007352

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.4	126.5	126.2	125.1	124.4
115°	141.0	143.1	142.4	142.1	141.0
117.5°	157.6	160.4	158.6	157.6	156.5
120°	174.1	176.9	174.1	174.1	173.1
122.5°	189.3	192.8	191.0	190.0	189.3
125°	205.1	208.3	207.3	206.2	205.9
127.5°	220.7	224.5	223.1	221.7	220.7
130°	235.1	239.7	239.0	238.3	236.9
132.5°	251.3	254.9	255.2	253.4	252.4
135°	265.4	269.3	270.0	269.7	268.6
137.5°	280.9	284.1	284.8	284.5	283.0
140°	294.7	297.9	299.6	299.6	298.2
142.5°	308.8	312.0	313.0	313.4	312.0
145°	322.2	324.6	326.8	327.1	325.7
147.5°	334.2	337.3	338.7	339.4	338.0
150°	346.5	348.6	350.0	351.1	350.0
152.5°	357.4	359.5	361.3	362.7	361.3
155°	368.4	369.4	370.5	372.2	371.2
157.5°	377.9	378.6	379.3	381.7	380.0
160°	386.3	387.0	387.4	389.5	388.1
162.5°	394.1	394.1	394.4	396.9	395.1
165°	400.8	400.4	400.4	402.9	401.1
167.5°	406.8	405.7	405.7	408.2	406.4
170°	411.4	410.3	409.9	412.4	410.3
172.5°	414.5	413.5	413.1	415.6	413.5
175°	417.0	415.9	415.2	417.7	415.6
177.5°	418.4	417.3	416.6	418.8	416.6
180°	417.7	417.7	417.7	417.7	417.7

(END OF REPORT)