

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010618

Luminaire Tested: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010618
REPORT IS A COMBINATION OF REPORTS P989882 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4335.0 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010618

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010618

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5459	5459	5459
5°	5473	5271	5263
10°	5425	5092	5041
15°	5349	4907	4798
20°	5263	4701	4557
25°	5150	4483	4300
30°	5028	4259	4029
35°	4900	4029	3760
40°	4766	3787	3496
45°	4617	3552	3220
50°	4467	3291	2943
55°	4274	3017	2662
60°	4077	2717	2363
65°	3890	2391	2051
70°	3622	2029	1687
75°	3233	1607	1310
80°	2796	1130	925
85°	2180	607	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4617 cd/sqm

TEST NUMBER: P1010618

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.1
10°-20°	135.0	3.1
20°-30°	199.4	4.6
30°-40°	232.9	5.4
40°-50°	234.1	5.4
50°-60°	205.7	4.7
60°-70°	153.2	3.5
70°-80°	87.2	2.0
80°-90°	26.8	0.6
90°-100°	34.9	0.8
100°-110°	168.5	3.9
110°-120°	412.9	9.5
120°-130°	524.2	12.1
130°-140°	560.0	12.9
140°-150°	523.6	12.1
150°-160°	422.4	9.7
160°-170°	272.6	6.3
170°-180°	93.9	2.2
0°-30°	382.2	8.8
0°-40°	615.1	14.2
0°-60°	1054.9	24.3
0°-90°	1322.0	30.5
90°-120°	616.3	14.2
90°-150°	2224.1	51.3
90°-180°	3013.0	69.5
0°-180°	4335.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	508	505	501	505	504	48
15°	483	482	476	479	477	136
25°	439	436	430	431	430	202
35°	379	377	371	368	366	237
45°	311	309	304	298	296	240
55°	236	236	230	225	223	211
65°	161	159	154	151	150	159
75°	85	83	82	80	78	91
85°	23	22	22	21	21	24
90°	1	8	18	21	22	4
95°	45	15	23	28	28	54
105°	219	227	161	31	32	232
115°	410	415	422	429	432	405
125°	579	584	587	589	590	517
135°	720	725	728	730	728	555
145°	831	836	838	839	839	520
155°	916	914	915	919	914	422
165°	966	963	963	968	963	273
175°	988	985	985	990	985	94
180°	988	988	988	988	988	

TEST NUMBER: P1010618

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	507.2	507.2	507.2	507.2	507.2
2.5°	509.4	507.6	502.8	507.2	506.8
5°	507.6	505.4	500.7	505.0	504.1
7.5°	503.7	501.5	496.7	500.7	500.2
10°	498.5	496.3	490.6	494.5	493.7
12.5°	491.5	489.7	484.5	487.1	486.7
15°	483.2	481.5	475.8	479.3	476.7
17.5°	474.0	471.9	466.2	468.8	467.9
20°	463.6	461.0	455.3	457.0	455.7
22.5°	451.8	449.2	443.5	444.8	443.1
25°	438.7	436.1	430.4	430.9	429.6
27.5°	425.2	422.6	416.5	416.9	415.6
30°	410.4	408.2	402.1	402.1	399.0
32.5°	395.5	392.5	388.1	385.1	383.8
35°	379.4	376.8	371.1	368.5	366.3
37.5°	363.3	359.8	354.1	351.1	349.8
40°	346.3	343.7	337.5	334.1	332.3
42.5°	329.3	326.2	320.1	316.6	314.9
45°	310.9	309.2	303.5	298.3	296.1
47.5°	293.1	290.4	285.2	280.0	278.2
50°	274.7	272.6	266.9	262.1	259.5
52.5°	255.6	254.3	248.1	244.2	241.6
55°	235.9	235.5	229.8	225.0	222.9
57.5°	217.6	215.9	211.5	207.2	204.5
60°	197.6	197.1	191.9	188.0	185.8
62.5°	179.7	178.4	173.1	169.2	167.9
65°	160.9	158.7	154.4	150.9	149.6
67.5°	140.9	139.1	135.6	132.6	130.8
70°	123.0	120.4	117.7	114.7	112.5
72.5°	104.2	102.5	99.4	96.8	95.9
75°	85.0	83.3	82.0	79.8	78.5
77.5°	68.0	67.2	65.4	63.7	63.7
80°	51.5	50.2	49.3	48.8	48.8
82.5°	35.3	35.3	35.3	34.5	34.0
85°	22.7	21.8	21.8	20.9	20.9
87.5°	11.3	10.0	9.6	9.2	9.2
90°	0.7	8.1	17.6	20.6	22.0
92.5°	16.9	12.5	19.1	24.2	25.0
95°	44.8	14.7	22.8	27.9	27.9
97.5°	81.5	60.9	23.5	29.4	30.1
100°	124.1	138.8	24.2	30.1	30.8
102.5°	172.6	182.1	54.3	30.1	31.6
105°	218.8	226.9	160.8	30.8	32.3
107.5°	268.0	274.6	285.6	172.6	76.4
110°	317.2	323.1	331.2	306.9	201.9

TEST NUMBER: P1010618

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	369.3	377.4	384.0	382.6
115°	410.5	414.9	421.5	428.8	431.8
117.5°	456.0	461.1	464.8	470.7	471.4
120°	497.8	504.4	506.7	512.5	512.5
122.5°	540.4	545.6	548.5	552.2	552.9
125°	578.6	584.5	587.4	588.9	590.4
127.5°	616.8	622.7	626.3	628.5	627.1
130°	652.0	657.9	660.8	663.8	662.3
132.5°	685.8	691.7	693.9	696.8	694.6
135°	720.3	724.7	727.7	729.9	727.7
137.5°	749.7	755.6	757.0	760.7	759.2
140°	779.1	783.5	785.7	788.6	787.1
142.5°	806.2	810.6	812.8	815.0	812.8
145°	831.2	836.3	837.8	839.3	839.3
147.5°	855.4	859.1	860.6	862.0	858.4
150°	877.5	879.7	881.1	882.6	880.4
152.5°	897.3	898.0	898.8	901.7	898.0
155°	915.6	914.2	914.9	918.6	914.2
157.5°	930.3	930.3	929.6	934.0	928.1
160°	943.5	942.8	942.1	946.5	941.3
162.5°	956.0	953.8	953.1	958.2	953.8
165°	965.6	963.4	962.6	968.5	963.4
167.5°	973.7	970.7	970.7	976.6	970.7
170°	980.3	977.3	977.3	983.2	977.3
172.5°	984.7	981.0	981.7	987.6	981.0
175°	988.3	984.7	985.4	990.5	984.7
177.5°	989.8	986.1	986.9	992.7	985.4
180°	988.3	988.3	988.3	988.3	988.3

(END OF REPORT)