

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010626

Luminaire Tested: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010626
REPORT IS A COMBINATION OF REPORTS P989935 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6439.0 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010626

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010626

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	89	85	81	84	80	77	74	64	62	59	49	47	46	35	34	33
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	27
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13
8	51	38	31	26	45	35	28	23	28	23	20	22	18	16	16	14	12
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10
10	44	32	25	20	39	29	23	19	24	19	15	19	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7571	7571	7571
5°	7592	7349	7343
10°	7521	7150	7096
15°	7422	6930	6833
20°	7280	6686	6550
25°	7106	6410	6259
30°	6929	6160	5965
35°	6728	5898	5726
40°	6539	5658	5474
45°	6327	5426	5266
50°	6117	5196	5039
55°	5887	4961	4832
60°	5660	4719	4619
65°	5427	4462	4371
70°	5077	4173	4113
75°	4633	3846	3847
80°	4121	3512	3546
85°	3602	3244	3329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6327 cd/sqm

TEST NUMBER: P1010626

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.0
10°-20°	190.2	3.0
20°-30°	284.5	4.4
30°-40°	339.6	5.3
40°-50°	355.4	5.5
50°-60°	333.5	5.2
60°-70°	278.5	4.3
70°-80°	199.2	3.1
80°-90°	121.2	1.9
90°-100°	121.6	1.9
100°-110°	282.5	4.4
110°-120°	594.6	9.2
120°-130°	729.3	11.3
130°-140°	766.2	11.9
140°-150°	709.7	11.0
150°-160°	570.9	8.9
160°-170°	368.4	5.7
170°-180°	127.0	2.0
0°-30°	541.4	8.4
0°-40°	881.0	13.7
0°-60°	1569.9	24.4
0°-90°	2168.8	33.7
90°-120°	998.7	15.5
90°-150°	3204.0	49.8
90°-180°	4270.0	66.3
0°-180°	6439.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	703	703	703	703	703	
5°	704	703	698	704	703	67
15°	670	673	672	680	679	189
25°	605	613	615	625	625	279
35°	521	533	543	555	558	326
45°	426	444	464	478	484	329
55°	325	350	378	398	405	291
65°	224	254	288	311	319	222
75°	122	158	196	221	231	130
85°	38	76	116	142	150	39
90°	11	58	110	140	150	11
95°	69	58	107	137	145	79
105°	302	331	275	121	130	320
115°	559	574	610	639	649	552
125°	784	792	818	836	844	701
135°	975	980	993	1010	1010	751
145°	1124	1130	1132	1140	1144	704
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1010626

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	703.4	703.4	703.4	703.4	703.4
2.5°	707.2	704.9	698.8	704.9	704.2
5°	704.2	702.6	698.0	704.2	703.4
7.5°	698.8	698.8	694.2	701.9	701.1
10°	691.1	692.7	688.8	696.5	695.0
12.5°	682.0	684.3	682.0	688.8	687.3
15°	670.5	672.8	672.0	679.7	678.9
17.5°	656.7	661.3	660.5	667.4	665.9
20°	641.3	645.9	647.5	654.4	655.1
22.5°	625.3	629.8	632.1	641.3	640.6
25°	605.3	613.0	615.3	625.3	625.3
27.5°	586.2	594.6	599.2	607.6	608.4
30°	565.5	575.4	581.6	590.8	590.8
32.5°	542.5	554.0	562.4	572.4	574.7
35°	521.0	533.3	543.3	554.8	557.8
37.5°	498.1	511.8	523.3	536.4	538.7
40°	475.1	488.9	504.2	517.2	520.3
42.5°	449.8	467.4	483.5	498.1	502.7
45°	426.0	444.4	463.6	478.1	484.3
47.5°	400.7	421.4	442.9	459.0	463.6
50°	376.2	397.7	421.4	439.1	444.4
52.5°	350.2	373.2	400.0	418.4	425.3
55°	324.9	350.2	377.8	398.4	404.6
57.5°	300.4	326.4	356.3	377.0	383.9
60°	274.3	301.9	333.3	354.8	363.2
62.5°	249.8	278.1	311.9	333.3	341.0
65°	224.5	254.4	288.1	311.1	318.8
67.5°	199.2	230.6	264.4	289.6	295.8
70°	172.4	205.4	242.1	266.7	274.3
72.5°	147.9	180.8	219.1	244.4	252.1
75°	121.8	157.8	196.2	221.4	230.6
77.5°	99.6	135.6	173.9	200.8	207.7
80°	75.9	113.4	153.2	179.3	187.0
82.5°	55.2	93.5	134.1	160.1	167.8
85°	37.5	75.9	116.5	142.5	150.2
87.5°	23.0	61.3	100.4	126.4	134.1
90°	11.0	58.4	110.4	140.4	150.1
92.5°	32.0	59.0	106.3	138.5	146.3
95°	68.9	58.1	106.7	137.3	145.0
97.5°	117.9	117.6	103.1	133.9	142.6
100°	174.6	219.0	99.5	129.6	138.2
102.5°	239.3	273.7	135.5	124.2	133.9
105°	301.8	331.2	274.8	120.6	129.5
107.5°	367.6	392.7	439.0	306.8	183.7
110°	433.3	455.1	496.6	483.8	348.0

TEST NUMBER: P1010626

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	496.8	514.5	554.5	582.6	587.6
115°	558.6	573.7	610.3	638.6	648.6
117.5°	620.1	633.2	664.2	690.5	697.6
120°	676.0	688.7	717.0	742.5	747.9
122.5°	733.5	742.0	769.7	791.5	797.9
125°	784.3	792.3	818.4	836.5	843.9
127.5°	835.9	843.1	867.2	885.5	888.9
130°	883.6	890.7	910.1	928.6	931.2
132.5°	928.4	936.4	950.8	968.6	971.0
135°	975.1	980.3	992.7	1009.5	1010.3
137.5°	1014.8	1022.0	1029.3	1046.6	1048.4
140°	1053.8	1059.7	1065.0	1080.5	1082.3
142.5°	1090.5	1095.6	1098.6	1111.6	1112.4
145°	1124.2	1130.4	1132.4	1140.4	1143.5
147.5°	1156.2	1161.1	1163.1	1167.4	1165.6
150°	1186.0	1188.9	1190.9	1192.9	1191.4
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)