

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010628

Luminaire Tested: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010628
REPORT IS A COMBINATION OF REPORTS P989937 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6164.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010628

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010628

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			34
1	93	89	85	81	84	80	77	74	64	62	59	49	47	46	35	34	33			27
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	27			22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23			18
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20			15
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17			13
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15			12
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13			10
8	51	38	31	26	45	35	28	23	28	23	20	22	18	16	16	14	12			9
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10			8
10	44	32	25	20	39	29	23	19	24	19	15	19	15	12	14	11	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7248	7248	7248
5°	7268	7035	7030
10°	7200	6845	6793
15°	7104	6634	6541
20°	6969	6400	6270
25°	6803	6136	5991
30°	6632	5896	5710
35°	6442	5646	5482
40°	6259	5416	5239
45°	6056	5195	5041
50°	5856	4974	4824
55°	5635	4748	4626
60°	5419	4518	4422
65°	5195	4272	4183
70°	4859	3996	3937
75°	4435	3681	3684
80°	3941	3363	3395
85°	3448	3105	3187

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6056 cd/sqm

TEST NUMBER: P1010628

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.9	1.0
10°-20°	182.1	3.0
20°-30°	272.3	4.4
30°-40°	325.1	5.3
40°-50°	340.2	5.5
50°-60°	319.2	5.2
60°-70°	266.6	4.3
70°-80°	190.7	3.1
80°-90°	116.0	1.9
90°-100°	116.4	1.9
100°-110°	270.4	4.4
110°-120°	569.3	9.2
120°-130°	698.2	11.3
130°-140°	733.5	11.9
140°-150°	679.4	11.0
150°-160°	546.5	8.9
160°-170°	352.7	5.7
170°-180°	121.5	2.0
0°-30°	518.3	8.4
0°-40°	843.4	13.7
0°-60°	1502.8	24.4
0°-90°	2076.1	33.7
90°-120°	956.1	15.5
90°-150°	3067.2	49.8
90°-180°	4088.0	66.3
0°-180°	6164.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	674	673	668	674	673	64
15°	642	644	643	651	650	181
25°	580	587	589	598	598	267
35°	499	510	520	531	534	312
45°	408	425	444	458	464	314
55°	311	335	362	381	387	278
65°	215	244	276	298	305	212
75°	117	151	188	212	221	125
85°	36	73	112	136	144	37
90°	10	56	106	134	144	10
95°	66	56	102	132	139	76
105°	289	317	263	116	124	306
115°	535	549	584	611	621	528
125°	751	758	784	801	808	671
135°	934	938	950	966	967	719
145°	1076	1082	1084	1092	1095	674
155°	1185	1183	1184	1188	1183	546
165°	1249	1246	1246	1253	1246	353
175°	1279	1274	1275	1282	1274	122
180°	1279	1279	1279	1279	1279	

TEST NUMBER: P1010628

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	673.4	673.4	673.4	673.4	673.4
2.5°	677.0	674.8	669.0	674.8	674.1
5°	674.1	672.6	668.2	674.1	673.4
7.5°	669.0	669.0	664.6	671.9	671.2
10°	661.6	663.1	659.4	666.8	665.3
12.5°	652.8	655.0	652.8	659.4	658.0
15°	641.8	644.0	643.3	650.6	649.9
17.5°	628.6	633.0	632.3	638.9	637.4
20°	613.9	618.3	619.8	626.4	627.1
22.5°	598.5	602.9	605.1	613.9	613.2
25°	579.5	586.8	589.0	598.5	598.5
27.5°	561.1	569.2	573.6	581.7	582.4
30°	541.3	550.9	556.7	565.5	565.5
32.5°	519.3	530.3	538.4	547.9	550.1
35°	498.8	510.5	520.1	531.1	534.0
37.5°	476.8	490.0	501.0	513.5	515.7
40°	454.8	468.0	482.6	495.1	498.0
42.5°	430.6	447.4	462.8	476.8	481.2
45°	407.8	425.4	443.8	457.7	463.6
47.5°	383.6	403.4	424.0	439.4	443.8
50°	360.1	380.7	403.4	420.3	425.4
52.5°	335.2	357.2	382.9	400.5	407.1
55°	311.0	335.2	361.6	381.4	387.3
57.5°	287.5	312.5	341.1	360.9	367.5
60°	262.6	289.0	319.1	339.6	347.7
62.5°	239.1	266.3	298.5	319.1	326.4
65°	214.9	243.5	275.8	297.8	305.1
67.5°	190.7	220.8	253.1	277.3	283.1
70°	165.0	196.6	231.8	255.3	262.6
72.5°	141.6	173.1	209.8	234.0	241.3
75°	116.6	151.1	187.8	212.0	220.8
77.5°	95.4	129.8	166.5	192.2	198.8
80°	72.6	108.6	146.7	171.6	179.0
82.5°	52.8	89.5	128.4	153.3	160.6
85°	35.9	72.6	111.5	136.4	143.8
87.5°	22.0	58.7	96.1	121.0	128.4
90°	10.5	56.0	105.7	134.4	143.7
92.5°	30.7	56.5	101.7	132.6	140.1
95°	66.1	55.7	102.1	131.5	138.8
97.5°	112.8	112.6	98.6	128.2	136.6
100°	167.2	209.7	95.2	124.1	132.3
102.5°	229.2	262.0	129.7	119.0	128.2
105°	289.0	317.1	263.1	115.5	124.0
107.5°	351.9	375.8	420.2	293.7	175.8
110°	414.8	435.6	475.4	463.1	333.2

TEST NUMBER: P1010628

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	492.6	530.8	557.8	562.5
115°	534.8	549.3	584.2	611.3	620.9
117.5°	593.7	606.1	635.9	661.1	667.8
120°	647.0	659.3	686.3	710.8	715.9
122.5°	702.1	710.3	736.8	757.7	763.8
125°	750.8	758.4	783.5	800.8	807.8
127.5°	800.2	807.1	830.2	847.7	850.9
130°	845.8	852.7	871.1	888.9	891.4
132.5°	888.9	896.5	910.3	927.3	929.6
135°	933.5	938.4	950.3	966.4	967.2
137.5°	971.5	978.3	985.4	1001.9	1003.7
140°	1008.7	1014.4	1019.5	1034.3	1036.1
142.5°	1043.9	1048.9	1051.7	1064.1	1064.9
145°	1076.2	1082.1	1084.0	1091.8	1094.7
147.5°	1106.8	1111.6	1113.5	1117.6	1115.7
150°	1135.3	1138.2	1140.1	1142.0	1140.6
152.5°	1161.0	1161.9	1162.9	1166.7	1161.9
155°	1184.7	1182.8	1183.8	1188.5	1182.8
157.5°	1203.7	1203.7	1202.8	1208.5	1200.9
160°	1220.8	1219.9	1218.9	1224.6	1218.0
162.5°	1237.0	1234.1	1233.2	1239.8	1234.1
165°	1249.3	1246.5	1245.5	1253.1	1246.5
167.5°	1259.8	1256.0	1256.0	1263.6	1256.0
170°	1268.3	1264.5	1264.5	1272.1	1264.5
172.5°	1274.0	1269.3	1270.2	1277.8	1269.3
175°	1278.8	1274.0	1275.0	1281.6	1274.0
177.5°	1280.7	1275.9	1276.9	1284.5	1275.0
180°	1278.8	1278.8	1278.8	1278.8	1278.8

(END OF REPORT)