

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007385

Luminaire Tested: S122IP-B530UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B530UB2750-4F0-XX-W2A-1_4000K
Description: Define 2 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1884.0 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007385

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007385

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007385

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.9	0.1
90°-100°	41.6	2.2
100°-110°	132.4	7.0
110°-120°	226.5	12.0
120°-130°	297.9	15.8
130°-140°	334.4	17.8
140°-150°	327.9	17.4
150°-160°	275.1	14.6
160°-170°	182.4	9.7
170°-180°	63.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.9	0.1
90°-120°	400.5	21.3
90°-150°	1360.8	72.2
90°-180°	1882.0	99.9
0°-180°	1884.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	20	19	19	2
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	231	230	229	227	225
125°	331	336	334	332	332	295
135°	428	434	435	435	433	331
145°	519	523	527	527	525	324
155°	594	595	597	600	598	273
165°	646	645	645	649	646	182
175°	672	670	669	673	670	64
180°	673	673	673	673	673	

TEST NUMBER: P1007385

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	7.4	19.9	18.7	19.3
92.5°	12.5	17.0	17.6	18.2	18.2
95°	29.5	35.2	36.4	36.4	35.2
97.5°	49.4	54.5	56.8	56.8	56.8
100°	72.1	76.7	78.4	78.4	77.8
102.5°	96.0	99.4	101.7	102.3	101.7
105°	122.1	123.8	125.0	126.1	126.1
107.5°	148.3	150.5	150.5	151.1	148.3
110°	173.3	176.7	176.7	176.7	175.0

TEST NUMBER: P1007385

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.5	203.9	203.4	201.7	200.5
115°	227.2	230.6	229.5	228.9	227.2
117.5°	253.9	258.5	255.6	253.9	252.2
120°	280.6	285.2	280.6	280.6	278.9
122.5°	305.1	310.7	307.9	306.2	305.1
125°	330.6	335.7	334.0	332.3	331.8
127.5°	355.6	361.9	359.6	357.3	355.6
130°	378.9	386.3	385.2	384.0	381.8
132.5°	405.0	410.7	411.3	408.5	406.7
135°	427.8	434.0	435.2	434.6	432.9
137.5°	452.8	457.9	459.0	458.4	456.2
140°	474.9	480.0	482.9	482.9	480.6
142.5°	497.6	502.8	504.5	505.0	502.8
145°	519.2	523.2	526.6	527.2	524.9
147.5°	538.5	543.7	545.9	547.1	544.8
150°	558.4	561.8	564.1	565.8	564.1
152.5°	576.0	579.4	582.3	584.6	582.3
155°	593.6	595.4	597.1	599.9	598.2
157.5°	609.0	610.1	611.3	615.2	612.4
160°	622.6	623.8	624.3	627.7	625.5
162.5°	635.1	635.1	635.7	639.7	636.8
165°	645.9	645.3	645.3	649.3	646.5
167.5°	655.6	653.9	653.9	657.8	655.0
170°	663.0	661.3	660.7	664.7	661.3
172.5°	668.1	666.4	665.8	669.8	666.4
175°	672.0	670.3	669.2	673.2	669.8
177.5°	674.3	672.6	671.5	674.9	671.5
180°	673.2	673.2	673.2	673.2	673.2

(END OF REPORT)