

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007412

Luminaire Tested: S122IP-B725UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B725UB2750-4F0-XX-W2A-1_2700K
Description: Define 2 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2510.0 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007412

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007412

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007412

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	55.5	2.2
100°-110°	176.4	7.0
110°-120°	301.8	12.0
120°-130°	396.9	15.8
130°-140°	445.5	17.7
140°-150°	436.9	17.4
150°-160°	366.5	14.6
160°-170°	243.1	9.7
170°-180°	84.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	533.6	21.3
90°-150°	1813.0	72.2
90°-180°	2507.0	99.9
0°-180°	2510.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	26	25	26	3
95°	39	47	48	48	47	44
105°	163	165	166	168	168	172
115°	303	307	306	305	303	300
125°	440	447	445	443	442	394
135°	570	578	580	579	577	440
145°	692	697	702	702	699	432
155°	791	793	795	799	797	364
165°	860	860	860	865	861	243
175°	895	893	892	897	892	85
180°	897	897	897	897	897	

TEST NUMBER: P1007412

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	9.8	26.5	25.0	25.7
92.5°	16.7	22.7	23.5	24.2	24.2
95°	39.4	46.9	48.4	48.4	46.9
97.5°	65.8	72.7	75.7	75.7	75.7
100°	96.1	102.2	104.4	104.4	103.7
102.5°	127.9	132.4	135.5	136.2	135.5
105°	162.7	165.0	166.5	168.0	168.0
107.5°	197.5	200.6	200.6	201.3	197.5
110°	230.8	235.4	235.4	235.4	233.1

TEST NUMBER: P1007412

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.2	271.7	270.9	268.7	267.2
115°	302.7	307.3	305.8	305.0	302.7
117.5°	338.3	344.4	340.6	338.3	336.0
120°	373.9	379.9	373.9	373.9	371.6
122.5°	406.4	414.0	410.2	407.9	406.4
125°	440.5	447.3	445.0	442.8	442.0
127.5°	473.8	482.1	479.1	476.1	473.8
130°	504.8	514.7	513.1	511.6	508.6
132.5°	539.6	547.2	548.0	544.2	541.9
135°	569.9	578.2	579.7	579.0	576.7
137.5°	603.2	610.0	611.5	610.8	607.7
140°	632.7	639.5	643.3	643.3	640.3
142.5°	663.0	669.8	672.1	672.8	669.8
145°	691.8	697.1	701.6	702.4	699.3
147.5°	717.5	724.3	727.3	728.8	725.8
150°	744.0	748.5	751.5	753.8	751.5
152.5°	767.4	772.0	775.8	778.8	775.8
155°	790.9	793.2	795.4	799.2	797.0
157.5°	811.3	812.8	814.4	819.7	815.9
160°	829.5	831.0	831.8	836.3	833.3
162.5°	846.2	846.2	846.9	852.2	848.4
165°	860.5	859.8	859.8	865.1	861.3
167.5°	873.4	871.1	871.1	876.4	872.6
170°	883.2	881.0	880.2	885.5	881.0
172.5°	890.0	887.8	887.0	892.3	887.8
175°	895.3	893.1	891.6	896.9	892.3
177.5°	898.4	896.1	894.6	899.1	894.6
180°	896.9	896.9	896.9	896.9	896.9

(END OF REPORT)