

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007413

Luminaire Tested: S122IP-B725UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B725UB2750-4F0-XX-W2A-1_3000K
Description: Define 2 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2532.0 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007413

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007413

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007413

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	56.0	2.2
100°-110°	177.9	7.0
110°-120°	304.4	12.0
120°-130°	400.4	15.8
130°-140°	449.4	17.7
140°-150°	440.7	17.4
150°-160°	369.7	14.6
160°-170°	245.2	9.7
170°-180°	85.7	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	538.3	21.3
90°-150°	1828.9	72.2
90°-180°	2529.0	99.9
0°-180°	2532.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	27	25	26	3
95°	40	47	49	49	47	44
105°	164	166	168	170	170	173
115°	305	310	308	308	305	302
125°	444	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	703	708	708	706	436
155°	798	800	802	806	804	367
165°	868	867	867	873	869	245
175°	903	901	899	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P1007413

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	9.9	26.7	25.2	26.0
92.5°	16.8	22.9	23.7	24.4	24.4
95°	39.7	47.3	48.9	48.9	47.3
97.5°	66.4	73.3	76.3	76.3	76.3
100°	97.0	103.1	105.4	105.4	104.6
102.5°	129.0	133.6	136.7	137.4	136.7
105°	164.1	166.4	168.0	169.5	169.5
107.5°	199.3	202.3	202.3	203.1	199.3
110°	232.9	237.4	237.4	237.4	235.2

TEST NUMBER: P1007413

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.5	274.1	273.3	271.0	269.5
115°	305.4	310.0	308.4	307.7	305.4
117.5°	341.3	347.4	343.6	341.3	339.0
120°	377.2	383.3	377.2	377.2	374.9
122.5°	410.0	417.6	413.8	411.5	410.0
125°	444.3	451.2	448.9	446.6	445.9
127.5°	477.9	486.3	483.3	480.2	477.9
130°	509.2	519.2	517.6	516.1	513.1
132.5°	544.4	552.0	552.8	548.9	546.6
135°	574.9	583.3	584.8	584.1	581.8
137.5°	608.5	615.4	616.9	616.1	613.1
140°	638.3	645.1	649.0	649.0	645.9
142.5°	668.8	675.7	678.0	678.7	675.7
145°	697.8	703.2	707.7	708.5	705.5
147.5°	723.8	730.6	733.7	735.2	732.2
150°	750.5	755.1	758.1	760.4	758.1
152.5°	774.2	778.7	782.6	785.6	782.6
155°	797.8	800.1	802.4	806.2	803.9
157.5°	818.4	820.0	821.5	826.8	823.0
160°	836.8	838.3	839.1	843.6	840.6
162.5°	853.6	853.6	854.3	859.7	855.9
165°	868.1	867.3	867.3	872.7	868.8
167.5°	881.1	878.8	878.8	884.1	880.3
170°	891.0	888.7	887.9	893.3	888.7
172.5°	897.8	895.6	894.8	900.1	895.6
175°	903.2	900.9	899.4	904.7	900.1
177.5°	906.2	904.0	902.4	907.0	902.4
180°	904.7	904.7	904.7	904.7	904.7

(END OF REPORT)