

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007414

Luminaire Tested: S122IP-B725UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B725UB2750-4F0-XX-W2A-1_3500K
Description: Define 2 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2543.0 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007414

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007414

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007414

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	56.2	2.2
100°-110°	178.7	7.0
110°-120°	305.8	12.0
120°-130°	402.1	15.8
130°-140°	451.4	17.7
140°-150°	442.6	17.4
150°-160°	371.3	14.6
160°-170°	246.2	9.7
170°-180°	86.1	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	540.7	21.3
90°-150°	1836.8	72.2
90°-180°	2540.0	99.9
0°-180°	2543.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	27	25	26	3
95°	40	48	49	49	48	45
105°	165	167	169	170	170	174
115°	307	311	310	309	307	303
125°	446	453	451	449	448	399
135°	577	586	587	587	584	446
145°	701	706	711	712	708	438
155°	801	804	806	810	807	369
165°	872	871	871	876	873	246
175°	907	905	903	909	904	86
180°	909	909	909	909	909	

TEST NUMBER: P1007414

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	10.0	26.8	25.3	26.1
92.5°	16.9	23.0	23.8	24.5	24.5
95°	39.9	47.5	49.1	49.1	47.5
97.5°	66.7	73.6	76.7	76.7	76.7
100°	97.4	103.5	105.8	105.8	105.1
102.5°	129.6	134.2	137.3	138.0	137.3
105°	164.9	167.2	168.7	170.2	170.2
107.5°	200.1	203.2	203.2	204.0	200.1
110°	233.9	238.5	238.5	238.5	236.2

TEST NUMBER: P1007414

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	270.7	275.3	274.5	272.2	270.7
115°	306.7	311.3	309.8	309.0	306.7
117.5°	342.8	348.9	345.1	342.8	340.5
120°	378.8	384.9	378.8	378.8	376.5
122.5°	411.8	419.4	415.6	413.3	411.8
125°	446.3	453.2	450.9	448.6	447.8
127.5°	480.0	488.4	485.4	482.3	480.0
130°	511.5	521.4	519.9	518.4	515.3
132.5°	546.7	554.4	555.2	551.3	549.0
135°	577.4	585.8	587.4	586.6	584.3
137.5°	611.1	618.0	619.6	618.8	615.7
140°	641.0	647.9	651.8	651.8	648.7
142.5°	671.7	678.6	680.9	681.7	678.6
145°	700.8	706.2	710.8	711.6	708.5
147.5°	726.9	733.8	736.9	738.4	735.4
150°	753.8	758.4	761.4	763.7	761.4
152.5°	777.5	782.1	786.0	789.0	786.0
155°	801.3	803.6	805.9	809.7	807.4
157.5°	822.0	823.5	825.1	830.4	826.6
160°	840.4	841.9	842.7	847.3	844.2
162.5°	857.3	857.3	858.0	863.4	859.6
165°	871.8	871.1	871.1	876.4	872.6
167.5°	884.9	882.6	882.6	887.9	884.1
170°	894.8	892.5	891.8	897.1	892.5
172.5°	901.7	899.4	898.7	904.0	899.4
175°	907.1	904.8	903.3	908.7	904.0
177.5°	910.2	907.9	906.3	911.0	906.3
180°	908.7	908.7	908.7	908.7	908.7

(END OF REPORT)