

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010647

Luminaire Tested: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010647
REPORT IS A COMBINATION OF REPORTS P990001 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7036.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010647

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010647

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21
5	65	54	46	40	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1010647

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	1.2
10°-20°	234.8	3.3
20°-30°	346.8	4.9
30°-40°	405.1	5.8
40°-50°	407.2	5.8
50°-60°	357.7	5.1
60°-70°	266.4	3.8
70°-80°	151.6	2.2
80°-90°	46.2	0.7
90°-100°	54.8	0.8
100°-110°	264.9	3.8
110°-120°	649.2	9.2
120°-130°	824.1	11.7
130°-140°	880.4	12.5
140°-150°	823.3	11.7
150°-160°	664.0	9.4
160°-170°	428.5	6.1
170°-180°	147.7	2.1
0°-30°	664.8	9.4
0°-40°	1069.9	15.2
0°-60°	1834.9	26.1
0°-90°	2299.1	32.7
90°-120°	968.9	13.8
90°-150°	3496.7	49.7
90°-180°	4737.0	67.3
0°-180°	7036.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	1	13	28	32	35	7
95°	70	23	36	44	44	84
105°	344	357	253	48	51	365
115°	645	652	663	674	679	637
125°	910	919	924	926	928	813
135°	1132	1139	1144	1148	1144	872
145°	1307	1315	1317	1320	1320	818
155°	1440	1437	1438	1444	1437	663
165°	1518	1515	1513	1523	1515	429
175°	1554	1548	1549	1557	1548	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1010647

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	1.2	12.7	27.7	32.3	34.6
92.5°	26.6	19.6	30.0	38.1	39.2
95°	70.4	23.1	35.8	43.9	43.9
97.5°	128.1	95.8	36.9	46.2	47.3
100°	195.1	218.2	38.1	47.3	48.5
102.5°	271.3	286.3	85.4	47.3	49.6
105°	344.0	356.7	252.8	48.5	50.8
107.5°	421.4	431.7	449.1	271.3	120.1
110°	498.7	507.9	520.6	482.5	317.5

TEST NUMBER: P1010647

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.6	580.7	593.4	603.7	601.4
115°	645.3	652.2	662.6	674.2	678.8
117.5°	716.9	725.0	730.7	740.0	741.1
120°	782.7	793.1	796.5	805.8	805.8
122.5°	849.6	857.7	862.3	868.1	869.3
125°	909.7	918.9	923.5	925.8	928.1
127.5°	969.7	978.9	984.7	988.2	985.8
130°	1025.1	1034.3	1038.9	1043.6	1041.3
132.5°	1078.2	1087.4	1090.9	1095.5	1092.0
135°	1132.5	1139.4	1144.0	1147.5	1144.0
137.5°	1178.6	1187.9	1190.2	1195.9	1193.6
140°	1224.8	1231.7	1235.2	1239.8	1237.5
142.5°	1267.5	1274.4	1277.9	1281.4	1277.9
145°	1306.8	1314.8	1317.2	1319.5	1319.5
147.5°	1344.9	1350.6	1352.9	1355.2	1349.5
150°	1379.5	1383.0	1385.3	1387.6	1384.1
152.5°	1410.7	1411.8	1413.0	1417.6	1411.8
155°	1439.5	1437.2	1438.4	1444.1	1437.2
157.5°	1462.6	1462.6	1461.5	1468.4	1459.1
160°	1483.4	1482.2	1481.1	1488.0	1479.9
162.5°	1503.0	1499.5	1498.4	1506.5	1499.5
165°	1518.0	1514.6	1513.4	1522.6	1514.6
167.5°	1530.7	1526.1	1526.1	1535.3	1526.1
170°	1541.1	1536.5	1536.5	1545.7	1536.5
172.5°	1548.0	1542.3	1543.4	1552.6	1542.3
175°	1553.8	1548.0	1549.2	1557.3	1548.0
177.5°	1556.1	1550.3	1551.5	1560.7	1549.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)