

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007444

Luminaire Tested: S122IP-B925UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B925UB2750-4F0-XX-W2A-1_3500K
Description: Define 2 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3291.0 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007444

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007444

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007444

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.3	0.1
90°-100°	72.7	2.2
100°-110°	231.3	7.0
110°-120°	395.7	12.0
120°-130°	520.4	15.8
130°-140°	584.1	17.7
140°-150°	572.8	17.4
150°-160°	480.5	14.6
160°-170°	318.7	9.7
170°-180°	111.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.3	0.1
90°-120°	699.7	21.3
90°-150°	2377.1	72.2
90°-180°	3288.0	99.9
0°-180°	3291.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	35	33	34	3
95°	52	62	64	64	62	58
105°	213	216	218	220	220	225
115°	397	403	401	400	397	393
125°	578	586	584	580	580	516
135°	747	758	760	759	756	577
145°	907	914	920	921	917	567
155°	1037	1040	1043	1048	1045	477
165°	1128	1127	1127	1134	1129	318
175°	1174	1171	1169	1176	1170	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P1007444

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	12.9	34.7	32.7	33.7
92.5°	21.8	29.8	30.8	31.8	31.8
95°	51.6	61.5	63.5	63.5	61.5
97.5°	86.3	95.3	99.2	99.2	99.2
100°	126.0	134.0	136.9	136.9	136.0
102.5°	167.7	173.7	177.6	178.6	177.6
105°	213.4	216.3	218.3	220.3	220.3
107.5°	259.0	263.0	263.0	264.0	259.0
110°	302.7	308.6	308.6	308.6	305.6

TEST NUMBER: P1007444

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.3	356.2	355.3	352.3	350.3
115°	396.9	402.9	400.9	399.9	396.9
117.5°	443.6	451.5	446.6	443.6	440.6
120°	490.2	498.2	490.2	490.2	487.2
122.5°	532.9	542.8	537.8	534.9	532.9
125°	577.5	586.5	583.5	580.5	579.5
127.5°	621.2	632.1	628.2	624.2	621.2
130°	661.9	674.8	672.8	670.8	666.9
132.5°	707.5	717.5	718.5	713.5	710.5
135°	747.2	758.1	760.1	759.1	756.2
137.5°	790.9	799.8	801.8	800.8	796.8
140°	829.6	838.5	843.5	843.5	839.5
142.5°	869.3	878.2	881.2	882.2	878.2
145°	907.0	913.9	919.9	920.9	916.9
147.5°	940.7	949.7	953.6	955.6	951.7
150°	975.5	981.4	985.4	988.4	985.4
152.5°	1006.2	1012.2	1017.1	1021.1	1017.1
155°	1037.0	1040.0	1042.9	1047.9	1044.9
157.5°	1063.8	1065.8	1067.8	1074.7	1069.7
160°	1087.6	1089.6	1090.6	1096.5	1092.6
162.5°	1109.4	1109.4	1110.4	1117.4	1112.4
165°	1128.3	1127.3	1127.3	1134.2	1129.3
167.5°	1145.2	1142.2	1142.2	1149.1	1144.2
170°	1158.1	1155.1	1154.1	1161.0	1155.1
172.5°	1167.0	1164.0	1163.0	1170.0	1164.0
175°	1173.9	1171.0	1169.0	1175.9	1170.0
177.5°	1177.9	1174.9	1172.9	1178.9	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)