

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010662

Luminaire Tested: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010662
REPORT IS A COMBINATION OF REPORTS P990061 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3747.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010662

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010662

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	110	110	110	110		103	103	103	103		90	90	90		78	78	78		67	67	67
1	100	96	92	88		94	90	86	83		79	76	74		68	66	65		59	57	56
2	91	84	77	72		85	78	73	68		69	65	61		60	57	54		52	49	47
3	83	74	66	60		78	69	62	57		61	55	51		53	49	46		46	43	40
4	76	65	57	51		71	61	54	48		54	48	44		47	43	39		41	37	35
5	70	58	50	44		65	55	47	42		48	42	38		42	38	34		37	33	30
6	65	52	44	38		60	49	42	36		44	37	33		38	33	30		33	30	27
7	60	47	39	33		56	45	37	32		40	33	29		35	30	26		30	27	24
8	55	43	35	30		52	41	33	28		36	30	26		32	27	23		28	24	21
9	52	39	32	26		48	37	30	25		33	27	23		29	25	21		26	22	19
10	48	36	29	24		45	34	27	23		31	25	21		27	22	19		24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1010662

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	2.2
10°-20°	234.8	6.3
20°-30°	346.8	9.3
30°-40°	405.1	10.8
40°-50°	407.2	10.9
50°-60°	357.7	9.5
60°-70°	266.4	7.1
70°-80°	151.6	4.0
80°-90°	44.0	1.2
90°-100°	16.8	0.4
100°-110°	81.1	2.2
110°-120°	198.7	5.3
120°-130°	252.3	6.7
130°-140°	269.5	7.2
140°-150°	252.0	6.7
150°-160°	203.3	5.4
160°-170°	131.2	3.5
170°-180°	45.2	1.2
0°-30°	664.8	17.7
0°-40°	1069.9	28.6
0°-60°	1834.9	49.0
0°-90°	2296.9	61.3
90°-120°	296.6	7.9
90°-150°	1070.4	28.6
90°-180°	1450.0	38.7
0°-180°	3747.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	0	4	8	10	11	4
95°	22	7	11	13	13	26
105°	105	109	77	15	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010662

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.7	12.0
95°	21.6	7.1	11.0	13.4	13.4
97.5°	39.2	29.3	11.3	14.1	14.5
100°	59.7	66.8	11.7	14.5	14.8
102.5°	83.0	87.6	26.1	14.5	15.2
105°	105.3	109.2	77.4	14.8	15.5
107.5°	129.0	132.2	137.5	83.0	36.8
110°	152.7	155.5	159.4	147.7	97.2



TEST NUMBER: P1010662

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.3	177.7	181.6	184.8	184.1
115°	197.5	199.7	202.8	206.4	207.8
117.5°	219.4	221.9	223.7	226.5	226.9
120°	239.6	242.8	243.8	246.7	246.7
122.5°	260.1	262.6	264.0	265.7	266.1
125°	278.5	281.3	282.7	283.4	284.1
127.5°	296.8	299.7	301.4	302.5	301.8
130°	313.8	316.6	318.0	319.5	318.7
132.5°	330.1	332.9	333.9	335.4	334.3
135°	346.7	348.8	350.2	351.3	350.2
137.5°	360.8	363.6	364.3	366.1	365.4
140°	374.9	377.1	378.1	379.5	378.8
142.5°	388.0	390.1	391.2	392.2	391.2
145°	400.0	402.5	403.2	403.9	403.9
147.5°	411.7	413.5	414.2	414.9	413.1
150°	422.3	423.3	424.1	424.8	423.7
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)