

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007454

Luminaire Tested: S122IP-B925UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007454
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B925UB2750-4F0-XX-W2A_3500K
Description: Define 2 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3681.0 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007454

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1007454

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007454

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.2	0.1
90°-100°	41.4	1.1
100°-110°	154.2	4.2
110°-120°	409.1	11.1
120°-130°	678.5	18.4
130°-140°	720.7	19.6
140°-150°	669.9	18.2
150°-160°	538.5	14.6
160°-170°	347.0	9.4
170°-180°	119.4	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.2	0.1
90°-120°	604.7	16.4
90°-150°	2673.8	72.6
90°-180°	3679.0	99.9
0°-180°	3681.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	18	23	24	3
95°	59	29	35	40	39	70
105°	276	303	55	65	69	295
115°	522	538	560	140	74	514
125°	738	750	767	774	776	658
135°	913	928	936	945	943	706
145°	1060	1059	1074	1080	1076	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1007454

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.9	10.9	18.2	22.7	24.5
92.5°	22.7	19.1	21.8	23.6	24.5
95°	59.0	29.1	35.4	40.0	39.0
97.5°	106.2	31.8	46.3	49.0	49.9
100°	160.7	36.3	51.8	59.0	60.8
102.5°	220.6	218.8	53.6	63.6	66.3
105°	276.0	303.3	55.4	65.4	69.0
107.5°	340.5	363.2	57.2	67.2	70.8
110°	402.2	421.3	158.9	68.1	71.7

TEST NUMBER: P1007454

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.4	476.7	461.3	69.9	72.6
115°	522.1	537.5	560.2	139.8	74.5
117.5°	575.7	593.8	609.3	479.4	241.5
120°	635.6	649.2	665.6	676.5	553.9
122.5°	686.4	701.0	719.1	724.6	725.5
125°	738.2	750.0	767.3	773.6	776.3
127.5°	785.4	798.1	811.8	820.8	821.7
130°	829.9	844.4	854.4	864.4	863.5
132.5°	875.3	887.1	897.1	905.3	904.4
135°	913.4	928.0	936.1	945.2	943.4
137.5°	953.4	964.3	973.4	982.5	979.7
140°	992.4	999.7	1009.7	1017.9	1013.3
142.5°	1025.1	1031.5	1043.3	1050.6	1046.0
145°	1059.6	1058.7	1074.2	1080.5	1076.0
147.5°	1089.6	1086.9	1102.3	1106.9	1103.2
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)