

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007455

Luminaire Tested: S122IP-B925UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B925UB2750-4F0-XX-W2A_4000K
Description: Define 2 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3645.0 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007455

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007455

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007455

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.2	0.1
90°-100°	41.0	1.1
100°-110°	152.7	4.2
110°-120°	405.1	11.1
120°-130°	671.9	18.4
130°-140°	713.7	19.6
140°-150°	663.3	18.2
150°-160°	533.3	14.6
160°-170°	343.6	9.4
170°-180°	118.3	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.2	0.1
90°-120°	598.8	16.4
90°-150°	2647.7	72.6
90°-180°	3643.0	99.9
0°-180°	3645.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	18	22	24	3
95°	58	29	35	40	39	69
105°	273	300	55	65	68	292
115°	517	532	555	138	74	509
125°	731	743	760	766	769	652
135°	904	919	927	936	934	699
145°	1049	1048	1064	1070	1066	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1007455

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.9	10.8	18.0	22.5	24.3
92.5°	22.5	18.9	21.6	23.4	24.3
95°	58.4	28.8	35.1	39.6	38.7
97.5°	105.2	31.5	45.9	48.6	49.5
100°	159.1	36.0	51.2	58.4	60.2
102.5°	218.5	216.7	53.0	62.9	65.6
105°	273.3	300.3	54.8	64.7	68.3
107.5°	337.2	359.6	56.6	66.5	70.1
110°	398.3	417.2	157.3	67.4	71.0

TEST NUMBER: P1007455

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	455.9	472.0	456.8	69.2	71.9
115°	517.0	532.3	554.8	138.5	73.7
117.5°	570.0	588.0	603.3	474.7	239.2
120°	629.4	642.9	659.1	669.8	548.5
122.5°	679.7	694.1	712.1	717.5	718.4
125°	731.0	742.7	759.8	766.0	768.7
127.5°	777.7	790.3	803.8	812.8	813.7
130°	821.8	836.2	846.1	856.0	855.1
132.5°	866.8	878.4	888.3	896.4	895.5
135°	904.5	918.9	927.0	936.0	934.2
137.5°	944.1	954.9	963.9	972.8	970.1
140°	982.7	989.9	999.8	1007.9	1003.4
142.5°	1015.1	1021.4	1033.1	1040.3	1035.8
145°	1049.3	1048.4	1063.7	1070.0	1065.5
147.5°	1078.9	1076.2	1091.5	1096.0	1092.4
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)