

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007319

Luminaire Tested: S122IP-B1080UB27-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B1080UB27-4F0-XX-W2A-1
Description: Define 2 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3817.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007319

CATALOG NUMBER: S122IP-B1080UB27-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007319

CATALOG NUMBER: S122IP-B1080UB27-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007319

CATALOG NUMBER: S122IP-B1080UB27-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.9	0.1
90°-100°	84.4	2.2
100°-110°	268.2	7.0
110°-120°	458.9	12.0
120°-130°	603.6	15.8
130°-140°	677.5	17.7
140°-150°	664.4	17.4
150°-160°	557.3	14.6
160°-170°	369.6	9.7
170°-180°	129.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.9	0.1
90°-120°	811.5	21.3
90°-150°	2757.0	72.2
90°-180°	3813.0	99.9
0°-180°	3817.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	15	40	38	39	4
95°	60	71	74	74	71	67
105°	248	251	253	256	256	261
115°	460	467	465	464	460	455
125°	670	680	677	673	672	599
135°	867	879	882	880	877	670
145°	1052	1060	1067	1068	1064	657
155°	1203	1206	1210	1215	1212	554
165°	1309	1308	1308	1316	1310	369
175°	1362	1358	1356	1364	1357	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P1007319

CATALOG NUMBER: S122IP-B1080UB27-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	15.0	40.3	38.0	39.1
92.5°	25.3	34.5	35.7	36.8	36.8
95°	59.8	71.4	73.7	73.7	71.4
97.5°	100.1	110.5	115.1	115.1	115.1
100°	146.2	155.4	158.8	158.8	157.7
102.5°	194.5	201.4	206.0	207.2	206.0
105°	247.5	250.9	253.2	255.5	255.5
107.5°	300.4	305.0	305.0	306.2	300.4
110°	351.0	357.9	357.9	357.9	354.5

TEST NUMBER: P1007319

CATALOG NUMBER: S122IP-B1080UB27-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	406.3	413.2	412.0	408.6	406.3
115°	460.4	467.3	465.0	463.8	460.4
117.5°	514.5	523.7	517.9	514.5	511.0
120°	568.6	577.8	568.6	568.6	565.1
122.5°	618.1	629.6	623.8	620.4	618.1
125°	669.8	680.2	676.8	673.3	672.2
127.5°	720.5	733.2	728.5	723.9	720.5
130°	767.7	782.6	780.3	778.0	773.4
132.5°	820.6	832.1	833.3	827.5	824.1
135°	866.7	879.3	881.6	880.5	877.0
137.5°	917.3	927.7	930.0	928.8	924.2
140°	962.2	972.5	978.3	978.3	973.7
142.5°	1008.2	1018.6	1022.0	1023.2	1018.6
145°	1052.0	1060.0	1066.9	1068.1	1063.5
147.5°	1091.1	1101.5	1106.1	1108.4	1103.8
150°	1131.4	1138.3	1142.9	1146.3	1142.9
152.5°	1167.1	1174.0	1179.7	1184.3	1179.7
155°	1202.7	1206.2	1209.6	1215.4	1211.9
157.5°	1233.8	1236.1	1238.4	1246.5	1240.7
160°	1261.4	1263.7	1264.9	1271.8	1267.2
162.5°	1286.8	1286.8	1287.9	1296.0	1290.2
165°	1308.6	1307.5	1307.5	1315.5	1309.8
167.5°	1328.2	1324.7	1324.7	1332.8	1327.0
170°	1343.2	1339.7	1338.5	1346.6	1339.7
172.5°	1353.5	1350.1	1348.9	1357.0	1350.1
175°	1361.6	1358.1	1355.8	1363.9	1357.0
177.5°	1366.2	1362.7	1360.4	1367.3	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9

(END OF REPORT)