

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007343

Luminaire Tested: S122IP-B1080UB40-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B1080UB40-4F0-XX-W2A-1
Description: Define 2 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3828.0 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007343

CATALOG NUMBER: S122IP-B1080UB40-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007343

CATALOG NUMBER: S122IP-B1080UB40-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007343

CATALOG NUMBER: S122IP-B1080UB40-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.9	0.1
90°-100°	84.6	2.2
100°-110°	269.0	7.0
110°-120°	460.3	12.0
120°-130°	605.3	15.8
130°-140°	679.5	17.7
140°-150°	666.3	17.4
150°-160°	558.9	14.6
160°-170°	370.7	9.7
170°-180°	129.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.9	0.1
90°-120°	813.9	21.3
90°-150°	2764.9	72.2
90°-180°	3824.0	99.9
0°-180°	3828.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	15	40	38	39	4
95°	60	72	74	74	72	67
105°	248	252	254	256	256	262
115°	462	469	466	465	462	457
125°	672	682	679	675	674	600
135°	869	882	884	883	880	672
145°	1055	1063	1070	1071	1066	659
155°	1206	1210	1213	1219	1215	555
165°	1312	1311	1311	1319	1314	370
175°	1366	1362	1360	1368	1361	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P1007343

CATALOG NUMBER: S122IP-B1080UB40-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	15.0	40.4	38.1	39.2
92.5°	25.4	34.6	35.8	36.9	36.9
95°	60.0	71.6	73.9	73.9	71.6
97.5°	100.4	110.8	115.4	115.4	115.4
100°	146.6	155.8	159.3	159.3	158.1
102.5°	195.1	202.0	206.6	207.8	206.6
105°	248.2	251.6	253.9	256.2	256.2
107.5°	301.3	305.9	305.9	307.0	301.3
110°	352.0	359.0	359.0	359.0	355.5

TEST NUMBER: P1007343

CATALOG NUMBER: S122IP-B1080UB40-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	407.5	414.4	413.2	409.8	407.5
115°	461.7	468.6	466.3	465.2	461.7
117.5°	516.0	525.2	519.4	516.0	512.5
120°	570.2	579.4	570.2	570.2	566.7
122.5°	619.8	631.4	625.6	622.1	619.8
125°	671.8	682.2	678.7	675.2	674.1
127.5°	722.6	735.3	730.6	726.0	722.6
130°	769.9	784.9	782.6	780.3	775.7
132.5°	823.0	834.5	835.7	829.9	826.5
135°	869.2	881.9	884.2	883.0	879.5
137.5°	919.9	930.3	932.6	931.5	926.9
140°	965.0	975.4	981.1	981.1	976.5
142.5°	1011.1	1021.5	1025.0	1026.1	1021.5
145°	1055.0	1063.1	1070.0	1071.2	1066.5
147.5°	1094.2	1104.6	1109.2	1111.6	1106.9
150°	1134.6	1141.6	1146.2	1149.6	1146.2
152.5°	1170.4	1177.3	1183.1	1187.7	1183.1
155°	1206.2	1209.7	1213.1	1218.9	1215.4
157.5°	1237.4	1239.7	1242.0	1250.1	1244.3
160°	1265.1	1267.4	1268.5	1275.5	1270.8
162.5°	1290.5	1290.5	1291.6	1299.7	1293.9
165°	1312.4	1311.2	1311.2	1319.3	1313.5
167.5°	1332.0	1328.6	1328.6	1336.6	1330.9
170°	1347.0	1343.6	1342.4	1350.5	1343.6
172.5°	1357.4	1353.9	1352.8	1360.9	1353.9
175°	1365.5	1362.0	1359.7	1367.8	1360.9
177.5°	1370.1	1366.6	1364.3	1371.3	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8

(END OF REPORT)