

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010676

Luminaire Tested: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010676
REPORT IS A COMBINATION OF REPORTS P990120 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4676.0 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010676

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010676

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25
6	63	51	42	37	58	47	40	34	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1010676

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.8
10°-20°	237.2	5.1
20°-30°	350.3	7.5
30°-40°	409.1	8.7
40°-50°	411.3	8.8
50°-60°	361.3	7.7
60°-70°	269.1	5.8
70°-80°	153.1	3.3
80°-90°	45.1	1.0
90°-100°	27.2	0.6
100°-110°	131.7	2.8
110°-120°	322.8	6.9
120°-130°	409.8	8.8
130°-140°	437.8	9.4
140°-150°	409.4	8.8
150°-160°	330.2	7.1
160°-170°	213.1	4.6
170°-180°	73.4	1.6
0°-30°	671.5	14.4
0°-40°	1080.6	23.1
0°-60°	1853.3	39.6
0°-90°	2320.6	49.6
90°-120°	481.8	10.3
90°-150°	1738.7	37.2
90°-180°	2355.0	50.4
0°-180°	4676.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	1	6	14	16	17	5
95°	35	12	18	22	22	42
105°	171	177	126	24	25	181
115°	321	324	330	335	338	317
125°	452	457	459	460	462	404
135°	563	567	569	571	569	434
145°	650	654	655	656	656	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010676

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	0.6	6.3	13.8	16.1	17.2
92.5°	13.2	9.8	14.9	18.9	19.5
95°	35.0	11.5	17.8	21.8	21.8
97.5°	63.7	47.6	18.4	23.0	23.5
100°	97.0	108.5	18.9	23.5	24.1
102.5°	134.9	142.4	42.5	23.5	24.7
105°	171.1	177.4	125.7	24.1	25.3
107.5°	209.5	214.7	223.3	134.9	59.7
110°	248.0	252.6	258.9	239.9	157.9



TEST NUMBER: P1010676

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	288.7	295.0	300.2	299.1
115°	320.9	324.3	329.5	335.2	337.5
117.5°	356.5	360.5	363.4	368.0	368.5
120°	389.2	394.4	396.1	400.7	400.7
122.5°	422.5	426.5	428.8	431.7	432.2
125°	452.3	456.9	459.2	460.4	461.5
127.5°	482.2	486.8	489.6	491.4	490.2
130°	509.7	514.3	516.6	518.9	517.8
132.5°	536.1	540.7	542.5	544.8	543.0
135°	563.1	566.6	568.9	570.6	568.9
137.5°	586.1	590.7	591.8	594.7	593.5
140°	609.0	612.5	614.2	616.5	615.4
142.5°	630.3	633.7	635.4	637.2	635.4
145°	649.8	653.8	655.0	656.1	656.1
147.5°	668.7	671.6	672.8	673.9	671.0
150°	686.0	687.7	688.8	690.0	688.3
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)