

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010684

Luminaire Tested: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010684
REPORT IS A COMBINATION OF REPORTS P990173 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5441.0 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010684

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010684

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	105	105	105	105		95	95	95	95		77	77	77		61	61	61		46	46	46
1	95	90	86	82		86	82	78	75		67	64	62		53	51	49		40	38	37
2	86	78	72	66		78	71	66	61		58	54	50		46	43	40		34	33	31
3	78	68	61	55		70	62	56	50		51	46	42		40	37	34		30	28	26
4	71	60	52	46		64	55	48	42		45	40	35		35	32	29		27	24	22
5	65	53	45	39		59	49	42	36		40	35	30		32	28	25		24	21	19
6	60	48	40	34		54	44	37	31		36	30	26		29	25	21		22	19	17
7	55	43	35	29		50	39	32	27		32	27	23		26	22	19		20	17	15
8	51	39	31	26		46	36	29	24		29	24	20		24	20	17		18	15	13
9	48	35	28	23		43	33	26	21		27	22	18		22	18	15		17	14	12
10	44	32	25	20		40	30	23	19		25	20	16		20	16	13		16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7472	7472	7472
5°	7492	7253	7247
10°	7423	7056	7003
15°	7325	6840	6743
20°	7184	6598	6464
25°	7013	6325	6177
30°	6838	6078	5887
35°	6641	5820	5651
40°	6452	5584	5402
45°	6243	5355	5196
50°	6038	5128	4974
55°	5809	4895	4769
60°	5586	4657	4558
65°	5357	4403	4313
70°	5009	4120	4059
75°	4572	3795	3797
80°	4066	3466	3499
85°	3564	3200	3285

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6243 cd/sqm

TEST NUMBER: P1010684

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.2
10°-20°	187.7	3.5
20°-30°	280.7	5.2
30°-40°	335.2	6.2
40°-50°	350.7	6.4
50°-60°	329.1	6.0
60°-70°	274.9	5.1
70°-80°	196.5	3.6
80°-90°	119.0	2.2
90°-100°	109.4	2.0
100°-110°	227.7	4.2
110°-120°	461.7	8.5
120°-130°	561.0	10.3
130°-140°	586.5	10.8
140°-150°	541.7	10.0
150°-160°	435.4	8.0
160°-170°	281.0	5.2
170°-180°	96.8	1.8
0°-30°	534.3	9.8
0°-40°	869.5	16.0
0°-60°	1549.3	28.5
0°-90°	2139.7	39.3
90°-120°	798.9	14.7
90°-150°	2488.1	45.7
90°-180°	3301.0	60.7
0°-180°	5441.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	695	693	689	695	694	66
15°	662	664	663	671	670	186
25°	597	605	607	617	617	275
35°	514	526	536	548	550	322
45°	420	439	458	472	478	324
55°	321	346	373	393	399	287
65°	222	251	284	307	315	219
75°	120	156	194	218	228	128
85°	37	75	115	141	148	38
90°	11	55	104	132	141	10
95°	54	53	98	127	135	62
105°	232	258	222	110	118	245
115°	427	441	475	500	509	422
125°	599	605	630	647	654	535
135°	744	748	759	775	777	573
145°	858	862	864	871	874	537
155°	944	942	943	947	942	435
165°	995	993	992	998	993	281
175°	1019	1015	1016	1021	1015	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1010684

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	694.2	694.2	694.2	694.2	694.2
2.5°	698.0	695.7	689.6	695.7	694.9
5°	694.9	693.4	688.9	694.9	694.2
7.5°	689.6	689.6	685.1	692.7	691.9
10°	682.1	683.6	679.8	687.4	685.9
12.5°	673.0	675.3	673.0	679.8	678.3
15°	661.7	663.9	663.2	670.7	670.0
17.5°	648.1	652.6	651.8	658.6	657.1
20°	632.9	637.5	639.0	645.8	646.5
22.5°	617.1	621.6	623.9	632.9	632.2
25°	597.4	605.0	607.2	617.1	617.1
27.5°	578.5	586.8	591.3	599.7	600.4
30°	558.1	567.9	573.9	583.0	583.0
32.5°	535.4	546.7	555.0	564.9	567.1
35°	514.2	526.3	536.1	547.5	550.5
37.5°	491.5	505.1	516.5	529.3	531.6
40°	468.8	482.4	497.6	510.4	513.5
42.5°	443.9	461.3	477.2	491.5	496.1
45°	420.4	438.6	457.5	471.9	477.9
47.5°	395.5	415.9	437.1	453.0	457.5
50°	371.3	392.5	415.9	433.3	438.6
52.5°	345.6	368.3	394.7	412.9	419.7
55°	320.6	345.6	372.8	393.2	399.3
57.5°	296.4	322.1	351.6	372.0	378.9
60°	270.7	297.9	328.9	350.1	358.4
62.5°	246.5	274.5	307.8	328.9	336.5
65°	221.6	251.1	284.3	307.0	314.6
67.5°	196.6	227.6	260.9	285.8	291.9
70°	170.1	202.7	239.0	263.2	270.7
72.5°	145.9	178.5	216.3	241.2	248.8
75°	120.2	155.8	193.6	218.5	227.6
77.5°	98.3	133.8	171.7	198.1	204.9
80°	74.9	111.9	151.2	176.9	184.5
82.5°	54.4	92.3	132.3	158.0	165.6
85°	37.1	74.9	114.9	140.7	148.2
87.5°	22.7	60.5	99.1	124.8	132.3
90°	10.6	55.2	103.6	132.4	141.4
92.5°	26.5	54.5	99.1	129.4	136.9
95°	54.5	52.9	98.4	127.1	134.7
97.5°	91.6	97.6	94.5	123.3	131.6
100°	134.7	174.1	90.8	118.7	127.1
102.5°	183.9	214.9	117.3	113.4	122.5
105°	231.6	258.1	222.5	109.7	118.0
107.5°	281.6	304.3	346.6	250.5	158.1
110°	331.5	351.1	389.8	384.5	282.3

TEST NUMBER: P1010684

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.9	395.8	433.0	458.7	464.0
115°	426.9	440.6	474.6	500.2	509.4
117.5°	473.9	485.1	514.6	538.9	545.6
120°	516.2	526.8	554.1	577.5	582.7
122.5°	560.1	566.9	593.4	613.8	619.9
125°	598.8	604.8	629.7	647.2	654.0
127.5°	638.1	643.4	666.1	683.4	687.2
130°	674.5	679.7	697.8	715.3	718.2
132.5°	708.5	714.5	728.2	744.8	747.9
135°	744.0	747.9	759.2	775.1	776.6
137.5°	774.3	779.7	786.4	802.3	804.6
140°	803.9	808.4	812.9	827.3	829.5
142.5°	831.9	835.6	837.9	850.0	851.5
145°	857.6	862.1	863.7	871.2	874.3
147.5°	881.8	885.6	887.1	890.9	890.1
150°	904.5	906.8	908.3	909.8	909.1
152.5°	925.0	925.7	926.5	929.5	925.7
155°	943.9	942.4	943.1	946.9	942.4
157.5°	959.0	959.0	958.3	962.8	956.8
160°	972.6	971.9	971.1	975.7	970.4
162.5°	985.5	983.2	982.5	987.8	983.2
165°	995.4	993.1	992.3	998.4	993.1
167.5°	1003.7	1000.7	1000.7	1006.7	1000.7
170°	1010.5	1007.5	1007.5	1013.5	1007.5
172.5°	1015.0	1011.3	1012.0	1018.1	1011.3
175°	1018.8	1015.0	1015.8	1021.1	1015.0
177.5°	1020.3	1016.6	1017.3	1023.4	1015.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)