

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010402

Luminaire Tested: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010402
REPORT IS A COMBINATION OF REPORTS P989036 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8184.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010402

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010402

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			46
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43			37
2	87	79	73	67	79	73	67	62	61	56	53	50	46	44	39	37	35			30
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	30			25
4	72	61	53	47	66	56	49	43	47	42	37	39	34	31	31	28	25			21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22			18
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19			16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	21	23	19	17			14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15			13
9	49	36	29	23	44	33	27	22	28	23	19	24	19	16	19	16	14			11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13291	13291	13291
5°	13328	12901	12891
10°	13203	12552	12456
15°	13029	12166	11995
20°	12781	11736	11500
25°	12476	11251	10987
30°	12163	10814	10472
35°	11813	10353	10053
40°	11478	9932	9608
45°	11107	9525	9243
50°	10741	9122	8847
55°	10333	8708	8482
60°	9937	8284	8108
65°	9527	7834	7672
70°	8914	7328	7221
75°	8137	6751	6755
80°	7231	6166	6224
85°	6330	5695	5843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11107 cd/sqm

TEST NUMBER: P1010402

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.1	1.4
10°-20°	333.9	4.1
20°-30°	499.4	6.1
30°-40°	596.2	7.3
40°-50°	623.8	7.6
50°-60°	585.4	7.2
60°-70°	489.0	6.0
70°-80°	349.6	4.3
80°-90°	210.7	2.6
90°-100°	177.4	2.2
100°-110°	321.6	3.9
110°-120°	616.7	7.5
120°-130°	738.0	9.0
130°-140°	765.7	9.4
140°-150°	704.1	8.6
150°-160°	565.1	6.9
160°-170°	364.7	4.5
170°-180°	125.7	1.5
0°-30°	950.4	11.6
0°-40°	1546.6	18.9
0°-60°	2755.9	33.7
0°-90°	3805.2	46.5
90°-120°	1115.6	13.6
90°-150°	3323.3	40.6
90°-180°	4379.0	53.5
0°-180°	8184.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1235	1235	1235	1235	1235	
5°	1236	1234	1225	1236	1235	117
15°	1177	1181	1180	1193	1192	332
25°	1063	1076	1080	1098	1098	490
35°	915	936	954	974	979	572
45°	748	780	814	839	850	577
55°	570	615	663	700	710	511
65°	394	447	506	546	560	390
75°	214	277	344	389	405	228
85°	66	133	204	250	264	68
90°	18	94	176	225	241	16
95°	75	87	164	212	226	83
105°	304	347	316	180	194	321
115°	556	578	635	677	692	549
125°	778	786	829	859	871	696
135°	966	971	990	1017	1021	744
145°	1113	1119	1121	1134	1139	697
155°	1225	1223	1224	1229	1223	564
165°	1292	1289	1288	1296	1289	365
175°	1322	1318	1318	1325	1318	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1010402

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1234.8	1234.8	1234.8	1234.8	1234.8
2.5°	1241.6	1237.5	1226.8	1237.5	1236.2
5°	1236.2	1233.5	1225.4	1236.2	1234.8
7.5°	1226.8	1226.8	1218.7	1232.1	1230.8
10°	1213.3	1216.0	1209.3	1222.7	1220.0
12.5°	1197.2	1201.2	1197.2	1209.3	1206.6
15°	1177.0	1181.0	1179.7	1193.1	1191.8
17.5°	1152.8	1160.8	1159.5	1171.6	1168.9
20°	1125.9	1133.9	1136.6	1148.7	1150.1
22.5°	1097.6	1105.7	1109.7	1125.9	1124.5
25°	1062.7	1076.1	1080.1	1097.6	1097.6
27.5°	1029.0	1043.8	1051.9	1066.7	1068.0
30°	992.7	1010.2	1021.0	1037.1	1037.1
32.5°	952.4	972.5	987.3	1004.8	1008.8
35°	914.7	936.2	953.7	973.9	979.3
37.5°	874.3	898.5	918.7	941.6	945.6
40°	834.0	858.2	885.1	908.0	913.3
42.5°	789.6	820.5	848.8	874.3	882.4
45°	747.9	780.2	813.8	839.4	850.1
47.5°	703.5	739.8	777.5	805.7	813.8
50°	660.5	698.1	739.8	770.8	780.2
52.5°	614.7	655.1	702.2	734.4	746.5
55°	570.3	614.7	663.2	699.5	710.2
57.5°	527.3	573.0	625.5	661.8	673.9
60°	481.6	530.0	585.1	622.8	637.6
62.5°	438.5	488.3	547.5	585.1	598.6
65°	394.1	446.6	505.8	546.1	559.6
67.5°	349.7	404.9	464.1	508.5	519.2
70°	302.7	360.5	425.1	468.1	481.6
72.5°	259.6	317.5	384.7	429.1	442.5
75°	213.9	277.1	344.4	388.7	404.9
77.5°	174.9	238.1	305.3	352.4	364.5
80°	133.2	199.1	269.0	314.8	328.2
82.5°	96.8	164.1	235.4	281.1	294.6
85°	65.9	133.2	204.5	250.2	263.6
87.5°	40.4	107.6	176.2	221.9	235.4
90°	18.5	94.2	175.6	225.2	240.7
92.5°	38.7	90.7	166.7	218.0	231.1
95°	74.7	86.9	163.7	212.2	225.6
97.5°	122.6	143.4	156.5	204.8	219.2
100°	178.1	240.9	149.4	196.3	210.8
102.5°	241.7	292.0	181.7	186.9	202.3
105°	303.6	346.6	316.1	179.8	193.9
107.5°	368.0	405.1	475.0	360.0	243.4
110°	432.5	464.6	529.2	531.8	402.0

TEST NUMBER: P1010402

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.4	521.1	583.0	625.4	635.7
115°	555.9	578.0	635.2	677.3	692.0
117.5°	616.8	634.5	685.1	725.2	737.0
120°	671.5	687.0	734.4	773.1	782.5
122.5°	728.5	738.1	783.7	818.2	828.6
125°	778.2	786.0	829.0	859.2	870.6
127.5°	829.3	835.8	874.3	904.2	911.6
130°	876.4	883.0	913.8	943.3	949.4
132.5°	920.3	928.2	951.3	979.4	985.9
135°	966.5	971.0	989.7	1017.0	1020.7
137.5°	1005.8	1012.2	1023.7	1050.1	1054.8
140°	1043.7	1049.6	1056.6	1080.7	1085.5
142.5°	1080.0	1084.6	1087.6	1108.0	1111.8
145°	1113.4	1119.0	1121.0	1133.7	1139.0
147.5°	1144.5	1149.5	1151.4	1157.4	1157.9
150°	1174.0	1177.0	1178.9	1180.9	1180.7
152.5°	1200.5	1201.5	1202.5	1206.4	1201.5
155°	1225.1	1223.1	1224.1	1229.0	1223.1
157.5°	1244.8	1244.8	1243.8	1249.7	1241.8
160°	1262.4	1261.5	1260.5	1266.4	1259.5
162.5°	1279.1	1276.2	1275.2	1282.1	1276.2
165°	1291.9	1289.0	1288.0	1295.8	1289.0
167.5°	1302.7	1298.8	1298.8	1306.7	1298.8
170°	1311.6	1307.6	1307.6	1315.5	1307.6
172.5°	1317.5	1312.5	1313.5	1321.4	1312.5
175°	1322.4	1317.5	1318.4	1325.3	1317.5
177.5°	1324.3	1319.4	1320.4	1328.3	1318.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)