

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010691

Luminaire Tested: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010691
REPORT IS A COMBINATION OF REPORTS P990180 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5468.0 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010691

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010691

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1010691

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.5
10°-20°	237.2	4.3
20°-30°	350.3	6.4
30°-40°	409.1	7.5
40°-50°	411.3	7.5
50°-60°	361.3	6.6
60°-70°	269.1	4.9
70°-80°	153.1	2.8
80°-90°	45.6	0.8
90°-100°	36.4	0.7
100°-110°	176.0	3.2
110°-120°	431.3	7.9
120°-130°	547.5	10.0
130°-140°	584.9	10.7
140°-150°	546.9	10.0
150°-160°	441.1	8.1
160°-170°	284.7	5.2
170°-180°	98.1	1.8
0°-30°	671.5	12.3
0°-40°	1080.6	19.8
0°-60°	1853.3	33.9
0°-90°	2321.1	42.4
90°-120°	643.7	11.8
90°-150°	2323.0	42.5
90°-180°	3147.0	57.6
0°-180°	5468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	1	8	18	22	23	5
95°	47	15	24	29	29	56
105°	228	237	168	32	34	242
115°	429	433	440	448	451	423
125°	604	610	614	615	617	540
135°	752	757	760	762	760	579
145°	868	874	875	877	877	544
155°	956	955	956	959	955	441
165°	1008	1006	1005	1012	1006	285
175°	1032	1028	1029	1035	1028	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1010691

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	0.8	8.4	18.4	21.5	23.0
92.5°	17.6	13.0	19.9	25.3	26.1
95°	46.8	15.3	23.8	29.1	29.1
97.5°	85.1	63.7	24.5	30.7	31.4
100°	129.6	144.9	25.3	31.4	32.2
102.5°	180.2	190.2	56.8	31.4	33.0
105°	228.5	237.0	168.0	32.2	33.7
107.5°	279.9	286.8	298.3	180.2	79.8
110°	331.3	337.4	345.9	320.6	210.9

TEST NUMBER: P1010691

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.8	394.2	401.1	399.6
115°	428.7	433.3	440.2	447.9	450.9
117.5°	476.3	481.6	485.5	491.6	492.4
120°	520.0	526.9	529.2	535.3	535.3
122.5°	564.4	569.8	572.9	576.7	577.5
125°	604.3	610.5	613.5	615.1	616.6
127.5°	644.2	650.3	654.2	656.5	654.9
130°	681.0	687.2	690.2	693.3	691.8
132.5°	716.3	722.4	724.7	727.8	725.5
135°	752.3	756.9	760.0	762.3	760.0
137.5°	783.0	789.2	790.7	794.5	793.0
140°	813.7	818.3	820.6	823.7	822.1
142.5°	842.1	846.7	849.0	851.3	849.0
145°	868.1	873.5	875.0	876.6	876.6
147.5°	893.5	897.3	898.8	900.4	896.5
150°	916.5	918.8	920.3	921.8	919.5
152.5°	937.2	937.9	938.7	941.8	937.9
155°	956.3	954.8	955.6	959.4	954.8
157.5°	971.7	971.7	970.9	975.5	969.4
160°	985.5	984.7	983.9	988.5	983.2
162.5°	998.5	996.2	995.5	1000.8	996.2
165°	1008.5	1006.2	1005.4	1011.6	1006.2
167.5°	1016.9	1013.9	1013.9	1020.0	1013.9
170°	1023.8	1020.8	1020.8	1026.9	1020.8
172.5°	1028.4	1024.6	1025.4	1031.5	1024.6
175°	1032.3	1028.4	1029.2	1034.6	1028.4
177.5°	1033.8	1030.0	1030.7	1036.9	1029.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)