

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010418

Luminaire Tested: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010418
REPORT IS A COMBINATION OF REPORTS P989097 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8597.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010418

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010418

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	78	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	19	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12888	12476	12466
10°	12768	12138	12046
15°	12598	11764	11599
20°	12358	11349	11120
25°	12064	10880	10624
30°	11761	10457	10127
35°	11423	10011	9720
40°	11100	9605	9292
45°	10740	9211	8939
50°	10386	8821	8555
55°	9993	8421	8203
60°	9609	8011	7840
65°	9213	7575	7418
70°	8620	7085	6983
75°	7867	6528	6532
80°	6993	5962	6019
85°	6119	5505	5650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10740 cd/sqm

TEST NUMBER: P1010418

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.3	1.3
10°-20°	322.9	3.8
20°-30°	482.9	5.6
30°-40°	576.5	6.7
40°-50°	603.2	7.0
50°-60°	566.1	6.6
60°-70°	472.8	5.5
70°-80°	338.1	3.9
80°-90°	204.2	2.4
90°-100°	179.4	2.1
100°-110°	349.1	4.1
110°-120°	689.9	8.0
120°-130°	832.4	9.7
130°-140°	867.3	10.1
140°-150°	799.5	9.3
150°-160°	642.2	7.5
160°-170°	414.4	4.8
170°-180°	142.8	1.7
0°-30°	919.1	10.7
0°-40°	1495.6	17.4
0°-60°	2664.9	31.0
0°-90°	3680.0	42.8
90°-120°	1218.4	14.2
90°-150°	3717.5	43.2
90°-180°	4917.0	57.2
0°-180°	8597.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1194	1194	1194	1194	1194	
5°	1195	1193	1185	1195	1194	113
15°	1138	1142	1141	1154	1152	321
25°	1028	1041	1044	1061	1061	474
35°	884	905	922	942	947	553
45°	723	754	787	812	822	558
55°	552	594	641	676	687	494
65°	381	432	489	528	541	377
75°	207	268	333	376	392	221
85°	64	129	198	242	255	66
90°	18	93	174	222	238	16
95°	82	87	163	212	224	92
105°	343	387	342	181	195	363
115°	631	653	710	752	767	623
125°	884	892	935	964	976	790
135°	1098	1103	1122	1149	1152	845
145°	1265	1272	1274	1286	1292	792
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010418

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1194.1	1194.1	1194.1	1194.1	1194.1
2.5°	1200.6	1196.7	1186.3	1196.7	1195.4
5°	1195.4	1192.8	1185.0	1195.4	1194.1
7.5°	1186.3	1186.3	1178.5	1191.5	1190.2
10°	1173.3	1175.9	1169.4	1182.4	1179.8
12.5°	1157.6	1161.5	1157.6	1169.4	1166.8
15°	1138.1	1142.0	1140.7	1153.7	1152.4
17.5°	1114.7	1122.5	1121.2	1132.9	1130.3
20°	1088.7	1096.5	1099.1	1110.8	1112.1
22.5°	1061.4	1069.2	1073.1	1088.7	1087.4
25°	1027.6	1040.6	1044.5	1061.4	1061.4
27.5°	995.1	1009.4	1017.2	1031.5	1032.8
30°	959.9	976.8	987.3	1002.9	1002.9
32.5°	920.9	940.4	954.7	971.6	975.5
35°	884.5	905.3	922.2	941.7	946.9
37.5°	845.5	868.9	888.4	910.5	914.4
40°	806.5	829.9	855.9	878.0	883.2
42.5°	763.5	793.4	820.8	845.5	853.3
45°	723.2	754.4	786.9	811.7	822.1
47.5°	680.3	715.4	751.8	779.1	786.9
50°	638.7	675.1	715.4	745.3	754.4
52.5°	594.4	633.5	679.0	710.2	721.9
55°	551.5	594.4	641.3	676.4	686.8
57.5°	509.9	554.1	604.8	640.0	651.7
60°	465.7	512.5	565.8	602.2	616.5
62.5°	424.0	472.2	529.4	565.8	578.8
65°	381.1	431.8	489.1	528.1	541.1
67.5°	338.2	391.5	448.8	491.7	502.1
70°	292.7	348.6	411.0	452.7	465.7
72.5°	251.0	307.0	372.0	414.9	427.9
75°	206.8	267.9	333.0	375.9	391.5
77.5°	169.1	230.2	295.3	340.8	352.5
80°	128.8	192.5	260.1	304.4	317.4
82.5°	93.7	158.7	227.6	271.9	284.9
85°	63.7	128.8	197.7	241.9	254.9
87.5°	39.0	104.1	170.4	214.6	227.6
90°	18.0	92.9	173.8	222.5	237.7
92.5°	41.3	90.5	165.6	216.3	229.2
95°	82.4	87.3	163.4	211.5	224.5
97.5°	136.9	152.5	156.7	204.7	218.8
100°	200.4	264.3	150.0	196.7	210.8
102.5°	272.8	323.7	188.0	187.6	202.8
105°	343.1	386.6	342.1	180.9	194.8
107.5°	416.6	453.9	524.1	387.3	252.7
110°	490.1	522.4	586.7	583.8	434.5

TEST NUMBER: P1010418

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	561.5	587.5	649.2	691.9	701.3
115°	630.6	652.9	709.7	752.2	767.0
117.5°	699.8	718.0	767.8	808.0	819.5
120°	762.1	778.7	824.9	863.7	872.9
122.5°	826.9	837.3	882.0	916.2	926.4
125°	883.6	892.5	934.7	964.2	975.6
127.5°	941.7	949.3	987.4	1016.7	1023.6
130°	995.3	1002.9	1033.4	1062.5	1068.1
132.5°	1045.3	1054.2	1077.1	1105.0	1110.7
135°	1097.8	1103.2	1121.9	1148.7	1151.8
137.5°	1142.4	1150.1	1161.4	1187.8	1192.0
140°	1185.8	1192.5	1199.7	1223.7	1228.0
142.5°	1227.1	1232.5	1235.8	1256.1	1259.2
145°	1265.1	1271.6	1273.8	1286.4	1291.6
147.5°	1300.6	1306.2	1308.4	1314.5	1314.2
150°	1334.1	1337.4	1339.7	1341.9	1341.2
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)