

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010692

Luminaire Tested: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010692
REPORT IS A COMBINATION OF REPORTS P990181 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5413.0 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010692

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010692

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1010692

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	1.5
10°-20°	234.8	4.3
20°-30°	346.8	6.4
30°-40°	405.1	7.5
40°-50°	407.2	7.5
50°-60°	357.7	6.6
60°-70°	266.4	4.9
70°-80°	151.6	2.8
80°-90°	45.1	0.8
90°-100°	36.0	0.7
100°-110°	174.2	3.2
110°-120°	426.9	7.9
120°-130°	541.9	10.0
130°-140°	578.9	10.7
140°-150°	541.4	10.0
150°-160°	436.7	8.1
160°-170°	281.8	5.2
170°-180°	97.1	1.8
0°-30°	664.8	12.3
0°-40°	1069.9	19.8
0°-60°	1834.9	33.9
0°-90°	2298.0	42.5
90°-120°	637.1	11.8
90°-150°	2299.4	42.5
90°-180°	3115.0	57.5
0°-180°	5413.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	1	8	18	21	23	5
95°	46	15	24	29	29	55
105°	226	235	166	32	33	240
115°	424	429	436	443	446	419
125°	598	604	607	609	610	534
135°	745	749	752	755	752	573
145°	859	865	866	868	868	538
155°	947	945	946	950	945	436
165°	998	996	995	1001	996	282
175°	1022	1018	1019	1024	1018	97
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P1010692

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	0.8	8.4	18.2	21.3	22.8
92.5°	17.5	12.9	19.7	25.1	25.8
95°	46.3	15.2	23.5	28.8	28.8
97.5°	84.3	63.0	24.3	30.4	31.1
100°	128.3	143.5	25.1	31.1	31.9
102.5°	178.4	188.3	56.2	31.1	32.6
105°	226.2	234.6	166.2	31.9	33.4
107.5°	277.1	283.9	295.3	178.4	78.9
110°	327.9	334.0	342.4	317.3	208.8

TEST NUMBER: P1010692

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.5	381.8	390.2	397.0	395.5
115°	424.3	428.9	435.7	443.3	446.4
117.5°	471.4	476.7	480.5	486.6	487.4
120°	514.7	521.5	523.8	529.9	529.9
122.5°	558.7	564.0	567.1	570.9	571.6
125°	598.2	604.3	607.3	608.8	610.3
127.5°	637.7	643.7	647.5	649.8	648.3
130°	674.1	680.2	683.2	686.2	684.7
132.5°	709.0	715.1	717.4	720.4	718.1
135°	744.7	749.2	752.3	754.6	752.3
137.5°	775.1	781.1	782.7	786.4	784.9
140°	805.4	810.0	812.3	815.3	813.8
142.5°	833.5	838.1	840.3	842.6	840.3
145°	859.3	864.6	866.2	867.7	867.7
147.5°	884.4	888.2	889.7	891.2	887.4
150°	907.1	909.4	910.9	912.5	910.2
152.5°	927.6	928.4	929.2	932.2	928.4
155°	946.6	945.1	945.9	949.7	945.1
157.5°	961.8	961.8	961.0	965.6	959.5
160°	975.5	974.7	973.9	978.5	973.2
162.5°	988.4	986.1	985.3	990.6	986.1
165°	998.2	996.0	995.2	1001.3	996.0
167.5°	1006.6	1003.6	1003.6	1009.6	1003.6
170°	1013.4	1010.4	1010.4	1016.5	1010.4
172.5°	1018.0	1014.2	1014.9	1021.0	1014.2
175°	1021.8	1018.0	1018.7	1024.0	1018.0
177.5°	1023.3	1019.5	1020.3	1026.3	1018.7
180°	1021.8	1021.8	1021.8	1021.8	1021.8

(END OF REPORT)