

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010693

Luminaire Tested: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010693
REPORT IS A COMBINATION OF REPORTS P990182 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5235.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010693

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010693

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9182	9182	9182
5°	9204	8865	8852
10°	9122	8564	8477
15°	8996	8253	8069
20°	8851	7906	7664
25°	8663	7541	7232
30°	8457	7162	6776
35°	8241	6776	6324
40°	8015	6370	5880
45°	7767	5975	5415
50°	7514	5535	4949
55°	7190	5075	4476
60°	6857	4569	3974
65°	6541	4021	3449
70°	6090	3413	2837
75°	5440	2703	2202
80°	4696	1900	1557
85°	3660	1022	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7767 cd/sqm

TEST NUMBER: P1010693

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	1.5
10°-20°	227.1	4.3
20°-30°	335.4	6.4
30°-40°	391.7	7.5
40°-50°	393.8	7.5
50°-60°	345.9	6.6
60°-70°	257.6	4.9
70°-80°	146.6	2.8
80°-90°	43.6	0.8
90°-100°	34.9	0.7
100°-110°	168.5	3.2
110°-120°	412.9	7.9
120°-130°	524.2	10.0
130°-140°	560.0	10.7
140°-150°	523.6	10.0
150°-160°	422.4	8.1
160°-170°	272.6	5.2
170°-180°	93.9	1.8
0°-30°	642.8	12.3
0°-40°	1034.5	19.8
0°-60°	1774.1	33.9
0°-90°	2222.0	42.4
90°-120°	616.3	11.8
90°-150°	2224.1	42.5
90°-180°	3013.0	57.6
0°-180°	5235.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	853	853	853	853	853	
5°	854	850	842	849	848	81
15°	813	810	800	806	802	229
25°	738	734	724	725	722	340
35°	638	634	624	620	616	399
45°	523	520	510	502	498	404
55°	397	396	386	378	375	355
65°	271	267	260	254	252	267
75°	143	140	138	134	132	153
85°	38	37	37	35	35	41
90°	1	8	18	21	22	5
95°	45	15	23	28	28	54
105°	219	227	161	31	32	232
115°	410	415	422	429	432	405
125°	579	584	587	589	590	517
135°	720	725	728	730	728	555
145°	831	836	838	839	839	520
155°	916	914	915	919	914	422
165°	966	963	963	968	963	273
175°	988	985	985	990	985	94
180°	988	988	988	988	988	

TEST NUMBER: P1010693

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	853.0	853.0	853.0	853.0	853.0
2.5°	856.7	853.7	845.7	853.0	852.3
5°	853.7	850.1	842.0	849.3	847.9
7.5°	847.1	843.5	835.4	842.0	841.3
10°	838.3	834.7	825.1	831.7	830.3
12.5°	826.6	823.7	814.9	819.3	818.5
15°	812.7	809.7	800.2	806.1	801.7
17.5°	797.3	793.6	784.1	788.5	787.0
20°	779.7	775.3	765.7	768.7	766.5
22.5°	759.9	755.5	745.9	748.1	745.2
25°	737.9	733.5	723.9	724.7	722.5
27.5°	715.1	710.7	700.4	701.2	699.0
30°	690.2	686.5	676.2	676.2	671.1
32.5°	665.2	660.1	652.8	647.6	645.4
35°	638.1	633.7	624.2	619.8	616.1
37.5°	611.0	605.1	595.6	590.4	588.2
40°	582.4	578.0	567.7	561.8	558.9
42.5°	553.8	548.6	538.4	532.5	529.6
45°	523.0	520.0	510.5	501.7	498.0
47.5°	492.9	488.5	479.7	470.9	467.9
50°	462.1	458.4	448.9	440.8	436.4
52.5°	429.8	427.6	417.3	410.7	406.3
55°	396.8	396.1	386.5	378.5	374.8
57.5°	366.0	363.1	355.7	348.4	344.0
60°	332.3	331.5	322.7	316.1	312.5
62.5°	302.2	300.0	291.2	284.6	282.4
65°	270.6	267.0	259.6	253.8	251.6
67.5°	236.9	234.0	228.1	223.0	220.0
70°	206.8	202.4	198.0	192.9	189.2
72.5°	175.3	172.4	167.2	162.8	161.4
75°	143.0	140.1	137.9	134.2	132.0
77.5°	114.4	113.0	110.0	107.1	107.1
80°	86.5	84.3	82.9	82.1	82.1
82.5°	59.4	59.4	59.4	57.9	57.2
85°	38.1	36.7	36.7	35.2	35.2
87.5°	19.1	16.9	16.1	15.4	15.4
90°	0.7	8.1	17.6	20.6	22.0
92.5°	16.9	12.5	19.1	24.2	25.0
95°	44.8	14.7	22.8	27.9	27.9
97.5°	81.5	60.9	23.5	29.4	30.1
100°	124.1	138.8	24.2	30.1	30.8
102.5°	172.6	182.1	54.3	30.1	31.6
105°	218.8	226.9	160.8	30.8	32.3
107.5°	268.0	274.6	285.6	172.6	76.4
110°	317.2	323.1	331.2	306.9	201.9

TEST NUMBER: P1010693

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	369.3	377.4	384.0	382.6
115°	410.5	414.9	421.5	428.8	431.8
117.5°	456.0	461.1	464.8	470.7	471.4
120°	497.8	504.4	506.7	512.5	512.5
122.5°	540.4	545.6	548.5	552.2	552.9
125°	578.6	584.5	587.4	588.9	590.4
127.5°	616.8	622.7	626.3	628.5	627.1
130°	652.0	657.9	660.8	663.8	662.3
132.5°	685.8	691.7	693.9	696.8	694.6
135°	720.3	724.7	727.7	729.9	727.7
137.5°	749.7	755.6	757.0	760.7	759.2
140°	779.1	783.5	785.7	788.6	787.1
142.5°	806.2	810.6	812.8	815.0	812.8
145°	831.2	836.3	837.8	839.3	839.3
147.5°	855.4	859.1	860.6	862.0	858.4
150°	877.5	879.7	881.1	882.6	880.4
152.5°	897.3	898.0	898.8	901.7	898.0
155°	915.6	914.2	914.9	918.6	914.2
157.5°	930.3	930.3	929.6	934.0	928.1
160°	943.5	942.8	942.1	946.5	941.3
162.5°	956.0	953.8	953.1	958.2	953.8
165°	965.6	963.4	962.6	968.5	963.4
167.5°	973.7	970.7	970.7	976.6	970.7
170°	980.3	977.3	977.3	983.2	977.3
172.5°	984.7	981.0	981.7	987.6	981.0
175°	988.3	984.7	985.4	990.5	984.7
177.5°	989.8	986.1	986.9	992.7	985.4
180°	988.3	988.3	988.3	988.3	988.3

(END OF REPORT)